

EPROM

Memory size	Type No.	Organization	Maximum access time (ns)	Minimum cycle time (ns)	Power supply (V)	Operating temperature (°C)	Maximum power consumption (mW)		No. of pins	Type
							Active	Standby		
64K Bit	TMM2764AD-15	8,192 × 8	150	150	5V ± 5%	0 ~ 70	525	158	28	NMOS
	TMM2764AD-20		200	200						
	TMM2764AD-150		150	150	5V ± 10%		660	193		
	TMM2764AD-200		200	200						
128K Bit	TMM27128AD-15	16,384 × 8	150	150	5V ± 5%	0 ~ 70	525	158	28	NMOS
	TMM27128AD-20		200	200						
	TMM27128AD-150		150	150	5V ± 10%		660	193		
	TMM27128AD-200		200	200						
256K Bit	TMM27256BD-15	32,768 × 8	150	150	5V ± 5%	0 ~ 70	525	158	28	NMOS
	TMM27256BD-20		200	200						
	TMM27256BD-150		150	150	5V ± 10%		660	193		
	TMM27256BD-200		200	200						
	TC57256AD-12		120	120	5V ± 5%	-40 ~ 85	158	0.525	28	CMOS
	TC57256AD-150		150	150	5V ± 10%		165	0.550		
	TC57256AD-15		150	150						
	TC57256AD-20		200	200	5V ± 5%					
	TC57H256D-70		70	70		0 ~ 70	263	0.525		
	TC57H256D-85		85	85	5V ± 10%		275	0.550		
512K Bit	TMM27512AD-17	65,536 × 8	170	170		0 ~ 70			28	NMOS
	TMM27512AD-20		200	200	5V ± 5%		630	184		
	TMM27512AD-25		250	250						
	TMM27512AD-200		200	200	5V ± 10%		715	220		
	TMM27512AD-250		250	250		-40 ~ 85			28	CMOS
	TC57512AD-15		150	150	5V ± 5%		158	0.525		
	TC57512AD-20		200	200						
1M Bit	TC571000/1D-15	131,072 × 8	150	150	5V ± 5%	0 ~ 70			32	CMOS
	TC571000/1D-20		200	200		-40 ~ 85	158	0.525		
	TC571000/1D-200		200	200	5V ± 10%		165	0.550		
	* TC57100/1D-12		120	120	5V ± 5%	0 ~ 70	210	0.525		
	* TC57100/1AD-85	65,536 × 16	85	85			210	0.6525	40	CMOS
	TC571024D-15		150	150	5V ± 5%	0 ~ 70	210	0.525		
	TC571024D-20		200	200		-40 ~ 85				
	TC571024D-200		200	200	5V ± 10%		220	0.550		
	* TC571024D-85		85	85	5V ± 5%	0 ~ 70	210	0.525		
	* TC57H1024D-100		100	100	5V ± 10%		220	0.550		
	* TC57H1024AD-70		70	70			210	0.525		
	* TC57H1025AD-55		55	55	5V ± 5%					
4M Bit	* TC574000D-120	524,288 × 8	120	120	5V ± 10%	0 ~ 70	165	0.550	32	CMOS
	* TC574000D-150	262,144 × 16	150	150		0 ~ 70			40	CMOS
	* TC574200D-120		120	120	5V ± 10%		220	0.550		
	* TC574200D-150		150	150						

※: New product *: Under development