

Search Results

Evaluate

- Brochures
- PDF-Labeling and ..
- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Mini-Com Ult ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'UICFPSE2BL'

Your search criteria matched only one product, shown below

UICFPSE2BL



- Ultimate ID® components are part of a complete system for identification designed to efficiently support TIA/EIA-606-A standard labeling requirements
- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Raised rail design for aesthetic appeal
- Supplied with color coordinated screw cover and clear station and port label covers, labels sold separately
- Can be clearly identified with the PanTher™ LS8E or Cougar™ LS9 Hand-Held Thermal Transfer Printers
- Non-adhesive computer printable label sheets for desktop printers and write-on labels available
- Replacement screw covers and label covers available
- Optional icons available

• Part Number	UICFPSE2BL
• RoHS Compliancy Status	Compliant
• Part Description	Single gang, vertical sloped Ultimate ID® faceplate holds up to two Mini-Com® Modules.
• Product Type	Faceplate
• Material	ABS
• Color	Black
• Height (In.)	4.50
• Height (mm)	114.3
• Width (In.)	2.75
• Width (mm)	69.8
• CE Compliant	No
• Labels Required	1-One Port, 1-Two Port
• No. of Module Spaces	2
• No. of Ports	2
• Overall Size W x H (In.)	2.75 x 4.5
• Overall Size W x H (mm)	69.8mm x 114.3mm
• Pricing Description	Faceplate, 2 Port, Executive, Sloped, Ultimate ID, Black
• Thickness (In.)	1.09
• Thickness (mm)	27.7
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.