

REVISIONS

A	C077942	JAF	28 JUN 94
B	C095307	CST	18 NOV 99
C	C094431	CST	24 NOV 99

REPLACES

PR-2142

RELEASE NO

CHECK

CHECK

CHECK

JAF 28 JUN 94

FORMTEK

DRAWN

MICRO SWITCH



FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - TOGGLE

CATALOG LISTING
1TL5 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

	DIM.	TOL.	DIM.	TOL.
NO PLACES	X	1/64	X	0.015
ONE PLACE	X	0.015	X	0.015
TWO PLACES	X, XX	0.005	X, XX	0.005
THREE PLACES	X, XX, XXX	0.0005	X, XX, XXX	0.0005

SI METRIC

US CUSTOMARY

DESIGN UNITS

RAW MATERIAL - COMMERCIAL STANDARD

MICRO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE

PROTECTIVE COATINGS ARE APPLIED

WEIGHT

CATALOG LISTING


CIRCUIT MADE
WITH TOGGLE LEVER INKEYWAY
SIDE
(1-2)CENTER
(1-2)OPPOSITE
KEYWAY
(2-3)

ELECTRICAL RATING


15A-125, 250 OR 277VAC
1/2HP-125VAC; 1HP-250, 277VAC
5A-125VAC "L" CODE L19110A-125, 250, 277VAC
1/4-125VAC; 1/2HP-250, 277VAC
3A-125VAC "L" L192

NOTES


- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
- 2 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING, MARKED ON SIDE OF SWITCH
- 3 - FURNISHED UNASSEMBLED
- 4 - FOR TERMINAL COVER, SEE MICRO SWITCH CATALOG LISTING 5PA7
- 5 - APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
- 6 - BRIGHT FINISH TOGGLE LEVER AND MOUNTING NUTS



LOCKWASHER



LOCKING RING



HEX NUT