


344071-1 Product Details

[Share](#) [Print](#) [Email](#)

344071-1

TE Internal Number: 344071-1

 [Active](#)

Econoseal III

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 250 Series
- Wire-to-Wire
- Applies To Wire/Cable
- Contact
- Contact Type = Tab

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [.250 SERIES TAB HIGH CURR](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Product Photo](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = 250
- [Product Type](#) = Contact
- Wire/Cable Type = Discrete Wire
- Cable Type = Thin Wall
- Termination Method to Wire/Cable = Crimp

Electrical Characteristics:

- Contact - Rated Current (A) = 20
- Operating Voltage Reference = DC

Termination Features:

- Wire/Cable Size (AWG) = 15 - 20
- Wire/Cable Size (mm²) = 0.5 - 1.5

Body Features:

- Wire Type = Stranded

Contact Features:

- Contact Type = Tab
- Contact Base Material = Brass
- Contact Plating, Mating Area, Material = Tin

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Wire/Cable
- Accepts Wire Insulation Diameter, Range (mm [in]) = 1.60 - 2.39 [0.063 - 0.094]

Operation/Application:

- Application Use = Wire-to-Wire
- Contact Transmits (Typical Application) = Power

Packaging Features:

- Packaging Method = Reel
- Packaging Quantity = 3,000

Other:

- GET 0.64 Connector System = No
- Brand = AMP

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

