EZ-LIGHT® TL50 Universal AC Voltage Tower Light

Multi-Color General-Purpose or Audible Indicators



- Rugged, cost-effective, and easy-to-install multi-segment indicators
- Illuminated segments provide easy-to-see operator guidance and indication of equipment status
- Displays up to 5 colors
- Available in black or light gray housing
- Audible models available with standard, sealed, or omni-directional audible element
- Compact devices are completely self-contained - no controller needed
- 85 to 264V ac operation
- No assembly required

Non-Audible Models

Model[1]	# of LED Colors	LED Function[2]	Connection[3]	Inputs
TL50ZR	1	Red	4-wire PVC cable	85-264V ac
TL50ZGR	2	Green, Red		
TL50ZGYR	3	Green, Yellow, Red		
TL50ZBGYR	4	Blue, Green, Yellow, Red	5-wire PVC cable	
TL50ZWBGYR	5	White, Blue, Green, Yellow, Red	6-wire PVC cable	

Audible Models

Standard Audible Models[1]	# of LED Colors	LED Function[2]	Connection[3]	Inputs
TL50ZRA	1	Red	4-wire PVC cable	85-264V ac
TL50ZGRA	2	Green, Red		
TL50ZGYRA	3	Green, Yellow, Red	5-wire PVC cable	
TL50ZBGYRA	4	Blue, Green, Yellow, Red	6-wire PVC cable	

Sealed Audible Models[1]			# of LED Colors	LED Function[2]	Connection[3]	Inputs
Continuous	Pulsed at 1.6 Hz	Staccato				
TL50ZRALS	TL50ZRALS3	TL50ZRALS4	1	Red	4-wire PVC cable	85-264V ac
TL50ZGRALS	TL50ZGRALS3	TL50ZGRALS4	2	Green, Red		
TL50ZGYRALS	TL50ZGYRALS3	TL50ZGYRALS4	3	Green, Yellow, Red	5-wire PVC cable	
TL50ZBGYRALS	TL50ZBGYRALS3	TL50ZBGYRALS4	4	Blue, Green, Yellow, Red	6-wire PVC cable	

Omni-Directional Sealed Audible Models[1]			# of LED Colors	LED Function[2]	Connection[3]	Inputs
Continuous	Pulsed at 1.6 Hz	Staccato				
TL50ZRAOS	TL50ZRAOS3	TL50ZRAOS4	1	Red	4-wire PVC cable	85-264V ac
TL50ZGRAOS	TL50ZGRAOS3	TL50ZGRAOS4	2	Green, Red		
TL50ZGYRAOS	TL50ZGYRAOS3	TL50ZGYRAOS4	3	Green, Yellow, Red	5-wire PVC cable	
TL50ZBGYRAOS	TL50ZBGYRAOS3	TL50ZBGYRAOS4	4	Blue, Green, Yellow, Red	6-wire PVC cable	

[1] Cabled Black models only are listed. For gray housing, add suffix **C** at the end of the model number (cabled models) or before the **QP** (pigtail models), for example, **TL50ZRC** or **TL50ZRCQP**.

[2] The first color listed is the bottom color, going up in successive order. Contact the factory for other colors and color combinations. Five color options are only available in non-audible cabled models. Four color options are only available in audible cabled models.

[3] Cabled models only are listed; mating cordset required for pigtail models (see *Cordsets* on page 3). For 150 mm (5.9 in) PVC pigtail with QD, add **QP** to the end of the model number, for example, **TL50ZRQP**.

Specifications

Supply Voltage and Current
85 - 264V ac; 50 or 60 Hz
Indicators: Max. current per LED color:
- **at 85V ac:** 35 mA
- **at 120V ac:** 30 mA
- **at 240V ac**: 20 mA
- **at 264V ac:** 18 mA

Standard Audible Alarm: 30 mA max. current
Sealed Audible Alarm: 35 mA max. current
Omni-Directional Sealed Audible Alarm: 45 mA max. current

Indicators
LEDs are independently selected, 1 to 5 colors depending on model

Supply Protection Circuitry:
Protected against reverse polarity and transient voltages

Input Response Time
Indicator ON/OFF: 500 ms (max.)

Audible Adjustment
Standard Audible Alarm: Unscrew the cover (up to 1.5 turns max.) to adjust the audible intensity. Do not exceed 1.5 turns or the cover may detach during operation. For max. intensity, rotate the center plug 180° counterclockwise to remove it.
Sealed Audible Alarm: Rotate the front cover until the desired intensity is reached.
Omni-Directional Sealed Audible Alarm: No adjustment.

Connections
4-wire, 5-wire, or 6-wire 2m (6.5 ft) integral cable; 4-pin or 5-pin 150 mm (5.9 in) PVC pigtail with QD, depending on model

Leakage Current Immunity
500µA
Application Note: The use of relay output PLC is recommended since there is no leakage current. Solid state output PLCs often have leakage current above 1mA and, therefore, turn the light on in the off state. To counteract the leakage current, a shunt resistor must be used. A resistor must be applied from the neutral wire of the device to the hot wire of each channel of the device.

Vibration and Mechanical Shock:
All models meet Mil. Std. 202F requirements method 201A (vibration: 10 to 60 Hz max., double amplitude 0.06 in, maximum acceleration 10G). Also meets IEC 947-5-2; 30G 11 ms duration, half sine wave.

Operating Conditions:
Non-Audible: −40° to +50° C (−40° to +122° F)
Standard and Sealed Audible: −20° to +50° C (−4° to +122° F)
Max. Rel. Humidity: 95% at 50° C (non-condensing)

Audible Alarm
Audible measurements are made in the direction sound exits the device. For standard audible models, this is the top of the unit (when mounted vertically, sound is directed toward the ceiling). For sealed audible models, sound exits the vented openings in the side of the unit, which should be oriented so that the sound is directed toward the machine operator(s). In environments with high ambient noise levels or high ceilings that absorb sound, the sealed or omni-directional models are recommended.
Standard Audible Alarm: 2.7 KHz ± 500 Hz oscillation frequency; max. intensity 92 db at 1 m (3.3 ft) (typical)
Sealed Audible Alarm: 2.9 KHz ± 250 Hz oscillation frequency; max. intensity 94 db at 1 m (3.3 ft) (typical)
Omni-Directional Sealed Audible Alarm: 2.1 KHz ± 250 Hz oscillation frequency; max intensity 99 db at 1m (3.3 ft) (typical)

Construction:
Bases and Covers: ABS
Light Segment: Polycarbonate

Environmental Rating
Non-Audible and Sealed Audible: IEC IP67
Standard Audible: IEC IP50

Certifications
Approvals pending

Dimensions



# of Colors	Tower Height (H)			
	Non-Audible	Standard Audible*	Sealed Audible	Omni-Directional Sealed Audible
1	130.2mm (5.1 in)	161.0mm (6.3 in)	184.1mm (7.2 in)	198.1 mm (7.8 in)
2	170.9mm (6.7 in)	201.7mm (7.9 in)	224.8mm (8.9 in)	238.8 mm (9.4 in)
3	211.6mm (8.3 in)	242.4mm (9.5 in)	265.5mm (10.5 in)	279.5 mm (11.0 in)
4	252.3mm (9.9 in)	283.1mm (11.1 in)	306.2mm (12.1 in)	320.2 mm (12.6 in)
5	293.0mm (11.5 in)	-	-	-

* Tower height (H) with top unscrewed approximately 3.5 mm to allow sound to escape

Hookups

4-wire Hookup	5-wire Hookup	6-wire Hookup
		
1 = Brown 2 = Blue 3 = Black 4 = White C1 = Color 1 C2 = Color 2 C3 = Color 3 A = Audible	1 = Brown 2 = Blue 3 = White 4 = Black 5 = Gray C1 = Color 1 C2 = Color 2 C3 = Color 3 C4 = Color 4 A = Audible	1 = Brown 2 = Blue 3 = White 4 = Black 5 = Gray 6 = Red C1 = Color 1 C2 = Color 2 C3 = Color 3 C4 = Color 4 C5 = Color 5 A = Audible

Accessories

Cordsets

4-Pin Micro-Style Cordsets				
Model	**Length**	**Style**	**Dimensions**	**Pinout**
MQAC2-406	1.83 m (6 ft)	Straight		 1 = Brown 2 = Blue 3 = Black 4 = White
MQAC2-415	4.57 m (15 ft)			
MQAC2-430	9.14 m (30 ft)			

5-Pin Micro-Style Cordsets				
Model	**Length**	**Style**	**Dimensions**	**Pinout**
MQAC2-506	1.83 m (6 ft)	Straight		 1 = Brown 2 = Blue 3 = White 4 = Black 5 = Gray
MQAC2-515	4.57 m (15 ft)			
MQAC2-530	9.14 m (30 ft)			

Mounting Brackets

All measurements in mm

SMB30A

- Right-angle bracket with curved slot for versatile orientation
- Clearance for M6 (¼ in) hardware
- Mounting hole for 30 mm sensor
- 12-ga. stainless steel



Hole center spacing: A to B=40
Hole size: A=ø 6.3, B= 27.1 x 6.3, C=ø 30.5

SMB30FA

- Swivel bracket with tilt and pan movement for precise adjustment
- Mounting hole for 30 mm sensor
- 12-ga. 304 stainless steel
- Easy sensor mounting to extrude rail T-slot
- Metric and inch size bolt available



Bolt thread: SMB30FA, A= 3/8 - 16 x 2 in; SMB30FAM10, A= M10 - 1.5 x 50
Hole size: B= ø 30.1

SMB30MM

- 12-ga. stainless steel bracket with curved mounting slots for versatile orientation
- Clearance for M6 (¼ in) hardware
- Mounting hole for 30 mm sensor



Hole center spacing: A = 51, A to B = 25.4
Hole size: A = 42.6 x 7, B = ø 6.4, C = ø 30.1

SMBAMS30P

- Flat SMBAMS series bracket
- 30 mm hole for mounting sensors
- Articulation slots for 90+° rotation
- 12-ga. 300 series stainless steel



Hole center spacing: A=26.0, A to B=13.0
Hole size: A=26.8 x 7.0, B=ø 6.5, C=ø 31.0

SMBAMS30RA

- Right-angle SMBAMS series bracket
- 30 mm hole for mounting sensors
- Articulation slots for 90+° rotation
- 12-ga. (2.6 mm) cold-rolled steel



Hole center spacing: A=26.0, A to B=13.0
Hole size: A=26.8 x 7.0, B=ø 6.5, C=ø 31.0

SMB30SC

- Swivel bracket with 30 mm mounting hole for sensor
- Black reinforced thermoplastic polyester
- Stainless steel mounting and swivel locking hardware included



Hole center spacing: A=ø 50.8
Hole size: A=ø 7.0, B=ø 30.0

LMB Sealed Right-Angle Bracket

Model	Description	Construction	
LMB30RA	**Direct-Mount Models:** Bracket kit with base, 30 mm adapter, set screw, fasteners, o-rings, and gaskets	Black polycarbonate	
LMB30RAC		Gray polycarbonate	
LMBE12RA	**Pipe-Mount Models:** Bracket kit with base, ½-14 pipe adapter, set screw, fasteners, o-rings, and gaskets. For use with stand-off pipe (listed and sold separately)	Black polycarbonate	
LMBE12RAC		Gray polycarbonate	

Elevated Mount System

<table>
<tr><th colspan="3">Model</th><th>Features</th><th>Components</th></tr>
<tr><td colspan="3">SA-M30TE12 - Black Acetal</td><td rowspan="2">• Streamlined black acetal or white UHMW stand-off pipe adapter/cover
• Connects between 30 mm light base and ½ in. NPSM/DN15 pipe
• Mounting hardware included</td><td rowspan="2"> </td></tr>
<tr><td colspan="3">SA-M30TE12C - White UHMW</td></tr>
<tr><td>Polished 304 Stainless Steel</td><td>Black Anodized Aluminum</td><td>Clear Anodized Aluminum</td><td rowspan="4">• Elevated-use stand-off pipe (½ in. NPSM/DN15)
• Polished 304 stainless steel, black anodized aluminum, or clear anodized aluminum surface
• ½ in. NPT thread at both ends
• Compatible with most industrial environments</td><td rowspan="4"> </td></tr>
<tr><td>SOP-E12-150SS
150 mm (6 in) long</td><td>SOP-E12-150A
150 mm (6 in) long</td><td>SOP-E12-150AC
150 mm (6 in) long</td></tr>
<tr><td>SOP-E12-300SS
300 mm (12 in) long</td><td>SOP-E12-300A
300 mm (12 in) long</td><td>SOP-E12-300AC
300 mm (12 in) long</td></tr>
<tr><td>SOP-E12-900SS
900 mm (36 in) long</td><td>SOP-E12-900A
900 mm (36 in) long</td><td>SOP-E12-900AC
900 mm (36 in) long</td></tr>
<tr><td colspan="3">SA-E12M30 - Black Acetal</td><td rowspan="2">• Streamlined black acetal or white UHMW mounting base adapter/cover
• Connects between ½ in. NPSM/DN15 pipe and 30 mm (1-3/16 in) drilled hole
• Mounting hardware included</td><td rowspan="2"> </td></tr>
<tr><td colspan="3">SA-E12M30C - White UHMW</td></tr>
</table>

Banner Engineering Corp Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. **IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.**

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp.