

SMF5.0AT1 Series

200 W Transient Voltage Suppressor SOD-123 Flat Lead Package

The SMF5.0A Series is designed to protect voltage sensitive components from high voltage, high energy transients. Excellent clamping capability, high surge capability, low zener impedance and fast response time. Because of its small size, it is ideal for use in cellular phones, portable devices, business machines, power supplies and many other industrial/consumer applications.

Features

- Stand-off Voltage: 5 – 58 Volts
- Peak Power – 200 Watts @ 1 ms (SMF5.0A – SMF58A)
- Low Leakage
- Response Time is Typically < 1 ns
- ESD Rating of Class 3 (> 16 kV) per Human Body Model
- ESD Rating of Level 4 (8 kV Contact Discharge) per IEC61000-4-2
- EFT (Electrical Fast Transients) Rating of 40 A per IEC61000-4-4
- Low Profile – Maximum Height of 1.0 mm
- Small Footprint – Footprint Area of 8.45 mm²
- Supplied in 8 mm Tape and Reel – 3,000 Units per Reel
- Cathode Indicated by Polarity Band
- Lead Orientation in Tape: Cathode Lead to Sprocket Holes
- Pb-Free Packages are Available

Mechanical Characteristics:

CASE: Void-free, transfer-molded, thermosetting plastic
Epoxy Meets UL 94 V-0

LEAD FINISH: 100% Matte Sn (Tin)

MOUNTING POSITION: Any

QUALIFIED MAX REFLOW TEMPERATURE: 260°C



Device Meets MSL 1 Requirements



ON Semiconductor®


<http://onsemi.com>

PLASTIC SURFACE MOUNT ZENER OVERVOLTAGE TRANSIENT SUPPRESSOR 5 – 58 VOLTS 200 WATT PEAK POWER



**SOD-123FL
CASE 498
PLASTIC**

MARKING DIAGRAM



xx = Device Code (Refer to page 3)
M = Date Code
▪ = Pb-Free Package
(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping†
SMFxxxAT1G	SOD-123FL (Pb-Free)	3000/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

DEVICE MARKING INFORMATION

See specific marking information in the device marking column of the Electrical Characteristics table on page 3 of this data sheet.

SMF5.0AT1 Series

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Maximum P_{pk} Dissipation (PW-10/1000 μ s) (Note 1) SMF5.0A – SMF58A	P_{pk}	200	W
Maximum P_{pk} Dissipation @ $T_A = 25^\circ\text{C}$, (PW-8/20 μ s) (Note 2)	P_{pk}	1000	W
DC Power Dissipation @ $T_A = 25^\circ\text{C}$ (Note 3) Derate above 25°C	P_D	385	mW
Thermal Resistance, Junction-to-Ambient (Note 3)	$R_{\theta JA}$	4.0	$\text{mW}/^\circ\text{C}$
Thermal Resistance, Junction-to-Lead (Note 3)	$R_{\theta Jcathode}$	325	$^\circ\text{C}/\text{W}$
Operating and Storage Temperature Range	T_J, T_{stg}	-55 to +150	$^\circ\text{C}$


Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Non-repetitive current pulse at $T_A = 25^\circ\text{C}$, per waveform of Figure 2.
2. Non-repetitive current pulse at $T_A = 25^\circ\text{C}$, per waveform of Figure 3.
3. Mounted with recommended minimum pad size, DC board FR-4.

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted, $V_F = 3.5\text{ V}$ Max. @ I_F (Note 4) = 12 A)

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F

4. 1/2 sine wave (or equivalent square wave), PW = 8.3 ms, duty cycle = 4 pulses per minute maximum.



SMF5.0AT1 Series

ELECTRICAL CHARACTERISTICS ($T_L = 30^\circ\text{C}$ unless otherwise noted, $V_F = 1.25$ Volts @ 200 mA)

Device*	Marking	V_{RWM} (V)	V_{BR} @ I_T (V) (Note 6)			I_T	I_R @ V_{RWM}	$V_{C(Max)}$	$I_{PP(Max)}$ (A)
		(Note 5)	Min	Nom	Max	(mA)	(μA)	(V)	(Note 7)
SMF5.0A, G	KE	5	6.4	6.7	7	10	400	9.2	21.7
SMF6.0A, G	KG	6	6.67	7.02	7.37	10	400	10.3	19.4
SMF6.5A, G	KK	6.5	7.22	7.6	7.98	10	250	11.2	17.9
SMF7.0A, G	KM	7	7.78	8.2	8.6	10	100	12	16.7
SMF7.5A, G	KP	7.5	8.33	8.77	9.21	1	50	12.9	15.5
SMF8.0A, G	KR	8	8.89	9.36	9.83	1	25	13.6	14.7
SMF8.5A, G	KT	8.5	9.44	9.92	10.4	1	10	14.4	13.9
SMF9.0A, G	KV	9	10	10.55	11.1	1	5	15.4	13.0
SMF10A, G	KX	10	11.1	11.7	12.3	1	2.5	17	11.8
SMF11A, G	KZ	11	12.2	12.85	13.5	1	2.5	18.2	11.0
SMF12A, G	LE	12	13.3	14	14.7	1	2.5	19.9	10.1
SMF13A, G	LG	13	14.4	15.15	15.9	1	1	21.5	9.3
SMF14A, G	LK	14	15.6	16.4	17.2	1	1	23.2	8.6
SMF15A, G	LM	15	16.7	17.6	18.5	1	1	24.4	8.2
SMF16A, G	LP	16	17.8	18.75	19.7	1	1	26	7.7
SMF17A, G	LR	17	18.9	19.9	20.9	1	1	27.6	7.2
SMF18A, G	LT	18	20	21	22.1	1	1	29.2	6.8
SMF20A, G	LV	20	22.2	23.35	24.5	1	1	32.4	6.2
SMF22A, G	LX	22	24.4	25.6	26.9	1	1	35.5	5.6
SMF24A, G	LZ	24	26.7	28.1	29.5	1	1	38.9	5.1
SMF26A, G	ME	26	28.9	30.4	31.9	1	1	42.1	4.8
SMF28A, G	MG	28	31.1	32.8	34.4	1	1	45.4	4.4
SMF30A, G	MK	30	33.3	35.1	36.8	1	1	48.4	4.1
SMF33A, G	MM	33	36.7	38.7	40.6	1	1	53.3	3.8
SMF36A, G	MP	36	40	42.1	44.2	1	1	58.1	3.4
SMF40A, G	MR	40	44.4	46.8	49.1	1	1	64.5	3.1
SMF43A, G	MT	43	47.8	50.3	52.8	1	1	69.4	2.9
SMF45A, G	MV	45	50	52.65	55.3	1	1	72.7	2.8
SMF48A, G	MX	48	53.3	56.1	58.9	1	1	77.4	2.6
SMF51A, G	MZ	51	56.7	59.7	62.7	1	1	82.4	2.4
SMF54A, G	NE	54	60	63.15	66.3	1	1	87.1	2.3
SMF58A, G	NG	58	64.4	67.8	71.2	1	1	93.6	2.1

5. A transient suppressor is normally selected according to the Working Peak Reverse Voltage (V_{RWM}) which should be equal to or greater than the DC or continuous peak operating voltage level.

6. V_{BR} measured at pulse test current I_T at ambient temperature of 25°C .

7. Surge current waveform per Figure 2 and derate per Figure 3.

*The "G" suffix indicates Pb-Free package available.

SMF5.0AT1 Series

TYPICAL PROTECTION CIRCUIT





Figure 1. Pulse Rating Curve




Figure 2. 10 X 1000 μs Pulse Waveform




Figure 3. 8 X 20 μs Pulse Waveform




Figure 4. Pulse Derating Curve

SMF5.0AT1 Series




Figure 5. Typical Derating Factor for Duty Cycle




Figure 6. Steady State Power Derating




Figure 7. Forward Voltage





Figure 8. Capacitance versus Working Peak Reverse Voltage

SMF5.0AT1 Series

PACKAGE DIMENSIONS

SOD-123FL
CASE 498-01
ISSUE A




NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH.
4. DIMENSIONS D AND J ARE TO BE MEASURED ON FLAT SECTION OF THE LEAD: BETWEEN 0.10 AND 0.25 MM FROM THE LEAD TIP.

DIM	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.90	0.95	1.00	0.035	0.037	0.039
A1	0.00	0.05	0.10	0.000	0.002	0.004
b	0.70	0.90	1.10	0.028	0.035	0.043
c	0.10	0.15	0.20	0.004	0.006	0.008
D	1.50	1.65	1.80	0.059	0.065	0.071
E	2.50	2.70	2.90	0.098	0.106	0.114
L	0.55	0.75	0.95	0.022	0.030	0.037
HE	3.40	3.60	3.80	0.134	0.142	0.150
θ	0°	-	8°	0°	-	8°

SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative