





Double & Triple with Ground Terminal Blocks

The CDLG2.5 is a double level and the CTLG2.5 is a triple level terminal block with an additional connection point for earthing (Grounding) cables.

This separate connection point is appropriately identified by the green-yellow imprint on its top.

The triple level terminal block is an ideal choice for motor, sensor, actuator and initiator connections.



Terminal Width	6 mm		6 mm		
Height x Length	50 x 71 mm		62 x 87.5 mm		
Stripping Length	9 mm		9 mm		
Insulation Material	Polyamide 6.6		Polyamide 6.6		
Type of Connection	5 Screw clamps & 2 tapped holes for cross connect.		7 Screw clamps & 1 tapped holes for cross connect.		
LED Voltage					
Approvals					
Wire Range	24-12 AWG		24-12 AWG		
Voltage Rating	300 V		300 V		
Current Rating	24 A		25 A		
Torque	4.5 lb-in		4.5 lb-in		
Other Approvals					
	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.	
Terminal Block	CDLG2.5	50	CTLG2.5	50	
End Plate 	EPCDLG2.5	50	EPCTLG2.5	50	
DIN Rail for ordering information refer to page 72					
End Stop for ordering information refer to page 74 	CA202	50	CA202	50	
	CA702	50	CA702	50	
	CA802	50	CA802	50	
Internal Jumper 	2 pole	CA627/2	100	CA627/2	100
	3 pole	CA627/3	50	CA627/3	50
	4 pole	CA627/4	50	CA627/4	50
	10 pole	CA627/10	10	CA627/10	10
Current Bars 	2 pole	CA703/1	100	CA703/1	100
	3 pole	CA704/1	100	CA704/1	100
	4 pole	CA705/1	100	CA705/1	100
	10 pole	CA732/10	100	CA732/10	100
	10 pole (breakable)	CA732/10-A	100	CA732/10-A	100
	100 pole	CA732/100	10	CA732/100	10
Shorting Sleeve & Screw 	CA611/S/Q	100	CA611/S/Q	100	
External Jumper 	2 pole	CA715/2	100	CA715/2	100
	3 pole	CA715/3	100	CA715/3	100
	4 pole	CA715/4	100	CA715/4	100
	10 pole	CA715/10	50	CA715/10	50
Marking Tags 	MT2	100	MT2	100	

COLOR BLOCKS

(other than grey standard)

When ordering please add color suffix to Cat. No.

Example: CTS2.5U-N/R

Color	Ordering Suffix
Red	R
Blue	BU
Black	BL
Orange	O
Green	G
Yellow	Y
White	W
Beige	BG
Dark Brown	DB