


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		P	REVISED PER ECO-11-004835	11MAR11	RK	HMR

D

OPENING FOR CABLE
(SEE DASH NO. FOR DIA.)



C


SIZE IDENTIFICATION LETTER
MOLDED IN APPROXIMATE AREA
SHOWN, SEE TABLE

#4-40 HEX NUT
(QTY. 2)
MATL: CARBON STEEL
FINISH: $\triangle 2$

#4-40 FIL HD SCREW
(QTY. 2)
MATL: STEEL
FINISH: $\triangle 2$

1.920
±.015


AMP LOGO



TEXTURED
FINISH

B

- PARTS PACKAGED UNASSEMBLED, AS A UNIT KIT.
- $\triangle 2$ ZINC PLATED .000200-.000400 THICK, CLEAR CHROMATE COATING.



CABLE CLAMP HALF
(QTY. 2)
MATL: ZINC ALLOY
FINISH:NICKEL OVER COPPER

#4-40 MOUNTING SCREW
(QTY. 2)
MATL: CARBON STEEL
FINISH: $\triangle 2$

D	.280	5745173-5
G	.350	5745173-4
K	.430	5745173-3
M	.480	5745173-2
P	.530	5745173-1
NECK SIZE IDENT	MAX CABLE DIA	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 12AUG05	 TE Connectivity			
DIMENSIONS: INCHES		CHK C. ROHDE 12AUG05				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY 12AUG05	NAME CABLE CLAMP KIT, SIZE 3, 180 DEGREE, AMPLIMITE			
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		—				
MATERIAL SEE CALLOUTS	FINISH SEE CALLOUTS	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-5745173	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 of 1	REV P	

D

C

5745173

B

A