







- 1 MATERIAL:HOUSING-HTN NYLON, BLACK, IR REFLOW PROCESSING COMPATIBLE, UL 94V-0. TERMINALS-.013[0.33] THICK PHOS BRONZE PLATED WITH .000050 [1.27μm] THICK HARD GOLD IN LOCALIZED AREA AND .000150 [3.18μm] THICK TIN-LEAD IN SOLDER AREA OVER .000050 [1.27μm] THICK NICKEL UNDERPLATE.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
4. ALL DIMENSIONS SHOWN IN BRACKETS [] ARE IN MILLIMETERS.



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SEE APPLICATION SPECIFICATION

SUGGESTED PANEL CUTOUT

557564-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN V. SLACK 31JAN92	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES [mm]		CHK B. FOX 08JUN92			
		APVD G. REED 08JUN92	NAME		
		PRODUCT SPEC 108-1392	MODULAR JACK ASSEMBLY, SIX PORT, 8 POSITION, RIGHT ANGLE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-2048			
MATERIAL		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-557564
FINISH		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1	REV B