






NOTES

- 1.製品詳細寸法については、527931000 DOC PART 000図面を参照下さい。
RE DETAILED DIMENSION, SEE 527931000 DOC PART 000
2. 梱包数量：1000個 / リール
NUMBER OF CONNECTORS：1000 PCS/REEL
3. リードテープ長さ LEAD TAPE LENGTH




4. トップテープの剥離強度：0.1N-1.3N(10-130gf)(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE：0.1N-1.3N(10-130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.



5. 材料(MATERIAL)
キャリアテープ(CARRIER TAPE)：ポリプロピレン(POLYPROPYLENE)
トップテープ(TOP TAPE)：PET, PE, PEF
リール(REEL)：ポリスチレン(PS) <リサイクル材を含む>
POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAINED>

6. 本製品は 52793**90 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52793**90.




24mm幅キャリアテープ
24mm WIDTH CARRIER TAPE


24	29.4	25.4	18.1	15.1	11.4	527931170	11
			17.1	14.1	10.4	527931070	10
			16.1	13.1	9.4	527930970	9
			15.1	12.1	8.4	527930870	8
			14.1	11.1	7.4	527930770	7
			13.1	10.1	6.4	527930670	6
			12.1	9.1	5.4	527930570	5
			11.1	8.1	4.4	527930470	4
キャリアテープ幅 CARRIER TAPE WIDTH	E	D	(C)	(B)	(A)	MATERIAL NO.	極数 CIRCUIT
					52793**70	MODEL NO.	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

EC NO: 108819 DRWN: RLALSANGI CHK'D: KTAKAHASHI REV APPR: TKUSUHARA01	2016/02/03	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®				
	2016/09/28			MM	NTS							
	2016/09/29	ANGULAR TOL ± 3.0 °		DRWN BY		DATE		1.0 FFC CONN ASSY NON ZIF SMT RA UPPER CONTACT EMBSTP PKG -LEAD FREE-				
	4 PLACES	± 0.2	RLALSANGI		2016/02/03							
	3 PLACES	± 0.2	CHK'D BY		DATE							
	2 PLACES	± 0.25	KTAKAHASHI		2016/09/28							
	1 PLACE	± 0.3	APPR BY		DATE							
	0 PLACES	± 0.3	TKUSUHARA01		2016/09/29		PRODUCT CUSTOMER DRAWING					
	A	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER		CUSTOMER	
			A3		52793			GENERAL				
DOCUMENT NUMBER 527930000					DOC TYPE PSD	DOC PART 000	SHEET NUMBER 2 OF 5					

RELEASE STATUS	P1	RELEASE DATE	29.09.2016	01:01:06
----------------	----	--------------	------------	----------





引き出し方向
PULL OUT DIRECTION

トップテープ
TOP TAPE

52793**19


SECTION:Y-Y

SECTION:X-X
(SCALE 4:1)

44mm幅キャリアテープ
44mm WIDTH CARRIER TAPE


44	49.4	45.4	34.1	31.1	27.4	527932770	27
			33.1	30.1	26.4	527932670	26
			32.1	29.1	25.4	527932570	25
			31.1	28.1	24.4	527932470	24
			30.1	27.1	23.4	527932370	23
			29.1	26.1	22.4	527932270	22
			28.1	25.1	21.4	527932170	21
			27.1	24.1	20.4	527932070	20
			26.1	23.1	19.4	527931970	19
			25.1	22.1	18.4	527931870	18
			24.1	21.1	17.4	527931770	17
キャリアテープ幅 CARRIER TAPE WIDTH	E	D	(C)	(B)	(A)	MATERIAL NO.	極数 CIRCUIT
					52793**70		MODEL NO.



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

EC NO: 108819 DRWN: RLALSANGI CHK'D: KTAKAHASHI APPR: TKUSUHARA01	2016/02/03 2016/09/28 2016/09/29	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®					
				MM		NTS							
		ANGULAR TOL ± 3.0 °		DRWN BY		DATE		1.0 FFC CONN ASSY NON ZIF SMT RA UPPER CONTACT EMBSTP PKG -LEAD FREE-					
				RLALSANGI		2016/02/03							
		4 PLACES ± 0.2		CHK'D BY		DATE							
		3 PLACES ± 0.2		KTAKAHASHI		2016/09/28							
		2 PLACES ± 0.25		APPR BY		DATE							
		1 PLACE ± 0.3		TKUSUHARA01		2016/09/29		PRODUCT CUSTOMER DRAWING					
		0 PLACES ± 0.3		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				52793				GENERAL	
						DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
A						527930000		PSD		000		4 OF 5	

RELEASE STATUS	P1	RELEASE DATE	29.09.2016	01:01:06
----------------	----	--------------	------------	----------


FORMAT: master-b-prod-A3
REVISION: 15
DATE: 2015/12/14





注記 NOTES:

1. 使用材料 MATERIAL
ハウジング: PPS, UL94V-0
ターミナル: リン青銅 (t=0.25)
メッキ: ニッケル下地 錫ピスマスメッキ
金具: リン青銅 (t=0.25)
メッキ: ニッケル下地 純錫メッキ
- HOUSING : PPS, UL94V-0
TERMINAL : PHOSPHOR BRONZE
PLATING : Sn-Bi OVER Ni
FITTING NAIL: PHOSPHOR BRONZE
PLATING : Sn OVER Ni
2. 基準面 [E] からの溶剤テールとフィッティングネイルの半田付け面のズレ量は、
上方向に0.1 MAX.、下方向0.15 MAX.とする。
MISALIGNMENT OF SOLDER TAIL AND FITTING NAIL FROM [E]
: UPPER DIRECTION 0.1 MAX., LOWER DIRECTION 0.15 MAX..
3. 偶数極に適用。
APPLY FOR EVEN CKT..
4. 本製品は 52793 **10 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52793**10.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
EC NO: 108819 DRWN: GB CHK'D: KTAKAHASHI APPR: TKUSUHARA01	2016/01/19 2016/09/28 2016/09/29	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®					
				MM		1:1							
		ANGULAR TOL ± 3.0 °		DRWN BY		DATE		1.0 FFC CONN NON ZIF SMT R/A (UPPER CONTACT) -LEAD FREE-					
				GB		2016/01/19							
		4 PLACES ± 0.2		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING					
				KTAKAHASHI		2016/09/28							
	3 PLACES ± 0.2		APPR BY		DATE		SERIES 52793						
			TKUSUHARA01		2016/09/29								
	2 PLACES ± 0.25		DRAWING SIZE		THIRD ANGLE PROJECTION		DOCUMENT NUMBER 527931000		MATERIAL NUMBER		CUSTOMER GENERAL		
			A3										
1 PLACE ± 0.3		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						DOC TYPE		DOC PART		SHEET NUMBER	
								PSD		000		2 OF 2	
0 PLACES ± 0.3													
A		REV											