


Specifications



Type : Nickel-Metal Hydride Battery			Size : AA Consumer Type	
Capacity ¹⁾	Typical		2100mAh	
	Minimum		2000mAh	
Nominal Voltage			1.2V	
Charging Current x Time		Fast Charge ²⁾		
Ambient Temp.	Charge Condition	Fast Charge ²⁾		0°C - 40°C
	Discharge Condition		0°C - 50°C	
	Storage Condition	Less than 30days		-20°C - 50°C
		Less than 90days		-20°C - 40°C
		Less than 1year		-20°C - 30°C
Internal Impedance ³⁾ (after discharge to E.V.=1.0V)			About 25mΩ(at 1000Hz)	
Weight ⁴⁾			About 29 g	
Size ⁴⁾ :(Diameter) x (Height)			14.35(D) x 50.4(H) mm	

1)Single cell capacity under the following condition.

Charge : 210mA×16h, Discharge : 420mA(E.V.=1.0V) at 20°C


2)Use recommended charging system.

3)After a few charge and discharge cycles under the above 1) condition.

4)With tube.

Typical Characteristics

Charge



Discharge

