






- NOTES:
1. MATERIAL AND FINISHS:
BODY - BERYLLIUM COPPER,ALBALOY PLATING
CONTACT - BERYLLIUM COPPER,GOLD PLATING
INSULATORS - DELRIN & TEFLON
FERRULE - COPPER,ALBAOY PLATING
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC 0-6 GHz
C. VSWR(RETURN LOSS): 1.5 MAX.
D. DIELECRTC WITHSTAND VOLTAGE: 1000 VRMS,MINS.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -40°C TO +155°C
- OTHER:
A. CRIMPED FERRULE: HEX CRIMP SIZE .100"
B. SOLDER CENTER CONDUCTOR
C. INSTALL INSULATOR
D. PRESS FIT METAL COVER



RECOMMENDED
CABLE STRIPPING DIMENSIONS
建議剝線尺寸

SCALE 8.000



THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	29-Jul-06	46108	CW
B	SEE SHEET 1 AND CHANGED THE HEX CRIMP SIZE TO .105	25-Aug-06	46240	CW
C	SEE SHEET 1 AND CHANGED THE HEX CRIMP SIZE TO .128	02-Aug-07	46731	
D	SEE SHEET 1	17-Sep-07		
E	SEE SHEET 1 AND CHANGED THE HEX CRIMP SIZE TO .105	24-Aug-10	48232	SH
F	1.80 WAS 2.70, 2.80 WAS 3.40; CRIMP HEX SIZE .100" WAS .105"	28-Jul-11	48709	SH

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ± 0.3mm ANGLES ±1°	MATERIAL SEE NOTES	DRAWN I.XU	DATE 27-Jul-11	TITLE MCX R/A CRIMP PLUG NON MAGNETIC (FOR RG-178)		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER C.WANG	DATE 29-Jul-06				
		APPROVED S.HSIEH	DATE 27-Jul-11				
		REFERENCE EAR # AND		SCALE: 8.0:1.0	SHEET 2 OF 2	DRAWING NO. 919-NMI22P-51A	
		CONFIGURATION LEVEL: □□□□		CAD FILE Root Folder\MCX\919-NMI22P-51A	DWG SIZE B	REV F	ITEM NO. 919-NMI22P-51A PART NO.919-NMI22P-51A

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.