

## IGBT

High speed DuoPack: IGBT in Trench and Fieldstop technology with soft, fast recovery anti-parallel diode

### IKW25N120H3

1200V high speed switching series third generation

Data sheet

High speed DuoPack: IGBT in Trench and Fieldstop technology with soft, fast recovery anti-parallel diode



#### Features:

TRENCHSTOP™ technology offering

- very low  $V_{CEsat}$
- low EMI
- Very soft, fast recovery anti-parallel diode
- maximum junction temperature 175°C
- qualified according to JEDEC for target applications
- Pb-free lead plating; RoHS compliant
- complete product spectrum and PSpice Models:  
<http://www.infineon.com/igbt/>

#### Applications:

- uninterruptible power supplies
- welding converters
- converters with high switching frequency



#### Key Performance and Package Parameters

| Type        | $V_{CE}$ | $I_C$ | $V_{CEsat}$ , $T_{vj}=25^{\circ}C$ | $T_{vjmax}$ | Marking  | Package    |
|-------------|----------|-------|------------------------------------|-------------|----------|------------|
| IKW25N120H3 | 1200V    | 25A   | 2.05V                              | 175°C       | K25H1203 | PG-TO247-3 |

**Table of Contents**

|                                           |    |
|-------------------------------------------|----|
| Description .....                         | 2  |
| Table of Contents .....                   | 3  |
| Maximum Ratings .....                     | 4  |
| Thermal Resistance .....                  | 4  |
| Electrical Characteristics .....          | 5  |
| Electrical Characteristics Diagrams ..... | 8  |
| Package Drawing .....                     | 15 |
| Testing Conditions .....                  | 16 |
| Revision History .....                    | 17 |
| Disclaimer .....                          | 17 |

## Maximum Ratings

For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.

| Parameter                                                                                                                                                                                                         | Symbol      | Value            | Unit             |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|------------------|------------------|
| Collector-emitter voltage                                                                                                                                                                                         | $V_{CE}$    | 1200             | V                |
| DC collector current, limited by $T_{vjmax}$<br>$T_C = 25^\circ\text{C}$<br>$T_C = 100^\circ\text{C}$                                                                                                             | $I_C$       | 50.0<br>25.0     | A                |
| Pulsed collector current, $t_p$ limited by $T_{vjmax}$                                                                                                                                                            | $I_{Cpuls}$ | 100.0            | A                |
| Turn off safe operating area $V_{CE} \leq 1200\text{V}$ , $T_{vj} \leq 175^\circ\text{C}$                                                                                                                         | -           | 100.0            | A                |
| Diode forward current, limited by $T_{vjmax}$<br>$T_C = 25^\circ\text{C}$<br>$T_C = 100^\circ\text{C}$                                                                                                            | $I_F$       | 25.0<br>12.5     | A                |
| Diode pulsed current, $t_p$ limited by $T_{vjmax}$                                                                                                                                                                | $I_{Fpuls}$ | 100.0            | A                |
| Gate-emitter voltage                                                                                                                                                                                              | $V_{GE}$    | $\pm 20$         | V                |
| Short circuit withstand time<br>$V_{GE} = 15.0\text{V}$ , $V_{CC} \leq 600\text{V}$<br>Allowed number of short circuits < 1000<br>Time between short circuits: $\geq 1.0\text{s}$<br>$T_{vj} = 175^\circ\text{C}$ | $t_{SC}$    | 10               | $\mu\text{s}$    |
| Power dissipation $T_C = 25^\circ\text{C}$<br>Power dissipation $T_C = 100^\circ\text{C}$                                                                                                                         | $P_{tot}$   | 326.0<br>156.0   | W                |
| Operating junction temperature                                                                                                                                                                                    | $T_{vj}$    | $-40 \dots +175$ | $^\circ\text{C}$ |
| Storage temperature                                                                                                                                                                                               | $T_{stg}$   | $-55 \dots +150$ | $^\circ\text{C}$ |
| Soldering temperature,<br>wave soldering 1.6mm (0.063in.) from case for 10s                                                                                                                                       |             | 260              | $^\circ\text{C}$ |
| Mounting torque, M3 screw<br>Maximum of mounting processes: 3                                                                                                                                                     | $M$         | 0.6              | Nm               |

## Thermal Resistance

| Parameter                                    | Symbol        | Conditions | Max. Value | Unit |
|----------------------------------------------|---------------|------------|------------|------|
| <b>Characteristic</b>                        |               |            |            |      |
| IGBT thermal resistance,<br>junction - case  | $R_{th(j-c)}$ |            | 0.46       | K/W  |
| Diode thermal resistance,<br>junction - case | $R_{th(j-c)}$ |            | 1.49       | K/W  |
| Thermal resistance<br>junction - ambient     | $R_{th(j-a)}$ |            | 40         | K/W  |

**Electrical Characteristic, at  $T_{vj} = 25^{\circ}\text{C}$ , unless otherwise specified**

| Parameter                            | Symbol        | Conditions                                                                                                    | Value       |                      |                 | Unit    |
|--------------------------------------|---------------|---------------------------------------------------------------------------------------------------------------|-------------|----------------------|-----------------|---------|
|                                      |               |                                                                                                               | min.        | typ.                 | max.            |         |
| Static Characteristic                |               |                                                                                                               |             |                      |                 |         |
| Collector-emitter breakdown voltage  | $V_{(BR)CES}$ | $V_{GE} = 0V, I_C = 0.50mA$                                                                                   | 1200        | -                    | -               | V       |
| Collector-emitter saturation voltage | $V_{CEsat}$   | $V_{GE} = 15.0V, I_C = 25.0A$<br>$T_{vj} = 25^{\circ}C$<br>$T_{vj} = 125^{\circ}C$<br>$T_{vj} = 175^{\circ}C$ | -<br>-<br>- | 2.05<br>2.50<br>2.70 | 2.40<br>-<br>-  | V       |
| Diode forward voltage                | $V_F$         | $V_{GE} = 0V, I_F = 12.5A$<br>$T_{vj} = 25^{\circ}C$<br>$T_{vj} = 175^{\circ}C$                               | -<br>-      | 1.80<br>1.85         | 2.35<br>-       | V       |
| Diode forward voltage                | $V_F$         | $V_{GE} = 0V, I_F = 25.0A$<br>$T_{vj} = 25^{\circ}C$<br>$T_{vj} = 125^{\circ}C$<br>$T_{vj} = 175^{\circ}C$    | -<br>-<br>- | 2.40<br>2.60<br>2.60 | 3.05<br>-<br>-  | V       |
| Gate-emitter threshold voltage       | $V_{GE(th)}$  | $I_C = 0.85mA, V_{CE} = V_{GE}$                                                                               | 5.0         | 5.8                  | 6.5             | V       |
| Zero gate voltage collector current  | $I_{CES}$     | $V_{CE} = 1200V, V_{GE} = 0V$<br>$T_{vj} = 25^{\circ}C$<br>$T_{vj} = 175^{\circ}C$                            | -<br>-      | -<br>-               | 250.0<br>2500.0 | $\mu A$ |
| Gate-emitter leakage current         | $I_{GES}$     | $V_{CE} = 0V, V_{GE} = 20V$                                                                                   | -           | -                    | 600             | nA      |
| Transconductance                     | $g_{fs}$      | $V_{CE} = 20V, I_C = 25.0A$                                                                                   | -           | 13.0                 | -               | S       |

**Electrical Characteristic, at  $T_{vj} = 25^{\circ}\text{C}$ , unless otherwise specified**

| Parameter                                                                                               | Symbol      | Conditions                                                                              | Value |       |      | Unit |
|---------------------------------------------------------------------------------------------------------|-------------|-----------------------------------------------------------------------------------------|-------|-------|------|------|
|                                                                                                         |             |                                                                                         | min.  | typ.  | max. |      |
| Dynamic Characteristic                                                                                  |             |                                                                                         |       |       |      |      |
| Input capacitance                                                                                       | $C_{ies}$   | $V_{CE} = 25V, V_{GE} = 0V, f = 1MHz$                                                   | -     | 1430  | -    | pF   |
| Output capacitance                                                                                      | $C_{oes}$   |                                                                                         | -     | 115   | -    |      |
| Reverse transfer capacitance                                                                            | $C_{res}$   |                                                                                         | -     | 75    | -    |      |
| Gate charge                                                                                             | $Q_G$       | $V_{CC} = 960V, I_C = 25.0A,$<br>$V_{GE} = 15V$                                         | -     | 115.0 | -    | nC   |
| Internal emitter inductance<br>measured 5mm (0.197 in.) from<br>case                                    | $L_E$       |                                                                                         | -     | 13.0  | -    | nH   |
| Short circuit collector current<br>Max. 1000 short circuits<br>Time between short circuits: $\geq 1.0s$ | $I_{C(SC)}$ | $V_{GE} = 15.0V, V_{CC} \leq 600V,$<br>$t_{SC} \leq 10\mu s$<br>$T_{vj} = 175^{\circ}C$ | -     | 87    | -    | A    |

**Switching Characteristic, Inductive Load**

| Parameter                                             | Symbol              | Conditions                                                                                                                                                                                                                                                                                                                                        | Value |      |      | Unit |
|-------------------------------------------------------|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|------|------|
|                                                       |                     |                                                                                                                                                                                                                                                                                                                                                   | min.  | typ. | max. |      |
| IGBT Characteristic, at $T_{vj} = 25^{\circ}\text{C}$ |                     |                                                                                                                                                                                                                                                                                                                                                   |       |      |      |      |
| Turn-on delay time                                    | $t_{d(\text{on})}$  | $T_{vj} = 25^{\circ}\text{C}$ ,<br>$V_{CC} = 600\text{V}$ , $I_C = 25.0\text{A}$ ,<br>$V_{GE} = 0.0/15.0\text{V}$ ,<br>$R_{G(\text{on})} = 23.0\Omega$ , $R_{G(\text{off})} = 23.0\Omega$ ,<br>$L\sigma = 80\text{nH}$ , $C\sigma = 67\text{pF}$<br>$L\sigma$ , $C\sigma$ from Fig. E<br>Energy losses include “tail” and diode reverse recovery. | -     | 27   | -    | ns   |
| Rise time                                             | $t_r$               |                                                                                                                                                                                                                                                                                                                                                   | -     | 41   | -    | ns   |
| Turn-off delay time                                   | $t_{d(\text{off})}$ |                                                                                                                                                                                                                                                                                                                                                   | -     | 277  | -    | ns   |
| Fall time                                             | $t_f$               |                                                                                                                                                                                                                                                                                                                                                   | -     | 17   | -    | ns   |
| Turn-on energy                                        | $E_{\text{on}}$     |                                                                                                                                                                                                                                                                                                                                                   | -     | 1.80 | -    | mJ   |
| Turn-off energy                                       | $E_{\text{off}}$    |                                                                                                                                                                                                                                                                                                                                                   | -     | 0.85 | -    | mJ   |
| Total switching energy                                | $E_{\text{ts}}$     |                                                                                                                                                                                                                                                                                                                                                   | -     | 2.65 | -    | mJ   |

**Diode Characteristic, at  $T_{vj} = 25^{\circ}\text{C}$** 

|                                                                  |              |                                                                                                                           |   |      |   |                  |
|------------------------------------------------------------------|--------------|---------------------------------------------------------------------------------------------------------------------------|---|------|---|------------------|
| Diode reverse recovery time                                      | $t_{rr}$     | $T_{vj} = 25^{\circ}\text{C}$ ,<br>$V_R = 600\text{V}$ ,<br>$I_F = 25.0\text{A}$ ,<br>$di_F/dt = 500\text{A}/\mu\text{s}$ | - | 290  | - | ns               |
| Diode reverse recovery charge                                    | $Q_{rr}$     |                                                                                                                           | - | 1.20 | - | $\mu\text{C}$    |
| Diode peak reverse recovery current                              | $I_{rrm}$    |                                                                                                                           | - | 10.4 | - | A                |
| Diode peak rate of fall of reverse recovery current during $t_b$ | $di_{rr}/dt$ |                                                                                                                           | - | -150 | - | A/ $\mu\text{s}$ |

**Switching Characteristic, Inductive Load**

| Parameter                                              | Symbol              | Conditions                                                                                                                                                                                                                                                                                                                                         | Value |      |      | Unit |
|--------------------------------------------------------|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|------|------|
|                                                        |                     |                                                                                                                                                                                                                                                                                                                                                    | min.  | typ. | max. |      |
| IGBT Characteristic, at $T_{vj} = 175^{\circ}\text{C}$ |                     |                                                                                                                                                                                                                                                                                                                                                    |       |      |      |      |
| Turn-on delay time                                     | $t_{d(\text{on})}$  | $T_{vj} = 175^{\circ}\text{C}$ ,<br>$V_{CC} = 600\text{V}$ , $I_C = 25.0\text{A}$ ,<br>$V_{GE} = 0.0/15.0\text{V}$ ,<br>$R_{G(\text{on})} = 23.0\Omega$ , $R_{G(\text{off})} = 23.0\Omega$ ,<br>$L\sigma = 80\text{nH}$ , $C\sigma = 67\text{pF}$<br>$L\sigma$ , $C\sigma$ from Fig. E<br>Energy losses include “tail” and diode reverse recovery. | -     | 26   | -    | ns   |
| Rise time                                              | $t_r$               |                                                                                                                                                                                                                                                                                                                                                    | -     | 35   | -    | ns   |
| Turn-off delay time                                    | $t_{d(\text{off})}$ |                                                                                                                                                                                                                                                                                                                                                    | -     | 347  | -    | ns   |
| Fall time                                              | $t_f$               |                                                                                                                                                                                                                                                                                                                                                    | -     | 50   | -    | ns   |
| Turn-on energy                                         | $E_{\text{on}}$     |                                                                                                                                                                                                                                                                                                                                                    | -     | 2.60 | -    | mJ   |
| Turn-off energy                                        | $E_{\text{off}}$    |                                                                                                                                                                                                                                                                                                                                                    | -     | 1.70 | -    | mJ   |
| Total switching energy                                 | $E_{\text{ts}}$     |                                                                                                                                                                                                                                                                                                                                                    | -     | 4.30 | -    | mJ   |

**Diode Characteristic, at  $T_{vj} = 175^{\circ}\text{C}$** 

|                                                                  |              |                                                                                                                            |   |      |   |                  |
|------------------------------------------------------------------|--------------|----------------------------------------------------------------------------------------------------------------------------|---|------|---|------------------|
| Diode reverse recovery time                                      | $t_{rr}$     | $T_{vj} = 175^{\circ}\text{C}$ ,<br>$V_R = 600\text{V}$ ,<br>$I_F = 25.0\text{A}$ ,<br>$di_F/dt = 500\text{A}/\mu\text{s}$ | - | 505  | - | ns               |
| Diode reverse recovery charge                                    | $Q_{rr}$     |                                                                                                                            | - | 2.75 | - | $\mu\text{C}$    |
| Diode peak reverse recovery current                              | $I_{rrm}$    |                                                                                                                            | - | 12.8 | - | A                |
| Diode peak rate of fall of reverse recovery current during $t_b$ | $di_{rr}/dt$ |                                                                                                                            | - | -85  | - | A/ $\mu\text{s}$ |




Figure 1. **Collector current as a function of switching frequency**  
( $T_j \leq 175^\circ\text{C}$ ,  $D=0.5$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $r_G=23\Omega$ )




Figure 2. **Forward bias safe operating area**  
( $D=0$ ,  $T_C=25^\circ\text{C}$ ,  $T_j \leq 175^\circ\text{C}$ ;  $V_{GE}=15\text{V}$ )




Figure 3. **Power dissipation as a function of case temperature**  
( $T_j \leq 175^\circ\text{C}$ )




Figure 4. **Collector current as a function of case temperature**  
( $V_{GE} \geq 15\text{V}$ ,  $T_j \leq 175^\circ\text{C}$ )




Figure 5. **Typical output characteristic**  
( $T_j=25^{\circ}\text{C}$ )




Figure 6. **Typical output characteristic**  
( $T_j=175^{\circ}\text{C}$ )




Figure 7. **Typical transfer characteristic**  
( $V_{CE}=20\text{V}$ )




Figure 8. **Typical collector-emitter saturation voltage as a function of junction temperature**  
( $V_{GE}=15\text{V}$ )




Figure 9. **Typical switching times as a function of collector current**  
(ind. load,  $T_J=175^{\circ}\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $r_G=23\Omega$ , test circuit in Fig. E)




Figure 10. **Typical switching times as a function of gate resistor**  
(ind. load,  $T_J=175^{\circ}\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=25\text{A}$ , test circuit in Fig. E)




Figure 11. **Typical switching times as a function of junction temperature**  
(ind. load,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=25\text{A}$ ,  $r_G=23\Omega$ , test circuit in Fig. E)




Figure 12. **Gate-emitter threshold voltage as a function of junction temperature**  
( $I_C=0.85\text{mA}$ )




Figure 13. **Typical switching energy losses as a function of collector current**  
(ind. load,  $T_J=175^\circ\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $r_G=23\Omega$ , test circuit in Fig. E)




Figure 14. **Typical switching energy losses as a function of gate resistor**  
(ind. load,  $T_J=175^\circ\text{C}$ ,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=25\text{A}$ , test circuit in Fig. E)




Figure 15. **Typical switching energy losses as a function of junction temperature**  
(ind load,  $V_{CE}=600\text{V}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=25\text{A}$ ,  $r_G=23\Omega$ , test circuit in Fig. E)




Figure 16. **Typical switching energy losses as a function of collector emitter voltage**  
(ind. load,  $T_J=175^\circ\text{C}$ ,  $V_{GE}=15/0\text{V}$ ,  $I_C=25\text{A}$ ,  $r_G=23\Omega$ , test circuit in Fig. E)




Figure 17. **Typical gate charge**  
( $I_C=25A$ )




Figure 18. **Typical capacitance as a function of collector-emitter voltage**  
( $V_{GE}=0V$ ,  $f=1MHz$ )




Figure 19. **Typical short circuit collector current as a function of gate-emitter voltage**  
( $V_{CE} \leq 600V$ , start at  $T_j=25^\circ C$ )




Figure 20. **Short circuit withstand time as a function of gate-emitter voltage**  
( $V_{CE} \leq 600V$ , start at  $T_j \leq 150^\circ C$ )




Figure 21. IGBT transient thermal impedance ( $D=t_p/T$ )




Figure 22. Diode transient thermal impedance as a function of pulse width ( $D=t_p/T$ )




Figure 23. Typical reverse recovery time as a function of diode current slope ( $V_R=600V$ )




Figure 24. Typical reverse recovery charge as a function of diode current slope ( $V_R=600V$ )




Figure 25. **Typical reverse recovery current as a function of diode current slope**  
( $V_R=600V$ )




Figure 26. **Typical diode peak rate of fall of reverse recovery current as a function of diode current slope**  
( $V_R=600V$ )




Figure 27. **Typical diode forward current as a function of forward voltage**






Figure 28. **Typical diode forward voltage as a function of junction temperature**

## PG-TO247-3



| DIM | MILLIMETERS |       | INCHES      |       |
|-----|-------------|-------|-------------|-------|
|     | MIN         | MAX   | MIN         | MAX   |
| A   | 4.83        | 5.21  | 0.190       | 0.205 |
| A1  | 2.27        | 2.54  | 0.089       | 0.100 |
| A2  | 1.85        | 2.16  | 0.073       | 0.085 |
| b   | 1.07        | 1.33  | 0.042       | 0.052 |
| b1  | 1.90        | 2.41  | 0.075       | 0.095 |
| b2  | 1.90        | 2.16  | 0.075       | 0.085 |
| b3  | 2.87        | 3.38  | 0.113       | 0.133 |
| b4  | 2.87        | 3.13  | 0.113       | 0.123 |
| c   | 0.55        | 0.68  | 0.022       | 0.027 |
| D   | 20.80       | 21.10 | 0.819       | 0.831 |
| D1  | 16.25       | 17.65 | 0.640       | 0.695 |
| D2  | 0.95        | 1.35  | 0.037       | 0.053 |
| E   | 15.70       | 16.13 | 0.618       | 0.635 |
| E1  | 13.10       | 14.15 | 0.516       | 0.557 |
| E2  | 3.68        | 5.10  | 0.145       | 0.201 |
| E3  | 1.00        | 2.60  | 0.039       | 0.102 |
| e   | 5.44 (BSC)  |       | 0.214 (BSC) |       |
| N   | 3           |       | 3           |       |
| L   | 19.80       | 20.32 | 0.780       | 0.800 |
| L1  | 4.10        | 4.47  | 0.161       | 0.176 |
| ØP  | 3.50        | 3.70  | 0.138       | 0.146 |
| Q   | 5.49        | 6.00  | 0.216       | 0.236 |
| S   | 6.04        | 6.30  | 0.238       | 0.248 |

|                                                                                                                     |
|---------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NO.</b><br>Z8B00003327                                                                                  |
| <b>SCALE</b><br>0 5 7.5mm                                                                                           |
| <b>EUROPEAN PROJECTION</b><br> |
| <b>ISSUE DATE</b><br>09-07-2010                                                                                     |
| <b>REVISION</b><br>05                                                                                               |




Figure A. Definition of switching times




Figure B. Definition of switching losses




Figure C. Definition of diode switching characteristics





Figure D. Thermal equivalent circuit


Figure E. Dynamic test circuit  
Parasitic inductance  $L_{\sigma}$ ,  
parasitic capacitor  $C_{\sigma}$ ,  
relief capacitor  $C_r$ ,  
(only for ZVT switching)

## Revision History

IKW25N120H3

Revision: 2014-12-01, Rev. 2.1

## Previous Revision

| Revision | Date       | Subjects (major changes since last revision) |
|----------|------------|----------------------------------------------|
| 1.1      | 2009-11-27 | -                                            |
| 1.2      | 2010-02-10 | -                                            |
| 2.1      | 2014-12-01 | Final data sheet                             |

## We Listen to Your Comments

Any information within this document that you feel is wrong, unclear or missing at all?

Your feedback will help us to continuously improve the quality of this document.

Please send your proposal (including a reference to this document) to: [erratum@infineon.com](mailto:erratum@infineon.com)

## Published by

Infineon Technologies AG

81726 Munich, Germany

81726 München, Germany

© 2014 Infineon Technologies AG

All Rights Reserved.

## Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics.

With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

## Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office ([www.infineon.com](http://www.infineon.com)).

## Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.

The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.