




+ TERMINALS & SPLICES

QUICK DISCONNECTS



✓ Active

TE CONNECTIVITY (TE)

PIGGY BACK FASTON RECEP.

FASTON | 250

150645-9

TE Internal Number: 150645-9

EU RoHS Compliant

EU ELV Compliant

Terminal Type Tab & Receptacle

Wire Size (AWG) 18 – 14

Mating Tab Width 6.35 mm [.25 in]

Mating Tab Thickness .81 mm [.032 in]

Fully Insulated Yes

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

WIRE TERMINAL 250 SERIES FASTON PIGGY BACK

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

FASTON Piggyback Receptacles

PDF

English

Product Specification

.110,.187 & 250 Series FASTON Terminals

TIF

English

.110,.187 & 250 Series FASTON Terminals

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

FASTON Yes

Disconnect Type Quick Disconnect

Insertion Force Normal

Insulated No

Wire Stop No

Wire/Cable Composition Stranded

Configuration Features

Connection Capacity Single

Body Features

Fully Insulated Yes

Plating Material Unplated

Contact Features

Terminal Type Tab & Receptacle

Terminal Orientation Piggyback

Barrel Type Open

Crimp Type F-Crimp

Dimensions

Wire Size (AWG) 18 – 14
Mating Tab Width 6.35 mm [.25 in]
Mating Tab Thickness .81 mm [.032 in]
Accepts Wire Insulation Diameter Range 3 – 4.29 mm [.118 – .169 in]
Overall Length 23.11 mm [.91 in]

Industry Standards

CSA Certified Yes
UL Rating Listed

Packaging Features

Packaging Method Reel
Packaging Quantity 1500

Other

Line Premier

PRODUCT COMPLIANCE



Statement of Compliance

[**Statement of Compliance**](#)

PDF
