





LOC	DIST	REVISIONS					
CM	54	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	REVISED PER ECO-12-016930	050CT12	KH	SM



.065	1.65	—	—
.063	1.60	—	—
.060	1.52	2.184	55.47
.045	1.14	.475	12.07
.030	0.76	.468	11.89
.022	0.56	.430	10.92
.018	0.46	.390	9.91
.015	0.38	.250	6.35
.012	0.30	.156	3.96
.010	0.25	.140	3.56
.008	0.20	.125	3.18
.005	0.13	.100	2.54
.003	0.08	.078	1.98
.001	0.03	.070	1.78
IN	MM	IN	MM

CONVERSION TABLE

RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

643377-2 SHOWN

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 12-11-92 N. GANNON CHK 12-11-92 R. SWING APD 1-11-93 R. SPEER PRODUCT SPEC — APPLICATION SPEC —		OMITTED  TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		NAME MTA-156 HEADLE ASSEMBLY, PLAIN, RIGHT ANGLE, .045 SQUARE POST, TIN PLATED, 14 POSITION, OMITTED POST	
MATERIAL 		FINISH 		WEIGHT — SIZE A1	
CUSTUMER DRAWING		GAGE CODE 00779		DRAWING NO C-643377	
		SCALE 5:1		SHEET 1 of 1	
		REV —			