


MODEL 38
10 mm Single-Turn Trimmer
Dust Proof
Carbon Element
Low TCR
RoHS Compliant

New Product



STYLES AVAILABLE

Top Adjust	38P
Side Adjust	38W

ELECTRICAL¹

Resistance Range	100 to 1,000,000 Ohms
Standard Resistance Tolerance	± 30%, (±20% and ±10% available)
Input Voltage, Maximum	200 Vdc
Power rating, Watts	Linear :0.15W, others : 0.07W, at 50 °C
End Resistance, Maximum	2 ohms or 0.5% whichever is greater
Actual Electrical Travel	220° ±20°
Insulation Resistance, Minimum	100 Megohms
Resolution	Essentially infinite
Contact Resistance Variation	5% Max.
Temperature Coefficient of Resistance	±500 ppm/°C

MECHANICAL


Torque, Maximum	1.5 in - oz.
Wiper Position	Approx. 50%

ENVIRONMENTAL

Operating Temperature Range	-25 °C to +70 °C
Rotational Life, 500 Cycles	±3% ΔR
Load Life, 0.15W, 100 Hours, 50°C	±5% ΔR
Resistance to Solder Heat	260°C for 3 sec.
Aqueous cleaning not recommended	

¹ Specifications subject to change without notice.


ORDERING INFORMATION²




² Contact our customer service for custom designs and features.

MODEL 38

Taper Options



CIRCUIT DIAGRAM




STANDARD RESISTANCE VALUES AND MARKING


100	500	1K	2K	5K	10K	20K	50K	100K	200K	500K	1MEG
-----	-----	----	----	----	-----	-----	-----	------	------	------	------

OUTLINE DRAWING³

Model 38P (Top Adjust)



Model 38W (Side Adjust)



³ Dimensions are in millimeters, Tolerances are ± 0.25 mm unless otherwise stated.

BI Technologies Corporation
4200 Bonita Place, Fullerton, CA 92835 USA

Phone: 714 447 2345 Website: www.bitechnologies.com

April 16, 2007

page 3 of 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

[38PKABR10KLF30](#) [38WMBBR10KLF30](#) [38PKACR5KLF20](#) [38PKACR5KLF10](#) [38PKAAR1MEGLF10](#)
[38PLAAR100LF20](#) [38PKAAR1MEGLF20](#) [38PKABR500KLF20](#) [38PKAAR50KLF20](#) [38PKACR200KLF20](#)
[38PKAAR50KLF30](#) [38PKACR20KLF20](#) [38PKACR10KLF20](#) [38PKABR5KLF20](#) [38PKAAR500KLF10](#)
[38PLAAR100KLF20](#) [38PKAAR100KLF20](#) [38PLAAR50KLF10](#) [38PKABR500LF20](#) [38PKAAR20KLF30](#)
[38PKAAR10KLF30](#) [38PKAAR20KLF20](#) [38PKABR100KLF10](#) [38PKACR50KLF20](#) [38PLAAR10KLF10](#)
[38PKACR500KLF30](#) [38PLAAR2KLF20](#) [38PKABR100LF20](#) [38PKAAR500LF10](#) [38PKAAR5KLF30](#) [38PLAAR20KLF10](#)
[38PLAAR500LF20](#) [38PKAAR100LF10](#) [38PKAAR200KLF30](#) [38PKABR100LF30](#) [38PKAAR2KLF20](#)
[38WLABR10KLF10](#) [38WMAAR10KLF30](#) [38WLB BR1KLF30](#) [38WMAAR100KLF30](#) [38WKBAR50KLF10](#)
[38PKABR10KLF10](#) [38PLACR5KLF30](#) [38WMBCR500LF20](#) [38PLAAR200KLF20](#) [38WMACR1MEGLF30](#)
[38WMABR50KLF20](#) [38PMACR200KLF10](#) [38WLB CR10KLF10](#) [38PKABR200KLF20](#) [38WMBAR20KLF30](#)
[38WMBAR10KLF30](#) [38WMABR20KLF20](#) [38WMAAR1MEGLF20](#) [38WMBAR1MEGLF20](#) [38WLB BR10KLF10](#)
[38PLABR2KLF10](#) [38WKBCR500KLF20](#) [38PMACR500LF10](#) [38PMAAR10KLF30](#) [38WLACR2KLF20](#)
[38WMBBR100LF20](#) [38WLB BR20KLF10](#) [38PMACR2KLF30](#) [38WKAAR500KLF10](#) [38PLACR500LF30](#)
[38PLACR100LF30](#) [38PLACR20KLF10](#) [38WLACR500LF10](#) [38WLACR100LF10](#) [38WLB CR500LF30](#)
[38PMACR5KLF10](#) [38WMBAR50KLF30](#) [38WMBBR500KLF20](#) [38WLB BR500LF30](#) [38WMABR200KLF30](#)
[38WLB BR1MEGLF10](#) [38WMABR500LF30](#) [38PKABR200KLF30](#) [38PMAAR10KLF20](#) [38WLAAR20KLF30](#)
[38WMBCR100KLF30](#) [38PKAAR1KLF20](#) [38WLB CR100LF30](#) [38WMBBR100KLF20](#) [38WMBBR500KLF30](#)
[38PLABR100LF20](#) [38PLABR500LF20](#) [38PLABR100LF30](#) [38PLAAR5KLF30](#) [38WMBBR100KLF30](#)
[38WLB CR200KLF30](#) [38WKABR100KLF10](#) [38PMACR100LF20](#) [38WKBCR50KLF10](#) [38WLB BR200KLF10](#)
[38WMABR100LF30](#) [38WKACR5KLF10](#) [38PLAAR20KLF30](#) [38WMABR1MEGLF30](#)