







LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AG	00	B1		REVISED PER ECO-11-005033	26MAR11	RK HMR



- △ HOUSING-MATERIAL : LIQUID-CRYSTAL-POLYMER.
- △ CONTACT-MATERIAL : PHOS. BRONZE.
- △ LATCH-MATERIAL : STAINLESS STEEL
- △ CONTACT-PLATE: 0.00508[.000200] MIN. MATTE TIN OVER 0.00127 [.000050] MIN NICKEL.
- 5. IN ADDITION TO THOSE RECOMMENDED "SIMM" P.C. BOARD DIMENSIONS AND TOLERANCES SHOWN, ALL JEDEC SPECIFICATIONS APPLY AS SHOWN ON MO-116, ISSUE A.
- 6. RECOMMENDED MATING S.I.M.M. TAB METALLURGY:
BASE METAL-COPPER. PLATING TO BE 0.00762[.000300] MIN TIN/LEAD OVER 0.00127[.000050] MIN NICKEL.
- △ 'S' IDENTIFIER LOCATED APPROXIMATELY AS SHOWN.
- △ 8 DATE CODE INFORMATION (YEAR WEEK), LOCATED APROXIMATELY AS SHOWN ON OPPOSITE SIDE ONLY.



118.11[4.650]	111.35[4.384]	60.96[2.400]	49.53[1.950]	125.48[4.940]	105.41[4.150]	80	5822134-4
107.95[4.250]	101.19[3.984]	55.88[2.200]	44.45[1.750]	115.32[4.540]	95.25[3.750]	72	5822134-3
F	E	D	C	B	A	NO. OF POS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER 07JAN05	 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK M.YEOMANS 07JAN05				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.YEOMANS 07JAN05	NAME			
		PRODUCT SPEC		CONNECTOR, MICRO-EDGE, .050, LP, TIN PL, W/METAL LATCH		
		APPLICATION SPEC				
		WEIGHT —				
MATERIAL		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
		A1		00779	5822134	—
FINISH		CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1
						REV B1