

MOMENTARY ACTION, SEALED SUB-SUBMINIATURE PUSHBUTTON SNAP-ACTION SWITCHES

The P7 series incorporates OTTO's patented double break design in a significantly smaller package than the P1 series. These subminiature switches embrace today's technology requirements by allowing for a large number of switches to fit within a faceplate.

The long life snap-action design is protected from the environment by a silicon rubber boot, operating on a patented "rolling sleeve" principle that gives long sealed life and smooth operation.

The P7 series is designed to meet the requirements of MIL-PRF-8805 including low level switching (10mA @ 30mV) with power switching up to 5 amps at 28VDC as well.

A variety of mounting styles are offered to best match the application. The P7-1, P7-2, P7-7 and P7-8 case styles feature a swaged bushing shape to allow press fit installation in aircraft flight control and hand grips and similar applications. The other styles feature threaded bushing mounting. The P7-3 case style has a front panel bezel, while the P7-5 and P7-6 have conventional bushings for rear panel mounted installations. Silver or black bezels are standard. Other colors available on special order.

Pushbuttons are available in a choice of nine colors. Excellent tactile feedback assures the operator that contact transfer has been made.

A choice of MIL-SPEC and commercial versions of these switches are offered: Moistureproof and dusttight to IP64 and MIL-PRF-8805 Design 2 or watertight to IP68S and to MIL-PRF-8805 Design 3.

Features:

- Low level switching capability
- Less than 25mΩ contact resistance
- High contact pressure
- 6 circuit variations
- Positive tactile feedback
- Variety of mounting styles
- Qualified to MIL-PRF-8805/110
- Moistureproof & dusttight to IP64 & MIL-PRF-8805 Design 2 or watertight to IP68S & MIL-PRF-8805 Design 3
- RoHS/WEEE/Reach compliant



Standard Characteristics/Ratings:

ELECTRICAL RATINGS:		Sea Level @ 28VDC			50,000 feet @ 28VDC		
Load	Circuits:	1 & 2	3-5	6	1 & 2	3-5	6
Resistive		5A	2.5A	4A	5A	2.5A	4A
Inductive		3A	1.5A	2A	3A	1.5A	2A
Lamp		1A	0.5A	N/A	N/A	N/A	N/A
Motor		3A	1.5A	N/A	N/A	N/A	N/A
DVV		1050Vrms			400Vrms		
Center Contact					3A max		
Low Level					10mA @ 30mV		
Electrical Life:		25,000 cycles					
Mechanical Life:		1,000,000 cycles					
Seal:		IP64 and MIL-PRF-8805 Design 2 or IP68S and MIL-PRF-8805 Design 3					
Operating Temp Range:		-55°C to +85°C					
Operating Force:		1.7 +/- 0.5 lb.					
Total Travel:		0.080 inches max					
Overtravel:		0.010 inches min					
MATERIALS:							
Case:		Anodized aluminum alloy					
Button:		Thermoplastic					
Terminals:		Brass with gold over silver					
Terminal Hardware:		None provided					
Mounting Hardware:		Hex nut, lockwasher and panel gasket when applicable					

SEALED AGAINST DUST & MOISTURE, LOW LEVEL SWITCHING OPTION


P7-1 Series Case Style 1 Press Fit Mount Also available with PC terminals.		P7-6 Series Case Style 6 15/32" Threaded Bushing Also available with PC pins.																																																																																												
P7-2 Series Case Style 2 Press Fit Mount Also available with PC pins.		P7-7 Series Case Style 7 Press Fit Mount Also available with PC pins.																																																																																												
P7-3 Series Case Style 3 Bezel/Threaded Bushing Also available with PC pins.		P7-8 Series Case Style 8 Press Fit Mount Guarded Button Also available with PC pins.																																																																																												
P7-5 Series Case Style 5 1/4" Threaded Bushing Also available with PC pins.		Terminal Style "A" & "B" Standard																																																																																												
PC Pin Mounting Pattern (As viewed from switch bottom. See above drawings for terminal identification.)		P7 PART NUMBER CODE <table><tr><td>P7</td><td>-</td><td>X</td><td>X</td><td>X</td><td>X</td><td>X</td></tr><tr><td>Case Style</td><td></td><td>Terminal Style/Construction Grade</td><td></td><td>Circuit Form</td><td>Contact Rating</td><td>Bezel Color/Button Dia.</td></tr><tr><td>1. Style 1</td><td></td><td>A. Solder/Commercial</td><td></td><td>1. N.O.</td><td>1. Std.</td><td>1. Clear/Std.</td></tr><tr><td>2. Style 2</td><td></td><td>B. Solder/Watertight</td><td></td><td>2. N.C.</td><td>2. Low Level</td><td>2. Black/Std.</td></tr><tr><td>3. Style 3</td><td></td><td>Commercial</td><td></td><td>3. N.C. 3 Terminal</td><td></td><td>3. Clear/0.312 ①</td></tr><tr><td>5. Style 5</td><td></td><td>1. Solder/Military/Short</td><td></td><td>4. N.O. 3 Terminal</td><td></td><td>4. Black/0.312 ①</td></tr><tr><td>6. Style 6</td><td></td><td>2. Solder/Commercial/Short</td><td></td><td>5. 5 Terminal</td><td></td><td></td></tr><tr><td>7. Style 7</td><td></td><td>3. Solder/Mil. Watertight/Short</td><td></td><td>6. 2 Circuit</td><td></td><td></td></tr><tr><td>8. Style 8</td><td></td><td>4. PC Pin/Commercial</td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>5. PC Pin/Military</td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>6. PC Pin/Mil. Watertight</td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>7. Solder/Com. Watertight/Short</td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>8. PC Pin/Com. Watertight</td><td></td><td></td><td></td><td></td></tr></table>		P7	-	X	X	X	X	X	Case Style		Terminal Style/Construction Grade		Circuit Form	Contact Rating	Bezel Color/Button Dia.	1. Style 1		A. Solder/Commercial		1. N.O.	1. Std.	1. Clear/Std.	2. Style 2		B. Solder/Watertight		2. N.C.	2. Low Level	2. Black/Std.	3. Style 3		Commercial		3. N.C. 3 Terminal		3. Clear/0.312 ①	5. Style 5		1. Solder/Military/Short		4. N.O. 3 Terminal		4. Black/0.312 ①	6. Style 6		2. Solder/Commercial/Short		5. 5 Terminal			7. Style 7		3. Solder/Mil. Watertight/Short		6. 2 Circuit			8. Style 8		4. PC Pin/Commercial							5. PC Pin/Military							6. PC Pin/Mil. Watertight							7. Solder/Com. Watertight/Short							8. PC Pin/Com. Watertight				
P7	-	X	X	X	X	X																																																																																								
Case Style		Terminal Style/Construction Grade		Circuit Form	Contact Rating	Bezel Color/Button Dia.																																																																																								
1. Style 1		A. Solder/Commercial		1. N.O.	1. Std.	1. Clear/Std.																																																																																								
2. Style 2		B. Solder/Watertight		2. N.C.	2. Low Level	2. Black/Std.																																																																																								
3. Style 3		Commercial		3. N.C. 3 Terminal		3. Clear/0.312 ①																																																																																								
5. Style 5		1. Solder/Military/Short		4. N.O. 3 Terminal		4. Black/0.312 ①																																																																																								
6. Style 6		2. Solder/Commercial/Short		5. 5 Terminal																																																																																										
7. Style 7		3. Solder/Mil. Watertight/Short		6. 2 Circuit																																																																																										
8. Style 8		4. PC Pin/Commercial																																																																																												
		5. PC Pin/Military																																																																																												
		6. PC Pin/Mil. Watertight																																																																																												
		7. Solder/Com. Watertight/Short																																																																																												
		8. PC Pin/Com. Watertight																																																																																												

① Not available with Case Styles 1, 2 & 5.

EXAMPLES OF CUSTOMIZED P7 SEALED PUSHBUTTONS



Actuation	OTTO Part Number
Momentary	P7-500001




Color	OTTO Part Number
Red	P7-900001
Black	P7-900002
White	P7-900009



Part Number: P7-500018

Mini Pushbutton, Shrouded

Actuation	OTTO Part Number
Momentary	P7-900196



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

OTTO:

[P7-3B6121](#) [P7-3B6122](#) [P7-5B6121](#) [P7-5B6122](#) [P7-6B6121](#) [P7-6B6122](#) [P7-511122](#) [P7-561128](#) [P7-351122](#) [P7-656122](#) [P7-536122](#) [P7-3B6142](#) [P7-112221](#) [P7-821112](#) [P7-821126](#) [P7-821129](#) [P7-626122](#) [P7-656221](#) [P7-712122](#) [P7-734122](#) [P7-751122](#) [P7-814129](#) [P7-551222](#) [P7-555111](#) [P7-571225](#) [P7-5B1121](#) [P7-5B1122](#) [P7-616242](#) [P7-8A1129](#) [P7-811222](#) [P7-511125](#) [P7-515126](#) [P7-536111](#) [P7-381244](#) [P7-3A1128](#) [P7-3A1242](#) [P7-824126](#) [P7-836229](#) [P7-8A1121](#) [P7-332124](#) [P7-371229](#) [P7-371244](#) [P7-376121](#) [P7-376225](#) [P7-381241](#) [P7-316121](#) [P7-321141](#) [P7-326146](#) [P7-326244](#) [P7-331149](#) [P7-331249](#) [P7-534111](#) [P7-311125](#) [P7-311126](#) [P7-311141](#) [P7-311148](#) [P7-314221](#) [P7-5A1121](#) [P7-516126](#) [P7-521129](#) [P7-521211](#) [P7-511111](#) [P7-534121](#) [P7-551221](#) [P7-551229](#) [P7-576121](#) [P7-831128](#) [P7-876221](#) [P7-3B6123](#) [P7-3B6225](#) [P7-7A1142](#) [P7-811122](#) [P7-811226](#) [P7-814121](#) [P7-816119](#) [P7-816228](#) [P7-3B1124](#) [P7-3B1149](#) [P7-3B6242](#) [P7-515128](#) [P7-515221](#) [P7-522119](#) [P7-741123](#) [P7-746122](#) [P7-371243](#) [P7-3A1142](#) [P7-3A1144](#) [P7-611229](#) [P7-621221](#) [P7-631146](#) [P7-632122](#) [P7-651122](#) [P7-722122](#) [P7-1B1224](#) [P7-231221](#) [P7-236222](#) [P7-256221](#) [P7-2B1222](#) [P7-611226](#) [P7-131122](#)