




	10	9	8	7	6	5	4	3	2	1	
F	TIN/LEAD OPTION										F

	10	9	8	7	6	5	4	3	2	1	
F	TIN OPTION										F
E											E

A

tb_frame_A3_P_AM_T
Rev. D 2004/06/28

	10	9	8	7	6	5	4	3	2	1															
F	TIN OPTION										F														
E	P.C.TAIL DIMENSION 'C' = 3.00												P.C.TAIL DIMENSION 'C' = 1.91												E
	CKT SIZE	DIM 'A'	DIM 'B'	PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6											
				ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.											
D	04	(4.19)	(2.00)		79107-7001		79107-7051	X	79107-7126		79107-7201		79107-7251	X	79107-7326	D									
	06	(6.19)	(4.00)		79107-7002		79107-7052	X	79107-7127		79107-7202		79107-7252	X	79107-7327										
	08	(8.19)	(6.00)		79107-7003		79107-7053	X	79107-7128		79107-7203	X	79107-7253	X	79107-7328										
	10	(10.19)	(8.00)		79107-7004		79107-7054	X	79107-7129		79107-7204		79107-7254	X	79107-7329										
	12	(12.19)	(10.00)		79107-7005		79107-7055		79107-7130		79107-7205		79107-7255		79107-7330										
	14	(14.19)	(12.00)		79107-7006		79107-7056	X	79107-7131		79107-7206		79107-7256	X	79107-7331										
	16	(16.19)	(14.00)		79107-7007		79107-7057	X	79107-7132		79107-7207	X	79107-7257	X	79107-7332										
	18	(18.19)	(16.00)		79107-7008		79107-7058	X	79107-7133		79107-7208		79107-7258	X	79107-7333										
	20	(20.19)	(18.00)		79107-7009		79107-7059	X	79107-7134		79107-7209		79107-7259	X	79107-7334										
	22	(22.19)	(20.00)		79107-7010		79107-7060	X	79107-7135		79107-7210		79107-7260	X	79107-7335										
C	24	(24.19)	(22.00)		79107-7011		79107-7061	X	79107-7136		79107-7211		79107-7261	X	79107-7336	C									
	26	(26.19)	(24.00)		79107-7012		79107-7062	X	79107-7137		79107-7212		79107-7262	X	79107-7337										
	28	(28.19)	(26.00)		79107-7013		79107-7063	X	79107-7138		79107-7213		79107-7263	X	79107-7338										
	30	(30.19)	(28.00)		79107-7014		79107-7064	X	79107-7139		79107-7214		79107-7264	X	79107-7339										
	32	(32.19)	(30.00)		79107-7015		79107-7065	X	79107-7140		79107-7215		79107-7265	X	79107-7340										
	34	(34.19)	(32.00)		79107-7016		79107-7066	X	79107-7141		79107-7216		79107-7266	X	79107-7341										
	36	(36.19)	(34.00)		79107-7017		79107-7067	X	79107-7142		79107-7217		79107-7267	X	79107-7342										
	38	(38.19)	(36.00)		79107-7018		79107-7068	X	79107-7143		79107-7218		79107-7268	X	79107-7343										
	40	(40.19)	(38.00)		79107-7019		79107-7069	X	79107-7144		79107-7219		79107-7269	X	79107-7344										
	42	(42.19)	(40.00)		79107-7020		79107-7070	X	79107-7145		79107-7220		79107-7270	X	79107-7345										
B	44	(44.19)	(42.00)		79107-7021		79107-7071	X	79107-7146		79107-7221		79107-7271	X	79107-7346	B									
	46	(46.19)	(44.00)		79107-7022		79107-7072	X	79107-7147		79107-7222		79107-7272	X	79107-7347										
	48	(48.19)	(46.00)		79107-7023		79107-7073	X	79107-7148		79107-7223		79107-7273	X	79107-7348										
	50	(50.19)	(48.00)		79107-7024		79107-7074	X	79107-7149		79107-7224		79107-7274	X	79107-7349										
	"X" - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.																								
A																	A								
tb_frame_A3_P_ME_T Rev. D 2004/04/02																9	8	7	6	5	4	3	2	1	

CHANGE TOLERANCES

EC NO: S2006-0225

DRWN:LOI/AO 2005/09/09

CHKD:80KOK 2005/09/09

APPR:PTL/IM 2005/09/10

REV

F2

DESCRIPTION

QUALITY SYMBOLS

▽=0

▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.25	± ---
1 PLACE	± 0.38	± ---
ANGULAR ±1/2°		

DRAFT WHERE APPLICABLE

MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY	DATE
AAB	1989/05/15
CHECKED BY	DATE
MJM	1989/05/15
APPROVED BY	DATE
WAZ	1989/05/15
MATERIAL NO.	
SIZE	A3

SCALE

NTS

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

SALES DRAWING

2MM DUAL ROW

VERTICAL RECEPTACLE T/H

MOLEX

MOLEX INCORPORATED

DOCUMENT NO.

SDA-79107-****

SHEET NO.

3 OF 4

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MOLDED VOID OPTION ASSEMBLIES WITHOUT PEGS

	ASSEMBLY		VOID LOCATION(S) SEE SHEET 1 FOR CONVENTION		PLATING OPTION	DIM. "A"	DIM. "B"	P.C. TAIL DIM. "C"	PLATING OPTION
CKT. SIZE	ITEM NO.		ROW	CKT. NO.(s)					
24		79107-5001			2	(24.19)	(22.00)	(3.00)	TIN/LEAD
			ROW B	6					
10		79107-5002			2	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5003			2	(26.19)	(24.00)	(3.00)	
			ROW B	5					
24		79107-5101			5	(24.19)	(22.00)	(3.00)	TIN
			ROW B	6					
10		79107-5102			5	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5103			5	(26.19)	(24.00)	(3.00)	
			ROW B	5					

"X" - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.

NOTES

1. TERMINALS WILL BE PRESENT IN VOIDED LOCATIONS HOWEVER, PIN WINDOWS WILL BE CLOSED.
2. VOIDS CANNOT BE PRESENT IN BOTH ROWS ON A CONNECTOR.

CHANGE TOLERANCES EC NO: S2006-0225 DRWN:YLO/AO 2005/09/09 CHKD:BO/KOK 2005/09/09 APPR:PTL/IM 2005/09/10	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY AAB	DATE 1989/05/15	TITLE SALES DRAWING 2MM DUAL ROW VERTICAL RECEPTACLE T/H			
			4 PLACES ± ---	± ---	CHECKED BY MJM	DATE 1989/05/15				
			3 PLACES ± ---	± ---	APPROVED BY WAZ	DATE 1989/05/15	MOLEX INCORPORATED			
			2 PLACES ± 0.25	± ---	DOCUMENT NO. SDA-79107-****					
			1 PLACE ± 0.38	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
ANGULAR ±1/2°										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
F2	REV	SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						