


# G2E133 Series

Centrifugal Blower

Ø 133mm



■ AC single inlet, forward curved centrifugal blower. Via a bracket, the integrated external-rotor motor is mounted on one side of the housing.

■ Housing and impeller of galvanised sheet-steel. Forward curved impellers are directly press-fitted onto the rotor of the external-rotor motor.

■ Direction of rotation is CW as seen from suction side. Insulation class "B".

■ Maintenance-free ball bearings.

■ UL, CSA, VDE approvals on some models, please contact application engineering.

Part  
Number

Curve

CFM  
@ 0

VAC

Hertz

Power  
(W)

dBA

Max Amb.  
Temp C

Bearing  
Type

Features

Capacitor  
(µF)

Wgt.  
(lbs)

G2E133-DN77-01

1

138.3

230

60\*

110

65

50



Ball

Leads

2

4.19

\* 50 Hz data available



ebmpapst

e-mail: [sales@us.ebmpapst.com](mailto:sales@us.ebmpapst.com) • TEL: 860-674-1515 • FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2006 © ebm-papst Inc. reserves the right to change any specifications or data without notice

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[G2E133-DN77-01](#) [G2E133-DN77-12](#) [G2E133-DN77-08](#) [G2E133-DN77-27](#)