

2SK796, 2SK796A

Silicon N-channel Power F-MOS FET

■ Features

- Low ON resistance $R_{DS(on)}$: $R_{DS(on)} = 3.0\Omega$ (typ.)
- High switching rate : $t_i = 40\text{ns}$ (typ.)
- No secondary breakdown
- High breakdown voltage, large power


■ Application

- No contact relay
- Solenoid drive
- Motor drive
- Control equipment
- Switching power source

■ Absolute Maximum Ratings ($T_c = 25^\circ\text{C}$)

Item	Symbol	Value	Unit
Drain-source voltage	2SK796	800	V
	2SK796A	900	
Gate-source voltage	V_{GS}	± 20	V
Drain current	DC	3	A
	Peak to peak value	6	
Power dissipation	$T_c = 25^\circ\text{C}$	90	W
	$T_a = 25^\circ\text{C}$	3.0	
Channel temperature	T_{ch}	150	$^\circ\text{C}$
Storage temperature	T_{stg}	$-55 \sim +150$	$^\circ\text{C}$

■ Package Dimensions



■ Electrical Characteristics ($T_c = 25^\circ\text{C}$)

Item	Symbol	Condition	min.	typ.	max.	Unit
Drain current	I_{DS}	$V_{DS} = 640\text{V}, V_{GS} = 0$			0.1	mA
Gate-source current	I_{GS}	$V_{GS} = \pm 20\text{V}, V_{DS} = 0$			± 1	μA
Drain-source voltage	2SK796	$I_D = 1\text{mA}, V_{GS} = 0$	800			V
	2SK796A		900			
Gate threshold voltage	V_{th}	$V_{DS} = 25\text{V}, I_D = 1\text{mA}$	1		5	V
Drain-source ON resistance	$R_{DS(on)}$	$V_{GS} = 10\text{V}, I_D = 2\text{A}$		3.5	5.0	Ω
Forward transfer admittance	$ Y_{fs} $	$V_{DS} = 25\text{V}, I_D = 2\text{A}$	0.7	1.7		S
Input capacitance	C_{iss}	$V_{DS} = 20\text{V}, V_{GS} = 0, f = 1\text{MHz}$		600		pF
Output capacitance	C_{oss}			110		pF
Reverse transfer capacitance	C_{rss}			50		pF
Turn-on time	t_{on}	$V_{GS} = 10\text{V}, I_D = 2\text{A}$ $V_{DD} = 200\text{V}, R_L = 100\Omega$		55		ns
Fall time	t_f			40		ns
Delay time	$t_d(\text{off})$			110		ns