

330854



ZONE	LTR	DESCRIPTION	DATE	APPROVED
	P1	REVISED PER ECO-11-005294	07APR11	HMR

WIRE SIZE (AWG)	CLIP	"J"	PNEUMATIC TOOL	MANUAL SERVICE TOOL
	COLOR CODE		1000 CLIPS/REEL	40 STRIPS 25 EACH
20	YELLOW	.051	2-330854-6	2-330854-4
24	RED	.029	2-330854-9	4-330854-1

CLIP SELECTION CHART


INSULATION DIA. RANGE	MANDREL NUMBER	
	PNEUMATIC TOOL (69585-1)	MANUAL SERVICE TOOL (69702)
.066-.075	69542	69561-1
.076-.085	69542-1	69561-1
.086-.095	69542-8	69561-4

MANDREL SELECTION CHART




NOTE:
1. TIN PLATE (MIL-T-10727) .0001 MIN THK


AMP IDENTIFYING CODE (SEE TABLE)




SUGGESTED GAGE DESIGN



SIDE VIEW OF GAGE



DOUBLE END HANDLE A.G.D STD.



END VIEW OF GAGE

SCALE: 1-1

NOTE: GAGE TO VERIFY "X" DIM ONLY

DIM	GO	NO GO
"X"	.0214	.0261

UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ±.008 ANGLES ± 5°	CONTRACT NO. <i>3-23-67</i>
MATERIAL PHOS BRONZE (QQ-P-750)	OR <i>R. Weller</i>
HEAT TREAT	CHK <i>R. Weller</i>
FINISH	APPD <i>Swahel</i>
NOTE 1	DESIGN APPD
	OTHER APPD

STE TE Connectivity	
NAME TERMI-POINT CLIP .031X.093 SYSTEM	
SIZE B	CODE IDENT NO. 00779
NUMBER 330854	
SCALE 10:1	WT CALC ACTUAL
SHEET 1 OF 1	

AMP INFO
LOC
AD251P