



4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.									
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
					D2	REV PER ECR 08-013956	04JUN08	JR	TM
AMP WIRE RANGE 12-10 AWG SOLID OR STRANDED				1 STAMP AMP 12-10, LOCATE APPROX AS SHOWN. 2 BODY - COPPER PER ASTM B-152 SLEEVE - COPPER PER ASTM B-152 INSULATION - NYLON 3 BODY - TIN PLATE PER ASTM B-545 SLEEVE - TIN PLATE PER ASTM B-545 INSULATION - COLOR , BLACK 4 DIMENSION APPLIES FROM EDGE OF METAL WIRE BBL TO FLANGE. 5 WIRE INSULATION DIA 3.8-6.4 6 TONGUE MATERIAL THK 1.07 MAX 7 FLANGE WIDTH 4.6					
									
				500		LOOSE PC		151471	
				QTY		DESCRIPTION		PART NO	
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS				MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		THIS DRAWING IS A CONTROLLED DOCUMENT.			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300V MAX		DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5180-13100] SOLID OR STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± -	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL - 2		FINISH - 3	
						DWN JR RUTH 23FEB2006		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
						CHK T MICHIELUTTI 23FEB06		NAME	
						APVD T MICHIELUTTI 23FEB06		TERMINAL, LIPPED BLADE, P.I.D.G., WIRE SIZE: 12-10 AWG	
						PRODUCT SPEC		SIZE	
						APPLICATION SPEC		CAGE CODE	
						WEIGHT -		DRAWING NO	
						CUSTOMER DRAWING		RESTRICTED TO	
						SCALE 5:1		SHEET 1 OF 1	
						REV D2			