

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

G

14

P

F

ZONE

LTR

F

EC 0720-0279-93

REVISIONS

DESCRIPTION

DATE

APPD

6-18-93

56 AB

AMP
WIRE RANGE

1/0 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 1.78±0.08[.070±.003]
FOR 14.73[.580] MAX WIRE INS DIA

INSULATION

DIMPLED SURFACE

15.88
[.625]
MAX WASHER R

BODY

20.50
[.807]

8.33±0.13
[.328±.005]

(FOR 5/16 STUD)

51.64
[2.033] MAX

61.62
[2.426] MAX

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C

VOLTAGE RATING:

CIRCULAR MIL AREA:
42.4-60.6mm² [83,700-119,500]

STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED

TOLERANCES UNLESS OTHERWISE
SPECIFIED:
2 PLC DEC ± 0.20(.008)
3 PLC DEC ± .1

MATERIAL
COPPER PER ASTM B-152
NYLON (MIL-M-20693) TYPE 1
COLOR: BLUE

FINISH
TIN PLATE PER MIL-T-10727

QTY

PACKAGE TYPE

PART NO

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 1/0 AWG

SIZE
CAGE CODE
DRAWING NO

B 00779 C=324113

SCALE
NTS SHEET 1 OF 1

AMP 1470-15 REV 3-92

13 AUG 1993

AMP12368

<UUI28A>DEPT1132>U.DWG1132>U.RBY>U.TERMINYL>U.CUST

CUSTOMER DRAWING