



CAVITY IDENTIFICATION ON
P/N (D) 582561-1 ONLY.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	R	ECO-08-020973	PY 11-08	JW



(1)-58256T-1 I. SAME AS -1 EXCEPT TO HAVE CAVITY IDENTIFICATION ON TOP SURFACE OF HOUSING.



SECTION A~A

① UPPER CASE LETTERS 1st. ALPHABET, LOWER CASE LETTERS 2ND ALPHABET, OMIT LETTERS G, I, O, & Q.
CIRCUIT CAVITY IDENTIFICATION MARKING SEE L-C-2K97.

GROOVES FOR ON CONTACT KEYING AMP'S OPTION DEPENDING ON METHOD OF MANUFACTURE. FOR "ON CONTACT" KEYING USE KEYING PLUG P/N 583487-1, (MUST BE ORDERED SEPARATELY.)

3. LASER MARKING ACCEPTABLE FOR ALL MARKING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		CONTRACT NO		AMP TRADE-MARK		AMP INCORPORATED HARRISBURG, PENNSYLVANIA			
FRACTIONS ± $\frac{1}{16}$	DECIMALS ± .005	ANGLES ± $\frac{1}{2}$	DR <i>J. A. Smith</i>	DATE 6-7-67	NAME 43 POSITION AMP-TAB CONNECTOR .100 CENTERS DUAL				
MATERIAL			CHK <i>J. S. Heide</i>	DATE 8/19/67					
SEE CALLOUT			DSGN ENGR	DATE					
			APPD <i>J. K. ...</i>	DATE 2/1/67					
			<i>K. ...</i>						
HEAT TREAT —			DSGN APPD		SIZE C	CODE IDENT NO 00779	NUMBER 582561	RFV R	
FINISH SEE CALLOUT			OTHER APPD		SCALE 4 —	WT	CALC	ACTUAL	SHEET

CUSTOMER DRAWING