









mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI	
ltr	ecr no	dr	date	linear	angles	projection	title	www.fciconnect.com			
A	V11921	JM	8/13/91				HEADER QUICKIE SLIM LINE				
B	V12776	JM	10/14/91				VERTICAL 4 WALLED				
C	V40796	MSC	5/31/94								
D	V20288	RGD	2/7/02	dr	J. MUSTARD	8/13/91					
E	N05-015	ZC	6/10/05	engr	W. FUNK	8/13/91					
F	N07-015	WG	8/02/07	chr	M.SMYK	8/13/91					
				appd	M.SMYK	8/13/91					
sheet index				revision sheet				scale		sheet	
								1:1		1 of 3	



2 X 5
STYLE A



2 X 7
STYLE C



2 X 5
STYLE B



2 X 8 THUR 2 X 30
STYLE D

KEY FOR PLATING AND TAIL LENGTH AND TYPE

X	TERMINAL PLATING (NOTE 9)	DIM S ± 0.1 ± 3	TERMINAL TYPE
-0XX(LF)	30u"/.76u Au OVER 50u"/1.27u Ni	.105/2.67	RD
-1XX(LF)	30u"/.76u GXT/GOLD FLASH	.105/2.67	RD
-2XX(LF)	30u"/.76u Au OVER 50u"/1.27u Ni	.150/3.81	RD
-3XX(LF)	30u"/.76u GXT/GOLD FLASH	.150/3.81	RD
-4XX(LF)	30u"/.76u Au OVER 50u"/1.27u Ni	.105/2.67	SQ
-5XX(LF)	15u"/.38u GXT/GOLD FLASH	.105/2.67	SQ
-6XX(LF)	30u"/.76u Au OVER 50u"/1.27u Ni	.150/3.81	SQ
-7XX(LF)	30u"/.76u GXT/GOLD FLASH	.150/3.81	SQ
-8XX(LF)	15u"/.38u Au OVER 50u"/1.27u Ni	.150/3.81	SQ
-9XX(LF)	30u"/.76u GXT/GOLD FLASH	.105/2.67	SQ

NOTES:

- ① SAME PIN POSITION TOLERANCE APPLIES TO BOTH ENDS OF EACH TERMINAL.
- ② MOLDING MAT'L: 30% GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL-94V-0, COLOR: BLUE.
3. 1° MAX DRAFT PERMISSIBLE ON ALL SURFACES.
4. 4 POUNDS/1.8 KILOGRAMS MIN. TERM. PULL-OUT FORCE.
- ⑤ TERMINAL MAT'L: PHOSPHOR BRONZE.
- ⑥ A. PART NUMBERS HAVING AN "R" FOLLOWING THE 8 DIGIT PART NUMBER (EXAMPLE 89239-010R) HAVE TWO PAIRS OF PINS AT EACH END TO PROVIDE RETENTION. LOCATION IS MANUFACTURER'S OPTION. SEE DETAIL "R" SHEET 1.
B. CONNECTORS WITH RETENTION AND ROUND PINS HAVE 15LB./6.8KG. MAX INSERTION AND .25LB./11KG. MIN RETENTION FORCE WHEN USED IN A .035/0.89±.003/0.08 DIA HOLE AND .062/1.58 THICK P.C.BOARD.
C. CONNECTORS WITH RETENTION AND SQUARE PINS HAVE A 15LB./6.8KG. MAX INSERTION AND A .5LB./23KG. MIN RETENTION WHEN USED IN A .040/1.02±.003/0.08 DIA HOLE AND A .062/1.58 THICK P.C.BOARD.
7. THE HOUSING OF XXXX-XYLF WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.
8. 88874-***LF IS JUST A LEAD FREE PRODUCT.
9. PLATING OPTION: MAYBE EITHER GOLD OR GXT PLATING AT MANUFACTURER'S OPTION.

mat'l. code					tolerances unless otherwise specified			CUSTOMER COPY				www.fciconnect.com	
ltr	ecr	no	dr	date	linear	.X ± 0.3		projection 	title HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED				
F						.XX ± 0.13							
						.XXX ± 0.05							
					angles	±							
			dr	J. MUSTARD	8/13/91			INCH/MM	product family QUICKIE			code	
			enr	W. FUNK	8/13/91				size	dwg no			
			chr	M.SMYK	8/13/91								
			appd	M.SMYK	8/13/91			scale 1:1	A3	88874		sheet 2 of 3	
sheet index	revision sheet												



NOTE 6	POS	DIM A	DIM B	DIM C	STYLE
88874—X02 (LF)	2X5	.78/19.8	.72/18.3	.400/10.16	B
↑ —X08(LF)	2X4	.68/17.3	.62/15.8	.300/7.62	A
—X10(LF)	2X5	.78/19.8	.72/18.3	.400/10.16	A
—X14(LF)	2X7	.98/24.9	.92/23.4	.600/15.24	C
—X16(LF)	2X8	1.08/27.9	1.02/25.9	.700/17.78	D
—X20(LF)	2X10	1.28/32.5	1.22/31.0	.900/22.86	↑
—X24(LF)	2X12	1.48/37.6	1.42/36.1	1.100/27.94	↑
—X26(LF)	2X13	1.58/40.1	1.52/38.6	1.200/30.48	↑
—X30(LF)	2X15	1.78/45.2	1.72/43.7	1.400/35.56	↑
—X34(LF)	2X17	1.98/50.3	1.92/48.8	1.600/40.64	↑
—X40(LF)	2X20	2.28/57.9	2.22/56.4	1.900/48.26	↑
—X44(LF)	2X22	2.48/63.0	2.42/61.5	2.100/53.34	↑
↓ —X50(LF)	2X25	2.78/70.6	2.72/69.1	2.400/60.96	↓
88874—X60 (LF)	2X30	3.28/83.3	3.22/81.8	2.900/73.66	D

[illegible]