


Glass Passivated Single-Phase Bridge Rectifier



Case Style KBPM

MAJOR RATINGS AND CHARACTERISTICS

$I_{F(AV)}$	2 A
V_{RRM}	50 V to 1000 V
I_{FSM}	60 A
I_R	5 μ A
V_F	1.1 V
T_j max.	150 °C

FEATURES

- UL Recognition file number E54214
- Ideal for printed circuit board
- High surge current capability
- High case dielectric strength
- Solder Dip 260 °C, 40 seconds
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



TYPICAL APPLICATIONS

General purpose use in ac-to-dc bridge full wave rectification for Switching Power Supply, Home Appliances, Office Equipment, and Telecommunication applications.

MECHANICAL DATA

Case: KBPM

Epoxy meets UL 94V-0 flammability rating

Terminals: Silver plated (E4 Suffix) leads, solderable per J-STD-002B and JESD22-B102D

Polarity: As marked on body

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise noted)

PARAMETER	SYMBOL	2KBP 005M	2KBP 01M	2KBP 02M	2KBP 04M	2KBP 06M	2KBP 08M	2KBP 10M	UNIT
		3N253	3N254	3N255	3N256	3N257	3N258	3N259	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Max. average forward output rectified current at $T_A = 55$ °C	$I_{F(AV)}$	2.0							A
Peak forward surge current single half sine-wave superimposed on rated load	I_{FSM}	60							A
Rating for fusing ($t < 8.3$ ms)	I^2t	15							A ² sec
Operating junction and storage temperature range	T_J, T_{STG}	- 55 to + 165							°C

ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)										
PARAMETER	TEST CONDITIONS	SYMBOL	2KBP 005M	2KBP 01M	2KBP 02M	2KBP 04M	2KBP 06M	2KBP 08M	2KBP 10M	UNIT
			3N253	3N254	3N255	3N256	3N257	3N258	3N259	
Maximum instantaneous forward voltage drop per leg	at 3.14 A	V_F	1.1							V
Maximum DC reverse current at rated DC blocking voltage per leg	$T_A = 25\text{ }^{\circ}\text{C}$ $T_A = 125\text{ }^{\circ}\text{C}$	I_R	5.0 500							μA
Typical junction capacitance per leg	at 4.0 V, 1 MHz	C_J	25							pF

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL	2KBP 005M	2KBP 01M	2KBP 02M	2KBP 04M	2KBP 06M	2KBP 08M	2KBP 10M	UNIT
		3N253	3N254	3N255	3N256	3N257	3N258	3N259	
Typical thermal resistance per leg ⁽¹⁾	R _{θJA}	30							°C/W
	R _{θJL}	11							

Note:

(1) Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with, 0.47 x 0.47" (12 x 12 mm) copper pads

ORDERING INFORMATION				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
2KBP06M-E4/45	1.895	45	30	Tube
2KBP06M-E4/51	1.895	51	600	Anti-static PVC Tray
3N257-E4/45	1.895	45	30	Tube
3N257-E4/51	1.895	51	600	Anti-static PVC Tray

RATINGS AND CHARACTERISTICS CURVES

($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)




Figure 1. Derating Curve Output Rectified Current




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current Per Leg




Figure 3. Typical Forward Characteristics Per Leg




Figure 5. Typical Junction Capacitance Per Leg





Figure 4. Typical Reverse Leakage Characteristics Per Leg

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.