

**Part Number: 74526-4110**

0.50mm Pitch LaneLink™ 10Gbase-CX4 Cable Assembly, 26 AWG, Lanyard Latch, 11.0m Length



Series image - Reference only

|                     |                  |
|---------------------|------------------|
| <b>Status:</b>      | <b>OBsolete</b>  |
| <b>Replacement:</b> | Contact Molex    |
| <b>Series:</b>      | 74526            |
| <b>Category:</b>    | Cable Assemblies |
| <b>Overview:</b>    | LaneLink™        |

**Mates With Part(s):**  
[91525](#) 4X/12X Latch LaneLink™ Receptacle  
[91804](#) LaneLink™ Connector

**Use With:**  
[74735](#) X2 Transceiver  
[74739](#) XPAK Transceiver

**Product Environmental Compliance**[EU RoHS](#): ELV and RoHS Compliant[China RoHS](#): [REACH SVHC](#): Not Reviewed[Low-Halogen Status](#): Not Reviewed**Part Detail****General**

|                        |                            |
|------------------------|----------------------------|
| <b>Status</b>          | <b>Obsolete</b>            |
| Category               | Cable Assemblies           |
| Series                 | <a href="#">74526</a>      |
| Connector to Connector | 4X Plug-to-4X Plug         |
| Overview               | <a href="#">LaneLink™</a>  |
| Product Name           | 10Gbase-CX4, 4X, LaneLink™ |

**Physical**

|                          |           |
|--------------------------|-----------|
| Cable Length             | 11.0m     |
| Circuits (Loaded)        | 16        |
| Gender                   | Plug/Plug |
| Lock to Mating Part      | Yes       |
| Packaging Type           | Bag       |
| Single Ended             | No        |
| Waterproof / Dustproof   | No        |
| Wire Insulation Diameter | N/A       |
| Wire Size AWG            | 26        |
| Wire/Cable Type          | Round     |

**Electrical****(Please review the Product Specification for specific details.)**

|                               |             |
|-------------------------------|-------------|
| Current - Maximum per Contact | 0.5A        |
| Impedance                     | 100Ω        |
| Shield Type                   | Full Shield |
| Shielded                      | Yes         |
| Voltage - Maximum             | 30V AC      |

**Material Info**

|     |              |
|-----|--------------|
| UPC | 800756825113 |
|-----|--------------|

**Reference - Drawing Numbers**

|               |              |
|---------------|--------------|
| Sales Drawing | SD-74526-400 |
|---------------|--------------|

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)