



Product Navigation

[Home](#) [About Us](#) [Products](#) [Investor Relations](#) [News](#) [Contact Us](#) [Secure EAX](#)

Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

 sales contacts

 stock check

 search

 Product Line Search

Please select a Product Line to search.

[Circuit Board Indicators](#) 

 find

 Part # / Text Search

Part No.:

Text Search:

 search

 quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF](#)

File

Application Notes FAQs

[Dialight Ltd \(UK\)](#)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)

Circuit Board Indicators - Through Hole Indicators	
P/N# 5501007F	5 mm Lens Single Color
Description	5 mm CBI Right Angle B
Package Options	100 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Single Housing
Configuration	5 mm Lens
Lamp Type	Single Color
Viewing	Right Angle
Viewing Angle	30
Test Current (mA)	20mA

Absolute Maximum Ratings (Ta = 25 °)	
Solder Temp	260° for 5 sec
Operating Temp	-40 to +80° C
Storage Temp	-40 to +100° C



RoHS / pB Free

[view PDF](#)

Operating Characteristics	
LED Position	
Color	Blue
Lamp Type	Single Color
LED Type	High Efficiency
Intensity Min (mcd)	520
Intensity Typ (mcd)	1000.0
Intensity Max (mcd)	1500.0
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	472
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	120
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Distributor Stock Check

Check stock with our distributors now.

5501007F

 check stock