



4

3





2

1

LOC		DIST		REVISIONS		
J		P	LTR	DESCRIPTION	DATE	APVD
				SEE SHEET 1	-	-



- (APPLIED TO SHEET 3)
1. TOLERANCES ON ALL DIMENSIONS ±0.15 UNLESS OTHERWISE SPECIFIED.
 2. P.C. BOARD THICKNESS APPLIES ACROSS TABS AND INCLUDES PLATING AND/OR METALIZATION.
 3. FINISH OF PAD : GOLD PLATING 0.00076 MIN. OVER Ni PLATING 0.002MIN.
- NO BURR
CHAMFER 0.25 MAX x 45° IF EXIST.



RECOMMENDED MATING P.C.B CONFIGURATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	31.75				
		CHK	25.4				
		APVD	H	1.8V	17.55	2.4	2.7
		PRODUCT SPEC	POWER SUPPLY				
		APPLICATION SPEC	D5 D4 D3				
		WEIGHT					
CUSTOMER DRAWING		SCALE	1:1	SHEET	3 OF 4	REV	B

Tyco Electronics Corporation Kawasaki, Japan	
NAME DDR SODIMM SOCKET 0.6mm PITCH 200POS 5.2H RVS TYPE TO FIT AMC APPLICATIONS	
SIZE A3	CAGE CODE C-1981281
DRAWING NO	RESTRICTED TO

