

**POWER FACTOR CORRECTION
RECTIFIERS (PFC DIODE)**

REVERSE VOLTAGE - **600** Volts
FORWARD CURRENT- **8.0** Amperes


FEATURES

- Power Factor Correction function.
- Glass passivated chip
- Superfast switching time for high efficiency
- Low forward voltage drop and high current capability
- Low reverse leakage current
- High surge capacity
- Plastic package has UL flammability classification 94V-0

MECHANICAL DATA

- Case : TO-220AC molded plastic
- Polarity : As marked on the body
- Weight : 0.08 ounces, 2.24 grams
- Mounting position : Any

TO-220AC



TO-220AC		
DIM.	MIN.	MAX.
A	14.22	15.88
B	9.65	10.67
C	2.54	3.43
D	5.84	6.86
E	8.26	9.28
F	-	6.35
G	12.70	14.73
H	4.83	5.33
I	0.51	1.14
J	0.30	0.64
K	3.53 Ø	4.09 Ø
L	3.56	4.83
M	1.14	1.40
N	2.03	2.92

All Dimensions in millimeter

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%

CHARACTERISTICS	SYMBOL	STPR806D	UNIT
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	600	V
Maximum RMS Voltage	V_{RMS}	420	V
Maximum DC Blocking Voltage	V_{DC}	600	V
Maximum Average Forward Rectified Current @ $T_C=100^\circ C$	$I_{(AV)}$	8	A
Peak Forward Surge Current 8.3ms single half-sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	100	A
Maximum Forward Voltage at 8.0A DC @ $T_J=25^\circ C$ @ $T_J=125^\circ C$	$V_F (MAX)$	1.75 1.4	V
Maximum DC Reverse Current at Rated DC Blocking Voltage @ $T_J=25^\circ C$ @ $T_J=125^\circ C$	I_R	5 200	uA
Typical Junction Capacitance (Note 1)	C_J	60	pF
Maximum Reverse Recovery Time (Note 2)	T_{RR}	25	ns
Typical Thermal Resistance (Note 3)	$R_{\theta JC}$	2.5	°C/W
Operating and Storage Temperature Range	T_J, T_{STG}	-55 to +150	°C

NOTES : 1. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
2. Reverse Recovery Test Conditions: $I_F=0.5A, I_R=1.0A, I_{RR}=0.25A$.
3. Thermal Resistance Junction to case.

REV. 1, 13-Sep-2001, KTGA10

FIG.1 - FORWARD CURRENT DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 - TYPICAL REVERSE CHARACTERISTICS




FIG.4 - TYPICAL FORWARD CHARACTERISTICS




FIG.5 - TYPICAL JUNCTION CAPACITANCE

