

PRODUCT NUMBER
91615-XXXXWLF

RoHS COMPATIBLE, SEE NOTE 7

OPTIONAL LETTER SEE SHEET 2
N: PRODUCT WITH TYPE MARKING ON CONNECTOR

OPTIONAL LETTER

A: PRODUCT WITH PICK UP CAP PACKED IN
TAPE & REEL SEE TAB56.
B: PRODUCT WITH PICK UP CAP PACKED IN TUBE.

NUMBER OF POSITIONS PER ROW: 03 UP TO 30.
MORE THAN 30 POSITIONS ON SPECIAL REQUEST.

PLATING CODE

3= 0.76µm GOLD ON CONTACT AREA.

2µm MIN MATTE TIN ON TAIL.

4= 2µm MIN MATTE TIN FULL PLATED

1.27µm Ni MINUNDERPLATING

NOTES:

1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0 COLOR: GREY.

2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.

3 - PACKAGING:

3 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.

5 UP TO 30 POSITIONS PRODUCT PACKED IN TUBE.

WHOLE 91615-303B PRODUCT PACKED IN TUBE.

4 - TO DETERMINE DIMENSIONS:

N = NUMBER OF POSITIONS PER ROW

EXAMPLE: 8 POS: ((N+2)x2.54)-0.08=25.32 mm.

5 - RECOMMENDED IR PROFILE PER TAB42.

6 - Ø2.65 MINI FOR PICK & PLACE ASSEMBLY(=0 INSERTION FORCE).

7 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

d - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.




b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code		SEE NOTES		surface		tolerance		projection		product family	
ltr	ecm no	lfr	date	ISO 1302	ISO 406	ISO 1101	ISO 1101	mm	mm	title	DUBOX
AB	T04-0347	DLE	04.11.10	tolerances unless otherwise specified	±0.3					BtB RECEIPT.	
AC	F06-0137	DLE	06.02.27	angles	linear					VERT DR SMT	
AD	F06-0204	DLE	06.06.23	±°						scale 5:1	
AE	F07-0169	DLE	07.03.30	dr	P NIZZI	95.11.17				dwg no	91615
AF	B-19123	LMU	14.10.21	lengr	P.NZ	01.07.23				sheet 1 of 3	A3
				chr	P.NZ	01.07.23				type	CUSTOMER
				qppd	J.F.N	01.07.23				Drawing	
sheet	revision	AE	D	B							
index	sheet	1	2	3							



FCIconnect.com


Copyright FCI

PRODUCT NUMBER
91615-YXXZNLF


RoHS COMPATIBLE, SEE NOTE 7

APPLICATION SPECIFIC


PRINTING METHOD FOR 91615-Y07 UP TO -Y50
MARKING: PART NUMBER AND DATE CODE



91615-YXXZNLF XXXX



PRINTING METHOD FOR 91615-Y03 UP TO -Y07




mat'l. code				surface			tolerance			projection		product family	
ltr	ecn no	dr	date	ISO 1302	ISO 406	ISO 1101	tolerances unless otherwise specified	linear	±0.3	mm	mm	DUBOX	title
A	F10379	DLE	01.07.23	angles									BtB RECEPT.
B	F04-0347	DLE	04.11.10	linear									VERT DR SMT
C	F06-0137	DLE	06.02.27	±2°									
D	F06-0204	DLE	06.06.23	dr	DLE	01.07.23							
E	B-19123	LMU	14.10.21	lengt	P.NZ	01.07.23							
				chr	P.NZ	01.07.23							
				apptd	JF.N	01.07.23							
sheet index	revision												



91615
CUSTOMER
Drawing

Form: A3



mat'l. code				surface		tolerance		projection	product family		
lfr	ecm no	dr	date	ISO 1302	ISO 406	ISO 1101	ISO 1101				
A	F04-034	DLE	04.11.10	tolerances unless otherwise specified	±0.3			mm	title		
B	F06-0204	DLE	06.06.23	angles	linear			mm			
				±2°				scale/A	dwg no		
				dr	DLE	04.11.10			sheet 3 of - size		
				engr	P.NZ	04.11.10					
				chr	P.NZ	04.11.10			A3		
				appd	P.NZ	04.11.10					
sheet	revision								type		
index	sheet										