

## Rubber Grommet KG-Type




### Characteristic

Installation can be made with a single touch and it is effective on preventing wire disconnection.

### Application


Controller devices / Telecommunication devices / Electric appliances, etc.



| Model No. | Material | Hardness | Color |
|-----------|----------|----------|-------|
| KG        | EPDM     | 50°±5°   | Black |

| Model No. | A  | B  | C   | D   | E   | F    | Net Weight (g) | Code No. |
|-----------|----|----|-----|-----|-----|------|----------------|----------|
| KG-74     | 7  | 5  | 3   | 4   | 1   | R1   | 0.1            | 5223     |
| KG-742    | 7  | 5  | 3   | 5   | 2   | R1   | 0.1            | 5224     |
| KG-95     | 9  | 7  | 3   | 5.5 | 0.8 | R1.5 | 0.3            | 5225     |
| KG-115    | 11 | 8  | 5   | 5   | 1   | R1.5 | 0.4            | 5226     |
| KG-135    | 13 | 8  | 5.5 | 5   | 1   | R1.5 | 0.5            | 5227     |
| KG-16     | 16 | 12 | 9   | 6.5 | 1.5 | R3   | 0.6            | 5229     |

## Rubber Grommet MG-Type



For MG-9

### Characteristic

It has a dustproof function other than wire disconnection preventing effect that ordinary grommets have.

### Application

Computers / Measuring instruments / Telecommunication devices / Electric appliances, etc.

| Model No. | Material | Hardness | Thickness of Membrane (mm) | Color |
|-----------|----------|----------|----------------------------|-------|
| MG        | EPDM     | 50°±5°   | approx.0.5                 | Black |

| Model No. | A  | A1 | B  | C   | D    | D1  | D2  | E    | Net Weight (g) | Code No. |
|-----------|----|----|----|-----|------|-----|-----|------|----------------|----------|
| MG-1      | 23 | 20 | 16 | 11  | 8.1  | 3.5 | 2   | 1.6  | 2.6            | 5601     |
| MG-2      | 25 | 22 | 18 | 13  | 8.8  |     |     | 2.3  | 3.0            | 5602     |
| MG-3      | 27 | 24 | 20 | 15  | 9.1  | 4   | 2.5 | 1.6  | 4.0            | 5603     |
| MG-4      | 29 | 26 | 22 | 17  | 9.8  |     |     | 2.3  | 4.6            | 5604     |
| MG-5      | 31 | 28 | 24 | 19  | 11.3 | 5   | 3   | 6.1  | 5.6            | 5605     |
| MG-6      | 35 | 31 | 26 |     | 12.2 |     |     | 3.2  | 8.2            | 5606     |
| MG-7      | 37 | 33 | 28 | 21  | 11.8 |     |     | 2.3  | 8.5            | 5607     |
| MG-8      | 39 | 35 | 30 | 23  | 12.7 |     |     | 3.2  | 9.5            | 5608     |
| MG-9      | 35 |    |    | 25  | 8    | 3   | 2   | 5.0  | 5609           |          |
| MG-10     | 41 | 37 | 32 |     | 11.8 | 5   | 2.3 | 9.7  | 5610           |          |
| MG-11     | 43 | 39 | 34 | 27  | 12.7 |     | 3.2 | 11.0 | 5611           |          |
| MG-12     | 45 | 42 | 36 | 28  | 13.8 | 6   | 4   | 2.3  | 14.5           | 5612     |
| MG-13     | 48 | 44 | 38 | 30  | 14.7 |     |     | 3.2  | 17.5           | 5613     |
| MG-14     | 16 | 13 | 9  | 4.5 | 8.5  | 3.5 | 2   | 2.3  | 1.3            | 5614     |
| MG-15     | 19 | 16 | 12 | 7   | 6.3  | 2.5 | 1.5 | 1.6  | 1.5            | 5615     |
| MG-16     | 21 | 18 | 14 | 9   | 8    | 3   | 2   | 2.3  | 2.0            | 5616     |
| MG-17     | 52 | 48 | 42 | 34  | 14.7 | 6   | 4   | 3.2  | 19.5           | 5617     |