




LOC	DIST	REVISIONS					
GP	0	F	LTW	DESCRIPTION	DATE	DWN	APRD
		H		ADDED: 3/6 AND 4/6 PER OSID-0146-00	23JAN02	DD	DS
		J		ADDED: 5/6 PER OSID-0006-01	15FEB02	JB	DS
		K		REVISED PER OSID-0027-01	20FEB02	JB	DS
		L		ADDED: 6/6 PER OS11-0029-01	04MAR02	JB	DS



- 1 FOR OPTIMUM PERFORMANCE, CONTACT PAD PLATING SHOULD BE SMOOTH AND FLAT. COPPER CONTACT PADS ARE TO BE OVERPLATED WITH 0.00127[0.00050] MIN THK NICKEL FOLLOWED WITH 0.00102[0.00040] MIN THK GOLD PLATING.
- 2 CONTACT MATING AREA: 0.00076 [0.00030] MIN THICK GOLD OVER 0.00381 [0.00150] NICKEL OR GOLD FLASH OVER 0.00051[0.00020] MIN THICK 80/20 PALLADIUM-NICKEL. MIN THICK. SOLDER TAILS: 0.00381[0.00150] MIN THICK TIN-LEAD UNDERPLATE: 0.00127[0.00050] MIN THICK NICKEL OVER ENTIRE CONTACT.
- 3 MATERIAL: HOUSING AND EXTRACTORS: GLASS FILLED, HIGH TEMPERATURE NYLON. CONTACTS: PHOS BRONZE
- 4 PART NUMBER 1-390074-4 AND 1-390074-6 PACKAGED IN TUBES.
- 5 EXTRACTOR MATERIAL: GLASS-FILLED, HIGH TEMPERATURE NYLON, COLOR-GRAY.
- 6 EXTRACTOR TO BE INSERTED IN PIN 1 END.
- 7 EXTRACTOR TO BE INSERTED IN PIN 84 END.
- 8 SEE SHEET 3 FOR DETAILS.
- 9 USE ONLY GOLD PLATE OPTION FOR THIS DASH NUMBER.

DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	6-390074-6
DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	5-390074-6
DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	4-390074-6
DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	3-390074-6
DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	2-390074-6
DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	1-390074-6
DETAIL A	DETAIL A	STD DRAM, 3.3 VOLT	1-390074-4
DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	390074-6
DETAIL B	DETAIL A	SYNC DRAM, 3.3 VOLT	390074-5
DETAIL A	DETAIL A	STD DRAM, 3.3 VOLT	390074-4
DETAIL A	DETAIL B	STD DRAM, 5 VOLT	390074-1
KEY #1	KEY #2	PART DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ALL DIMENSIONS ARE TO BE CONTROLLED BY THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN W. SORAH 21-AUG-96	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK R. TALLEY 21-AUG-96	NAME SOCKET ASSY, DUAL READ-OUT, VERSION 11, 17.78 [0.700], LOCKING EXTRACTORS, 168 POSITION	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.13 [0.005] 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°		APRD P. SMITH 21-AUG-96	PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CAGE CODE 00779 DRAWING NO. C390074	
MATERIAL 3		FINISH 1 2		CUSTOMER DRAWING SCALE 4:1 SHEET 1 OF 3 REV 1



Technical drawing of a mechanical part, likely a bracket or support, showing dimensions and tolerances. The drawing includes a top view and a side view. Key dimensions and tolerances are:

- Top view dimensions:
 - Overall width: 2.01 ± 0.1 [0.079 $\pm$.003]
 - Inner width: 0.1 [0.0039] (M, A, B)
 - Inner width tolerance: 0.039
- Side view dimensions:
 - Overall height: 3 [0.118] TYP
 - Radius: R FULL

The drawing also includes a title block with the text "TYP" and "R FULL".

THIS DRAWING IS A NON-REPLACEMENT FOR AMP INCORPORATED'S INSTRUCTIONS TO INSTALLERS AND THE GENERAL ASSEMBLY INSTRUCTION DRAWING SHOWN ON THE BACK OF THIS LATEST REVISION.						DWG NO. SORAH 21-AUG-96		AMP		AMP Incorporated Harrisburg, PA 17105-3608							
						CHG NO. R TALLEY 21-AUG-96											
DIMENSIONS: mm [INCHES]						TOLERANCES UNLESS OTHERWISE SPECIFIED:											
0 PLOC ± 1 PLOC ± 2 PLOC ±0.13 [.005] 3 PLOC ± 4 PLOC ± ANGLE ±° ±'						NAME SOCKET ASSY, DUAL READ-OUT, VERSION II, 17.78 [7.001], LOCKING EXTRACTORS, 168 POSITION											
						PRODUCT SPEC						SIZE		CASE CODE		DRAWING NO	
APPLICATION SPEC						WEIGHT -		A1		00779		C-390074					
MATERIAL SEE SH I						CUSTOMER DRAWING						SCALE		SHEET 2 OF 3		REV 1	
FINISH																	



SEE JEDEC SPEC. MO-161 FOR COMPLETE MODULE DETAILS
 $1.27 \pm 0.10 [0.050 \pm 0.004]$ THICK ACROSS CONTACT PADS 

