




REV	ECN	APP'D
-	6215	JT 6/18/08
A	6299	JT 5-29-09





PART NUMBER TABLE


APCD P/N	HARDWARE PACKAGE	CONTACTS SUPPLIED
JRS500100	NONE	NONE
JRS500101	NONE	YES
JRS500110	YES	NONE
JRS500111	YES	YES

NOTES:

1. MATERIALS:
HOUSING: POLYETHERIMIDE PER ASTM-D5205
GROMMET: SILICONE RUBBER PER A-A-59588
THREADED INSERT: STAINLESS STEEL
2. OPERATING RANGE:
TEMPERATURE: -65 °C TO 125 °C
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS AT SEA LEVEL AND 500 VRMS AT 80,000 FT. ALTITUDE
VIBRATION: MIL-STD-202, METHOD 204, TEST CONDITION G
SHOCK: MIL-STD-202, METHOD 213, TEST CONDITION C
3. PART ACCEPTS M39029/92-533 AND M39029/92-535 SOCKET CONTACTS, SIZE 16/16 AND SIZE 12/12.



MOUNTING CONFIGURATION



DIMENSIONS		TOLERANCES		PROJECTION		Amphenol Pcd		TITLE							
ANSI Y14.5M		.XX ±0.01				SPECIFICATION DRAWING		SNAP-IN RELAY SOCKET							
UNITS: INCHES		.XXX ±0.005				ENGR		1 POLE							
Pro/E FILE		ANGLES ±2.0°				Frank.Li 07-Apr-08		3 POS. SIZE 12, 2 POS. SIZE 16							
ORIGINAL 		THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC., BEVERLY, MA				CHKD		5/29/09		SIZE		DWG NO.		REV	
						APPD		5-29-09		B		JRS500100		A	
								CODE: 58982		SCALE: 2:1		SHEET 1 OF 1			