

Coaxial

Low Pass Filter

50Ω DC to 720 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Features

- good attenuation rate, 1.35 typ. 20dB/3dB BW ratio
- rugged shielded case
- other SLP models available with wide selection of cut-off frequencies

Applications

- lab use
- test equipment
- video equipment

SLP-800+
SLP-800

CASE STYLE: FF99

Connectors	Model	Price	Qty.
SMA	SLP-800(+)	\$34.95 ea.	(1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-720	800	1080-1400 1400-2000	1.7 18


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.67	1.98	.312	grams
17.02	50.29	7.92	42.0

typical frequency response






electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$ σ			
10.00	0.04 0.1	38.9	10.0	0.96
152.50	0.20 0.1	16.2	80.0	1.03
295.00	0.26 0.1	15.0	152.5	1.00
437.50	0.18 0.1	26.9	222.5	0.96
577.50	0.32 0.1	18.2	295.0	1.07
650.00	0.35 0.1	21.2	365.0	1.03
720.00	0.48 0.1	20.1	437.5	1.22
760.00	1.36 0.2	8.0	507.5	1.33
800.00	3.45 0.3	3.7	577.5	1.36
900.00	11.91 0.5	0.6	650.0	1.55
950.00	16.24 0.5	0.4	720.0	2.16
1000.00	20.40 0.6	0.3	740.0	2.17
1010.00	21.22 0.6	0.2	760.0	2.23
1050.00	24.40 0.7	0.2	780.0	2.36
1080.00	26.70 0.7	0.2	800.0	2.21
1100.00	28.21 0.7	0.2	900.0	1.27
1190.00	34.98 1.0	0.1	910.0	1.12
1250.00	39.81 1.3	0.1	950.0	1.02
1290.00	43.03 1.5	0.1	970.0	0.96
1300.00	43.66 1.4	0.1	1000.0	0.83
1400.00	53.30 3.1	0.1	1010.0	0.89
1500.00	64.81 3.4	0.1	1050.0	0.80
1600.00	68.20 6.6	0.1	1080.0	0.53
1700.00	66.77 2.9	0.1	1100.0	0.73
1720.00	68.97 6.7	0.1	1150.0	0.79
1735.00	70.75 8.2	0.1	1190.0	0.96
1800.00	71.72 6.9	0.1	1200.0	0.38
1820.00	65.74 5.8	0.1	1250.0	1.12
1900.00	61.76 6.1	0.1	1290.0	0.35
2000.00	56.62 3.2	0.1	1300.0	1.12



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. A
M98898
SLP-800
060508