

Duplex Multimode 62.5/125 Fiber Patch Cable (SC/ST), 10M (33-ft.)

MODEL NUMBER: **N304-10M**



Description

Tripp Lite's 10-meter (30ft - 33ft) multimode duplex fiber optic SC/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has ST to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 10-meters(30ft - 33ft) Connectors: 2 ST to 2 SC connectors
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)

Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/ST connectors

Package Includes

- 10-meter (30ft-33ft) duplex MMF cable ST/SC 62.5/125 fiber

Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Model Type	SC/ST
Network Speed	1Gbps
INPUT	
Cable Length (m)	10
UPC ASSIGNMENT	
Unit Carton UPC#	037332122551
PHYSICAL	
Color	Orange
Style	Fiber Optic
CONNECTIONS	
Connector A	SC
Connector B	ST
Number of Connectors	4
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.