



Wiha T-handle Hex Tools

Ergonomic handle design for high torque

Hole for hanging



Handle is molded directly onto blade

Smooth edges prevent injuries & eliminate pressure marks

Blade CVM tool steel, hardened, nickel-plated

Yellow = Inch

Red = Metric



[SHOP](#)

334 92 Set 10 Pc. Hex Driver T-handle Inch Sizes

Item No.	Hex	Inch	Inch	Hex	Inch	Inch	lbs.
334 92	334 53	3/32	6.0	334 68	3/16	6.0	1.74
	334 56	7/64	6.0	334 71	7/32	6.0	
	334 59	1/8	6.0	334 74	1/4	6.0	
	334 62	9/64	6.0	334 77	5/16	6.0	
	334 65	5/32	6.0	334 80	3/8	6.0	



[SHOP](#)

334 93 Set 8 Pc. Hex Driver T-handle Metric Sizes

Item No.	Hex	mm	mm	Hex	mm	mm	lbs.
334 93	334 01	2.0	100	334 09	5.0	100	1.64
	334 02	2.5	100	334 16	6.0	200	
	334 03	3.0	100	334 23	8.0	200	
	334 06	4.0	100	334 27	10.0	200	

[SHOP](#)

NEW
From Wiha



#33484



#33488

[SHOP](#)

334 84 Set 8 Pc. Hex Driver T-handle Inch Sizes - In metal stand

Item No.	Hex	Inch	Inch	Hex	Inch	Inch	lbs.
334 84	334 59	1/8	6.0	334 71	7/32	6.0	3.07
	334 62	9/64	6.0	334 74	1/4	6.0	
	334 65	5/32	6.0	334 77	5/16	6.0	
	334 68	3/16	6.0	334 80	3/8	6.0	

334 88 Set 8 Pc. Hex Driver T-handle Metric Sizes - In metal stand

Item No.	Hex	mm	mm	Hex	mm	mm	lbs.
334 88	334 01	2.0	100	334 10	5.0	150	3.07
	334 02	2.5	100	334 15	6.0	150	
	334 03	3.0	100	334 23	8.0	200	
	334 06	4.0	100	334 27	10.0	200	

334 Hex Driver, With Wiha T-handle Blade CVM steel, hardened, nickel-plated. Chamfered tip for easy insertion. Wiha-T-handle high quality plastic, impact resistant.

Item No.	Hex	Inch	Inch	Inch	Inch	lbs.	pkg.
334 53	3/32	6.0	2.8	7.0	.05	10	SHOP
334 56	7/64	6.0	2.8	7.0	.05	10	
334 59	1/8	6.0	2.8	7.0	.06	10	
334 62	9/64	6.0	2.8	7.0	.07	10	
334 65	5/32	6.0	2.8	7.0	.08	10	
334 68	3/16	6.0	3.5	7.0	.13	10	
334 71	7/32	6.0	3.5	7.0	.16	10	
334 74	1/4	6.0	3.5	7.0	.18	10	
334 77	5/16	6.0	3.5	7.0	.25	10	
334 80	3/8	6.0	4.1	7.0	.39	10	

Item								
No.	mm	mm	mm	mm	Inch	lbs.	pkg.	
334 01	2.0	100	80	126	4.9	.05	10	
334 36	2.0	200	80	226	8.9	.05	10	
334 02	2.5	100	80	126	4.9	.05	10	
334 37	2.5	200	80	226	8.9	.08	10	
334 03	3.0	100	80	126	4.9	.05	10	
334 04	3.0	150	80	176	6.9	.08	10	
334 05	3.0	200	80	226	8.9	.09	10	
334 35	3.0	350	100	382	15.0	.22	10	
334 06	4.0	100	80	126	4.9	.07	10	
334 07	4.0	150	80	176	6.9	.10	10	
334 08	4.0	200	80	226	8.9	.09	10	
334 38	4.0	350	100	382	15.0	.26	10	
334 09	5.0	100	100	132	5.2	.13	10	
334 10	5.0	150	100	182	7.1	.17	10	
334 11	5.0	200	100	232	9.1	.16	10	
334 12	5.0	350	100	382	15.0	.26	10	
334 13	5.0	450	120	488	19.1	.53	10	
334 14	6.0	100	100	132	5.2	.14	10	
334 15	6.0	150	100	182	7.1	.18	10	
334 16	6.0	200	100	232	9.1	.20	10	
334 17	6.0	350	100	382	15.0	.32	10	
334 19	7.0	200	100	232	9.1	.22	10	
334 21	8.0	100	100	132	5.2	.20	10	
334 23	8.0	200	100	232	9.1	.29	10	
334 34	8.0	350	100	372	14.6	.48	10	
334 25	10.0	100	120	138	5.4	.34	10	
334 27	10.0	200	120	238	9.3	.49	10	
334 29	12.0	200	120	238	9.3	.58	10	