





NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: AC 125V 7A, AC 250V 4A
5. CONTACT RESISTANCE: 20m ohm max. at 5V DC 1A.
6. DIELECTRIC STRENGTH: AC 1500V RMS
7. LIFE EXPECTANCY: Electrical: 6,000 cycle
8. OPERATING FORCE: 550±150gf
9. TRAVEL: Full: 5.5mm, Lock: 4.0mm

E-SWITCH®

TITLE			
P227 EE 2B20A			
B	10361	REVISED & REDRAWN	9/16/99
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE		DATE	DR
1.5:1		10/31/95	MM
DWG		P030100	REV
			B