


High Voltage Glass Passivated Junction Rectifier

Reverse Voltage 2000 to 4000V

Forward Current 0.25A

DO-204AL (DO-41)



Dimensions in inches and (millimeters)

*Glass-plastic encapsulation technique is covered by
Patent No. 3,996,602, and brazed-lead assembly by Patent No. 3,930,306

Features

- Plastic package has Underwriters Laboratories Flammability Classification 94V-0
- High temperature metallurgically bonded construction
- Cavity-free glass passivated junction
- Capable of meeting environmental standards of MIL-S-19500

Mechanical Data

Case: JEDEC DO-204AL, molded plastic over glass body

Terminals: Plated axial leads, solderable per MIL-STD-750, Method 2026

High temperature soldering guaranteed:
350°C/10 seconds, 0.375" (9.5mm) lead length, 5 lbs. (2.3kg) tension

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.012 ounce, 0.3 gram

Maximum Ratings & Thermal Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	GP02 -20	GP02 -25	GP02 -30	GP02 -35	GP02 -40	Unit
Maximum repetitive peak reverse voltage	V _{RRM}	2000	2500	3000	3500	4000	V
Maximum RMS Voltage	V _{RMS}	1400	1750	2100	2450	2800	V
Maximum DC blocking voltage	V _{DC}	2000	2500	3000	3500	4000	V
Maximum average forward rectified current 0.375" (9.5mm) lead length at T _A = 55°C	I _{F(AV)}	0.25					A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load at T _A = 55°C (JEDEC Method)	I _{FSM}	15					A
Typical thermal resistance ⁽¹⁾	R _{θJA}	130					°C/W
Operating junction and storage temperature range	T _J , T _{STG}	-65 to +175					°C

Electrical Characteristics Ratings at 25°C ambient temperature unless otherwise specified.

Maximum instantaneous forward voltage at 1.0A	V _F	3.0					V
Maximum DC reverse current T _A = 25°C at rated DC blocking voltage T _A = 100°C	I _R	5.0 50					μA
Typical reverse recovery time at I _F = 0.5A, I _R = 1.0A, I _{rr} = 0.25A	t _{rr}	2.0					μs
Typical junction capacitance at 4.0V, 1MHz	C _J	3.0					pF


Note: (1) Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted

*JEDEC registered values


High Voltage Glass Passivated Junction Rectifier

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)


**Fig. 1 – Forward Current
Derating Curve**




**Fig. 2 – Maximum Non-Repetitive
Peak Forward Surge Current**



**Fig. 3 – Typical Instantaneous
Forward Characteristics**



**Fig. 4 – Typical Reverse
Characteristics**



**Fig. 5 – Typical Junction
Capacitance**

