



KLP Series RCA Phono Jack PCB Mount

Features



- Audio Applications for Computers and Multimedia
- Two Contact Cost Efficient Design
- Right Angle and Vertical Mount Available
- CSA/NRTL Certified File No. LR78160

Performance Specifications

Materials and Finish

Housing:

KLP - PBT Thermoplastic, UL94V-0 Rated, Black, Red, Yellow, Orange and White Colors
KLPHT* - Zytel HTN, High Temperature Nylon, UL94V-0 Rated, Black, Yellow, Red and White Colors

Terminals: Copper Alloy, Tin over Nickel Plating

Mechanical Characteristics

Insertion Force: 0.3kg - 5.0kg

Extraction Force: 0.3kg - 3.0kg

Durability: 5000 Mating Cycles

Electrical Characteristics

Contact Resistance:

Before Durability Test: 30 Milliohms Max

After Durability Test: 60 Milliohms Max

Insulation Resistance: 100 Megohms Min. at 500V DC

Dielectric Strength: 250V AC for 1 Minute

Operating Temperature: -25°C to +80°C

* Only Available in Right Angle

RCA PHONO JACKS

KLP Series

Ordering Information

KLP	—	0848A-2	—	B
Series		Type		Color

Series

KLP - RCA Phono Jack

KLPHT - Reflow Compatible Version

Type

0848-2 - Single, Vertical

0848A-2 - Single, Right Angle




Colors

B - Black R - Red W - White Y - Yellow O - Orange




KLP Series Dimensions

Dimensions in mm

KLP-0848A-2



KLP-0848-2



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KLP-0848-2-R-G](#) [KLP-0848A-2-W-G](#) [KLPHT-0848A-2-Y](#) [KLPHT-0848A-2-W](#) [KLPHT-0848A-2-B](#) [KLPHT-0848A-2-R](#)
[KLP-0848A-2-B-G](#) [KLP-0848-2-W-G](#) [KLP-0848A-2-Y](#) [KLP-0848A-2-B](#) [KLP-0848A-2-O](#) [KLP-0848A-2-W](#) [KLP-](#)
[0848A-2-R](#) [KLP-0848A-2-R-G](#) [KLP-0848-2-R](#) [KLP-0848-2-W](#) [KLP-0848-2-B](#) [KLP-0848-2-Y](#) [KLP-0848A-2-Y-G](#) [KLP-](#)
[0848-2-B-G](#) [KLP-0848-2-Y-G](#)