



X8R/X8L Dielectric

General Specifications



AVX has developed a range of multilayer ceramic capacitors designed for use in applications up to 150°C. These capacitors are manufactured with an X8R and an X8L dielectric material. X8R material has capacitance variation of $\pm 15\%$ between -55°C and +150°C. The X8L material has capacitance variation of $\pm 15\%$ between -55°C to 125°C to 125°C and +15/40% from +125°C to +150°C.

The need for X8R and X8L performance has been driven by customer requirements for parts that operate at elevated temperatures. They provide a highly reliable capacitor with low loss and stable capacitance over temperature.

They are ideal for automotive under the hood sensors, and various industrial applications. Typical industrial application would be drilling monitoring system. They can also be used as bulk capacitors for high temperature camera modules.

Both X8R and X8L dielectric capacitors are automotive AEC-Q200 qualified. Optional termination systems, tin, FLEXITERM® and conductive epoxy for hybrid applications are available. Providing this series with our FLEXITERM® termination system provides further advantage to customers by way of enhanced resistance to both, temperature cycling and mechanical damage.

0805	5	A	104	K	4	T	2	A
Size	Voltage	Dielectric	Capacitance Code (in pF)	Capacitance Tolerance	Failure Rate	Terminations	Packaging	Special Code
0402 0603 0805 1206	10V = Z 16V = Y 25V = 3 50V = 5 100V = 1	X8R = F X8L = L	2 Sig. Digits + Number of Zeros e.g. 10 F = 106	J = $\pm 5\%$ K = $\pm 10\%$ M = $\pm 20\%$	4=Automotive A = Not Applicable	T = Plated Ni and Sn Z = FLEXITERM®**	2 = 7" Reel 4 = 13" Reel	A = Std. Product

NOTE: Contact factory for availability of Termination and Tolerance Options for Specific Part Numbers.

X8R

Style	0603			0805			1206	
	Reflow/Wave			Reflow/Wave			Reflow/Wave	
	25V	50V	100V	25V	50V	100V	25V	50V
221				J	J	J		
271	G	G		J	J	J		
331	G	G		J	J	J		
471	G	G	G	J	J	J		
681	G	G	G	J	J	J		
102	G	G	G	J	J	J	J	J
152	G	G	G	J	J	J	J	J
222	G	G	G	J	J	J	J	J
332	G	G	G	J	J	J	J	J
472	G	G	G	J	J	J	J	J
682	G	G	G	J	J	J	J	J
103	G	G	G	J	J	J	J	J
153	G	G		J	J	N	J	J
223	G	G		J	J	N	J	J
333	G	G		J	J		J	J
473	G	G		J	J		J	J
683	G			N	N		M	M
104				N	N		M	M
154				N	N		M	M
224				N			M	M
334							M	M
474							M	Q
684							Q	Q
105							Q	Q
Style	0603			0805			1206	

Size	0603	0805	1206	1210	
Soldering	Reflow/Wave	Reflow/Wave	Reflow/Wave	Reflow/Wave	
Packaging	All Paper	Paper/Embossed	Paper/Embossed	Paper/Embossed	
(L) Length	mm (in)	1.60 ± 0.15 (0.063 ± 0.006)	2.01 ± 0.20 (0.079 ± 0.008)	3.20 ± 0.20 (0.126 ± 0.008)	3.30 ± 0.4 (0.130 ± 0.016)
(W) Width	mm (in)	0.81 ± 0.15 (0.032 ± 0.006)	1.25 ± 0.20 (0.049 ± 0.008)	1.60 ± 0.20 (0.063 ± 0.008)	2.50 ± 0.20 (0.098 ± 0.008)
(t) Terminal	mm (in)	0.35 ± 0.15 (0.014 ± 0.006)	0.50 ± 0.25 (0.020 ± 0.010)	0.50 ± 0.25 (0.020 ± 0.010)	0.50 ± 0.25 (0.020 ± 0.010)

X8L

Size			0603			0805			1206				1210		
Soldering			Reflow/Wave			Reflow/Wave			Reflow/Wave				Reflow/Wave		
		WVDC	25V	50V	100V	25V	50V	100V	16V	25V	50V	100V	10V	50V	100V
271	Cap (pF)	270	G	G											
331		330	G	G	G	J	J	J							
471		470	G	G	G	J	J	J							
681		680	G	G	G	J	J	J							
102		1000	G	G	G	J	J	J		J	J				
152		1500	G	G	G	J	J	J		J	J	J			
182		1800	G	G	G	J	J	J		J	J	J			
222		2200	G	G	G	J	J	J		J	J	J			
272		2700	G	G	G	J	J	J		J	J	J			
332		3300	G	G	G	J	J	J		J	J	J			
392		3900	G	G	G	J	J	J		J	J	J			
472		4700	G	G	G	J	J	J		J	J	J			
562		5600	G	G	G	J	J	J		J	J	J			
682		6800	G	G	G	J	J	J		J	J	J			
822		8200	G	G	G	J	J	J		J	J	J			
103	Cap (µF)	0.01	G	G	G	J	J	J		J	J	J			
123		0.012	G	G		J	J	J		J	J	J			
153		0.015	G	G		J	J	J		J	J	J			
183		0.018	G	G		J	J	J		J	J	J			
223		0.022	G	G		J	J	J		J	J	J			
273		0.027	G	G		J	J	J		J	J	J			
333		0.033	G	G		J	J	N		J	J	J			
393		0.039	G	G		J	J	N		J	J	J			
473		0.047	G	G		J	J	N		J	J	J			
563		0.056	G	G		J	J	N		J	J	J			
683		0.068	G	G		J	J	N		J	J	J			
823		0.082	G	G		J	J	N		J	J	J			
104		0.1	G	G		J	J	N		J	J	M			
124		0.12				J	N			J	J	M			
154		0.15				J	N		J	J	J	Q			
184		0.18				N	N		J	J	J	Q			
224		0.22				N	N		J	J	J	Q			
274		0.27				N			J	M	M	Q			
334		0.33				N			J	M	M	Q			
394		0.39				N			M	M	P	Q			
474		0.47				N			M	M	P	Q			
684		0.68				N			M	M	P	Q			
824		0.82				N			M	M	P	Q			
105		1				N			M	M	P	Q			
155		1.5							M	M					
225		2.2							M	M				Z	Z
475													Z		
106													Z		
		WVDC	25V	50V	100V	25V	50V	100V	16V	25V	50V	100V	10V	50V	100V
SIZE			0603			0805			1206				1210		

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (-0.013)	0.56 (-0.022)	0.71 (-0.028)	0.9 (-0.035)	0.94 (-0.037)	1.02 (-0.04)	1.27 (-0.05)	1.4 (-0.055)	1.52 (-0.06)	1.78 (-0.07)	2.29 (-0.09)	2.54 (-0.1)	2.79 (-0.11)
PAPER						EMBOSSD							

X8R/X8L Dielectric

General Specifications


APPLICATIONS FOR X8R AND X8L CAPACITORS

- All market sectors with a 150°C requirement
- Automotive on engine applications
- Oil exploration applications
- Hybrid automotive applications
 - Battery control
 - Inverter / converter circuits
 - Motor control applications
 - Water pump
- Hybrid commercial applications
 - Emergency circuits
 - Sensors
 - Temperature regulation




ADVANTAGES OF X8R AND X8L MLC CAPACITORS

- Both ranges are qualified to the highest automotive AEC-Q200 standards
- Excellent reliability compared to other capacitor technologies
- RoHS compliant
- Low ESR / ESL compared to other technologies
- Tin solder finish
- FLEXITERM[®] available
- Epoxy termination for hybrid available
- 100V range available




ENGINEERING TOOLS FOR HIGH VOLTAGE MLC CAPACITORS

- Samples
- Technical Articles
- Application Engineering
- Application Support



X8R/X8L Dielectric

Specifications and Test Methods

Parameter/Test		X8R/X8L Specification Limits	Measuring Conditions	
Operating Temperature Range		-55°C to +150°C	Temperature Cycle Chamber	
Capacitance		Within specified tolerance	Freq.: 1.0 kHz $\pm$ 10% Voltage: 1.0Vrms $\pm$.2V	
Dissipation Factor		$\leq$ 2.5% for $\geq$ 50V DC rating $\leq$ 3.5% for 25V DC and 16V DC rating		
Insulation Resistance		100,000M Ω or 1000M Ω - μ F, whichever is less	Charge device with rated voltage for 120 $\pm$ 5 secs @ room temp/humidity	
Dielectric Strength		No breakdown or visual defects	Charge device with 250% of rated voltage for 1-5 seconds, w/charge and discharge current limited to 50 mA (max) Note: Charge device with 150% of rated voltage for 500V devices.	
Resistance to Flexure Stresses	Appearance	No defects	Deflection: 2mm Test Time: 30 seconds 1mm/sec 	
	Capacitance Variation	$\leq \pm 12\%$		
	Dissipation Factor	Meets Initial Values (As Above)		
	Insulation Resistance	$\geq$ Initial Value x 0.3		
Solderability		$\geq$ 95% of each terminal should be covered with fresh solder	Dip device in eutectic solder at 230 $\pm$ 5°C for 5.0 $\pm$ 0.5 seconds	
Resistance to Solder Heat	Appearance	No defects, <25% leaching of either end terminal	Dip device in eutectic solder at 260°C for 60 seconds. Store at room temperature for 24 $\pm$ 2 hours before measuring electrical properties.	
	Capacitance Variation	$\leq \pm 7.5\%$		
	Dissipation Factor	Meets Initial Values (As Above)		
	Insulation Resistance	Meets Initial Values (As Above)		
	Dielectric Strength	Meets Initial Values (As Above)		
Thermal Shock	Appearance	No visual defects	Step 1: -55°C $\pm$ 2°	30 $\pm$ 3 minutes
	Capacitance Variation	$\leq \pm 7.5\%$	Step 2: Room Temp	$\leq$ 3 minutes
	Dissipation Factor	Meets Initial Values (As Above)	Step 3: +125°C $\pm$ 2°	30 $\pm$ 3 minutes
	Insulation Resistance	Meets Initial Values (As Above)	Step 4: Room Temp	$\leq$ 3 minutes
	Dielectric Strength	Meets Initial Values (As Above)	Repeat for 5 cycles and measure after 24 $\pm$ 2 hours at room temperature	
Load Life	Appearance	No visual defects	Charge device with 1.5 rated voltage ($\leq$ 10V) in test chamber set at 150°C $\pm$ 2°C for 1000 hours (+48, -0) Remove from test chamber and stabilize at room temperature for 24 $\pm$ 2 hours before measuring.	
	Capacitance Variation	$\leq \pm 12.5\%$		
	Dissipation Factor	$\leq$ Initial Value x 2.0 (See Above)		
	Insulation Resistance	$\geq$ Initial Value x 0.3 (See Above)		
	Dielectric Strength	Meets Initial Values (As Above)		
Load Humidity	Appearance	No visual defects	Store in a test chamber set at 85°C $\pm$ 2°C/ 85% $\pm$ 5% relative humidity for 1000 hours (+48, -0) with rated voltage applied. Remove from chamber and stabilize at room temperature and humidity for 24 $\pm$ 2 hours before measuring..	
	Capacitance Variation	$\leq \pm 12.5\%$		
	Dissipation Factor	$\leq$ Initial Value x 2.0 (See Above)		
	Insulation Resistance	$\geq$ Initial Value x 0.3 (See Above)		
	Dielectric Strength	Meets Initial Values (As Above)		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera AVX:

06035F102K4T2A	08055F103K4T2A	12065F104K4T2A	06035F103J4T2A	08053F104K4T2A	08055F104K4T2A
08055F331K4T2A	08055F473K4T2A	12063F103K4T2A	12063F104K4T2A	12063F333K4T2A	12065F333K4T2A
08053F224KAT2A	06035F333J4T2A	06033F103K4T2A	12065F334KAT2A	06035F393KAT2A	06035F102J4T2A
06035F472KAT2A	12065F224K4Z2A	06033F473K4T2A	08053F103K4T2A	12063F104M4T2A	12065F104M4T2A
06035F103KAT2A	06035F103K4T2A	12065F103K4T2A	06035F472K4T2A	12065F334K4T2A	06035F333K4T2A
08055F223K4T2A	08055F222K4T2A	06035F473K4T2A	06033F683K4T2A	08055F102K4T2A	08055F333K4T2A
08055F683K4T2A	12063F474K4T2A	12065F224K4T2A	06035F223K4T2A	12065F473K4T2A	06035F332K4T2A
06035F103M4T2A	06033F102KAT2A	06033F393KAT2A	06033F563K4T2A	06035F102KAT2A	12063F334KAT2A
06033F103KAT2A	06035L104K4T2A	12065L474K4T2A	12061L104K4T2A	08051L333K4T2A	08053L334K4T2A
08055L224K4T2A	08053F102KAT2A	08055F102KAT2A	08055L472K4T2A	06033F473KAT2A	06035F682J4T2A
12063F104KAT2A	12065F104KAT2A	08053F103K4Z2A	06035F103K4Z2A	06033F683J4Z2A	06035F472J4Z2A
06035F103M4Z2A	08053F104K4Z2A	06033F104J4Z2A	06035F473J4Z2A	08055F104K4Z2A	08055F103K4Z2A
06035F473K4Z2A	08053F224K4Z2A	06035F331K4Z2A	06035F152K4Z2A	06035F102K4Z2A	08055F681K4Z2A
06035F473K4U2A	08055F104KAT2A	08053F104KAT2A	06033L104K4T2A	12063F474K4Z2A	08055F104K4Z4A
08055F471K4Z2A	12063F474M4Z2A	08053F104K4Z4A	08055F103KAT2A	08055F152KAT2A	06035L104K4Z2A
12065L105K4T2A	08055F153J4T2A	06035F102K4T4A	08055F472K4T2A	06035F102K4Z4A	08053F102K4T2A
08055F683K4T4A	08055F103K4T4A	08053F223K4T2A	06035F153K4T4A		