





A1



PROJECT NO.
B916823
A98-52300

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE DWN APVD
A1	-	D1	SEE PCN EG00-2505-00-1		20OCT2000 REH VB
		D2	SEE PCN EG00-0134-01-2		11JAN2001 REH VB
		E	SEE PCN EG00-0553-03-2		17FEB2003 LN REH
		E1	SEE PCN EG00-1054-03-1		24MAR2003 LN REH



CODING Z AS DRAWN

D2



NOTES
Bemerkungen

- 1 AMP-LOGO
AMP-Logo
- 2 ORDER-NUMBER
Bestell-Nummer
- 3 REVISIONS-NUMBER
Werkzeugänderungsindex
- 4 -
- 5 CAVITY MARKING
Nestmarkierung
- 6 PACKAGING IN LAYERS ACC. TO AMP-SPEC. 107-18032-300
Lagenverpackung nach AMP-Spez. 107-18032-300
- 7 MATERIAL MARKING
Werkstoffkennzeichnung
- 8 PIN TIPS ACC. TO TYCO SPEC. 114-18063
Tabspitzen nach Tyco Spez.
- 9 ELECTRICAL VALUES ACC. TO 114-18021
elektrische Werte nach

MATING WITH
Passend zu

929051-1 - COVER WITH LEVER
967671-1/-3 - COVER WITH LEVER
968473-1 - MQS SOCKET HSG.

E	1355505-4	A	B	3.6	MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 μ m)	3
					MODU II PIN	6	CuFe2	TIN PLATED (MIN. THICKN. 1 μ m)	2
D	1355505-3	A	B	2.8	HOUSING	1	PA6(GB20+GF10)	LIGHTGREY	1
					MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 μ m)	3
A1	1355505-2	A	A	2.8	MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 μ m)	2
					HOUSING	1	PA6(GB20+GF10)	BLUE	1
D2	1355505-1	D	Z	2.8	MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 μ m)	3
					MODU II PIN	6	CuSn6	TIN PLATED (MIN. THICKN. 2 μ m)	2
C	Assy No.	Rev.Cod.	"L"	Description	Pcs.	Material	Surface Finish	No.	1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN M. Reinhardt 17MAY99
DIMENSIONS: mm				CHK M. Reinhardt 19MAY99
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD -
0 PLC ± 0.5 1 PLC ± 0.5 2 PLC ± 0.5 3 PLC ± 0.5 4 PLC ± 0.5 ANGLES ± 0.5 FINISH				PRODUCT SPEC 108-18671-0 APPLICATION SPEC 114-18314-0 WEIGHT -
MATERIAL				CUSTOMER DRAWING

AMP Deutschland GmbH D - 63225 Langen				NAME 12POS. MQS PIN HEADER 90°, ASSY 12pol.MQS Stiftleiste 90°, Assy
SIZE A2	CAGE CODE 00779	DRAWING NO. C-1355505	RESTRICTED TO -	REV E1
SCALE 5.1				SHEET 1