


# Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

## 2000 Hour Long Life, General Purpose Aluminum Electrolytic



Type SK is a radial leaded aluminum electrolytic capacitor with a +85 °C, 2000 hour long life rating. The SK is a high CV rated product and is ideal for general purpose applications such as stereo radio, TV, computers and other consumer electronic products.

### Highlights

- +85 °C
- 2000 hours - long life
- High CV
- Available in T&R and ammo pack


### Specifications

| Capacitance Range                               | 0.47 to 15,000 μF                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
|-------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------|-------|----|----|----|-----|---------|---------|--|------------|--------------------|----|----|----|------|-------|------|-------|---------|---------|-------|-----|-----|-----------|------|-----|-----|-----|------------|------|-----|-----|-----|---------------------|-------------------|--------|------|--------|------|--------|------|
| Capacitance Tolerance                           | ±20%                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| Rated Voltage                                   | 6.3 to 450 Vdc                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| Operating Temperature Range                     | -40 °C to +85 °C; 6.3 to 100 Vdc<br>-25 °C to +85 °C; 160 to 450 Vdc                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| DC Leakage Current                              | 6.3 to 100 Vdc; I = ≤.01CV or 3 μA Max<br>Whichever is greater after 2 minutes application of DC working voltage at 20 °C<br>≥100 Vdc; I = ≤.03CV or 10 μA Max<br>Whichever is greater after 2 minutes application of DC working voltage at 20 °C<br>C = Capacitance in (μF)<br>V = Rated voltage<br>I = Leakage current in μA                                                                                                                                                                                                                                                                                                                                                                           |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| Dissipation Factor @ 120 Hz, +20 °C             | <table><tr><td>WV (V)</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td><td>63</td><td>100</td><td>160-250</td><td>350-450</td></tr><tr><td>DF(%)</td><td>24</td><td>20</td><td>16</td><td>14</td><td>12</td><td>10</td><td>10</td><td>10</td><td>20</td><td>24</td></tr></table>                                                                                                                                                                                                                                                                                                                                                                                                   |       |      |       |    |    |    |     |         |         |  | WV (V)     | 6.3                | 10 | 16 | 25 | 35   | 50    | 63   | 100   | 160-250 | 350-450 | DF(%) | 24  | 20  | 16        | 14   | 12  | 10  | 10  | 10         | 20   | 24  |     |     |                     |                   |        |      |        |      |        |      |
| WV (V)                                          | 6.3                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | 10    | 16   | 25    | 35 | 50 | 63 | 100 | 160-250 | 350-450 |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| DF(%)                                           | 24                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       | 20    | 16   | 14    | 12 | 10 | 10 | 10  | 20      | 24      |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| Ripple Multipliers for Voltage and Temperature: | <table><tr><th rowspan="2">Rated WVDC</th><th colspan="4">Ripple Multipliers</th></tr><tr><th>60Hz</th><th>120Hz</th><th>1kHz</th><th>10kHz</th></tr><tr><td>6 to 25</td><td>0.80</td><td>1.0</td><td>1.1</td><td>1.2</td></tr><tr><td>35 to 100</td><td>0.75</td><td>1.0</td><td>1.3</td><td>1.4</td></tr><tr><td>160 to 250</td><td>0.70</td><td>1.0</td><td>1.4</td><td>1.6</td></tr></table> <p>For capacitance values &gt; 1000 μF, the DF (%) value is increased 2% for every additional 1000 μF</p> <table><tr><th>Ambient Temperature</th><th>Ripple Multiplier</th></tr><tr><td>+85 °C</td><td>1.00</td></tr><tr><td>+75 °C</td><td>1.14</td></tr><tr><td>+65 °C</td><td>1.25</td></tr></table> |       |      |       |    |    |    |     |         |         |  | Rated WVDC | Ripple Multipliers |    |    |    | 60Hz | 120Hz | 1kHz | 10kHz | 6 to 25 | 0.80    | 1.0   | 1.1 | 1.2 | 35 to 100 | 0.75 | 1.0 | 1.3 | 1.4 | 160 to 250 | 0.70 | 1.0 | 1.4 | 1.6 | Ambient Temperature | Ripple Multiplier | +85 °C | 1.00 | +75 °C | 1.14 | +65 °C | 1.25 |
| Rated WVDC                                      | Ripple Multipliers                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
|                                                 | 60Hz                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | 120Hz | 1kHz | 10kHz |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| 6 to 25                                         | 0.80                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | 1.0   | 1.1  | 1.2   |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| 35 to 100                                       | 0.75                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | 1.0   | 1.3  | 1.4   |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| 160 to 250                                      | 0.70                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     | 1.0   | 1.4  | 1.6   |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| Ambient Temperature                             | Ripple Multiplier                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| +85 °C                                          | 1.00                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| +75 °C                                          | 1.14                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| +65 °C                                          | 1.25                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| Load Life Test                                  | Apply WVDC for 2000 hours at +85 °C<br>Capacitance change within 20% of initial limit<br>DF not to exceed 200% of initial requirement<br>Leakage current not to exceed 200% of initial                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| Shelf Life Test                                 | 1000 hrs at +85 °C with no voltage applied<br>Cap change within ±20% of initial values<br>DF not to exceed 200% of initial requirement<br>DC leakage current meets initial requirement                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |
| RoHS Compliant                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |       |      |       |    |    |    |     |         |         |  |            |                    |    |    |    |      |       |      |       |         |         |       |     |     |           |      |     |     |     |            |      |     |     |     |                     |                   |        |      |        |      |        |      |

# Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

## Outline Drawing

### Outline Dimensions (Millimeters)





Case vented on diameters 6.3 and greater

sleeve adds .5 Max. to diameter and 2.0 Max. to length




## Part Numbering System

| SK   | 100         | M                     | 100           | S                            | T                           |
|------|-------------|-----------------------|---------------|------------------------------|-----------------------------|
| Type | Capacitance | Capacitance Tolerance | Rated Voltage | Packaging                    | Lead Configuration          |
|      | ( $\mu$ F)  | (%)                   | (Vdc)         |                              |                             |
| SK   | 1R0 = 1     | K = $\pm 10$          | 6R3 = 6.3     | A = Tape & Ammo              | 1 = Lead cut                |
|      | 100 = 10    | M = $\pm 20$          | 010 = 10      | E = Different Characteristic | 2 = Lead form               |
|      | 101 = 100   |                       | 100 = 100     | R = Tape & Reel              | 4 = Lead crimp & cut (form) |
|      | 102 = 1000  |                       |               | S = Standard                 | T = Standard                |

## Temperature Characteristics



## Load Life Characteristics



# Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

## Ratings

| Cap<br>(μF)             | Catalog<br>Part Number | Max ESR<br>120 Hz<br>+25 °C<br>(Ω) | Max Ripple<br>120 Hz<br>+85 °C<br>(mA) | Size in. (mm)   |               |                   |                  |
|-------------------------|------------------------|------------------------------------|----------------------------------------|-----------------|---------------|-------------------|------------------|
|                         |                        |                                    |                                        | Diameter<br>(D) | Length<br>(L) | Lead Space<br>(S) | Lead Dia.<br>(d) |
| 6.3 Vdc (8 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 100                     | SK101M6R3ST            | 2.92                               | 130                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 220                     | SK221M6R3ST            | 1.33                               | 240                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 330                     | SK331M6R3ST            | 0.88                               | 300                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 470                     | SK471M6R3ST            | 0.62                               | 380                                    | .315 (8.0)      | .453 (11.5)   | .138 (3.5)        | .0236 (0.6)      |
| 1000                    | SK102M6R3ST            | 0.29                               | 580                                    | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 2200                    | SK222M6R3ST            | 0.14                               | 1050                                   | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 3300                    | SK332M6R3ST            | 0.10                               | 1250                                   | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 4700                    | SK472M6R3ST            | 0.08                               | 1700                                   | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 6800                    | SK682M6R3ST            | 0.07                               | 1900                                   | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 10000                   | SK103M6R3ST            | 0.05                               | 2250                                   | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 15000                   | SK153M6R3ST            | 0.04                               | 2680                                   | .630 (16.0)     | 1.38 (35.0)   | .295 (7.5)        | .0315 (0.8)      |
| 10 Vdc (13 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 33                      | SK330M010ST            | 7.64                               | 80                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 47                      | SK470M010ST            | 5.36                               | 95                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 100                     | SK101M010ST            | 2.52                               | 180                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 220                     | SK221M010ST            | 1.15                               | 250                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 330                     | SK331M010ST            | 0.76                               | 330                                    | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 470                     | SK471M010ST            | 0.54                               | 400                                    | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 1000                    | SK102M010ST            | 0.25                               | 630                                    | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 2200                    | SK222M010ST            | 0.14                               | 1100                                   | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 3300                    | SK332M010ST            | 0.10                               | 1400                                   | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 4700                    | SK472M010ST            | 0.08                               | 1800                                   | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 6800                    | SK682M010ST            | 0.07                               | 2150                                   | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 10000                   | SK103M010ST            | 0.05                               | 2500                                   | .709 (18.0)     | 1.38 (35.0)   | .295 (7.5)        | .0315 (0.8)      |
| 15000                   | SK153M010ST            | 0.04                               | 2950                                   | .709 (18.0)     | 1.65 (42.0)   | .295 (7.5)        | .0315 (0.8)      |
| 16 Vdc (20 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 22                      | SK220M016ST            | 9.65                               | 75                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 33                      | SK330M016ST            | 6.43                               | 110                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 47                      | SK470M016ST            | 4.52                               | 130                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 100                     | SK101M016ST            | 2.12                               | 185                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 220                     | SK221M016ST            | 0.97                               | 320                                    | .315 (8.0)      | .453 (11.5)   | .138 (3.5)        | .0236 (0.6)      |
| 330                     | SK331M016ST            | 0.64                               | 360                                    | .315 (8.0)      | .453 (11.5)   | .138 (3.5)        | .0236 (0.6)      |
| 470                     | SK471M016ST            | 0.45                               | 470                                    | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 1000                    | SK102M016ST            | 0.21                               | 790                                    | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 2200                    | SK222M016ST            | 0.14                               | 1350                                   | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 3300                    | SK332M016ST            | 0.10                               | 1700                                   | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 4700                    | SK472M016ST            | 0.08                               | 2100                                   | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 6800                    | SK682M016ST            | 0.07                               | 2500                                   | .709 (18.0)     | 1.38 (35.0)   | .295 (7.5)        | .0315 (0.8)      |
| 10000                   | SK103M016ST            | 0.05                               | 2700                                   | .709 (18.0)     | 1.65 (42.0)   | .295 (7.5)        | .0315 (0.8)      |
| 25 Vdc (32 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 10                      | SK100M025ST            | 18.57                              | 50                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 22                      | SK220M025ST            | 8.44                               | 90                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 33                      | SK330M025ST            | 5.63                               | 110                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 47                      | SK470M025ST            | 3.95                               | 130                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 100                     | SK101M025ST            | 1.85                               | 185                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |

# Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

| Cap<br>(µF)             | Catalog<br>Part Number | Max ESR<br>120 Hz<br>+25 °C<br>(Ω) | Max Ripple<br>120 Hz<br>+85 °C<br>(mA) | Size in. (mm)   |               |                   |                  |
|-------------------------|------------------------|------------------------------------|----------------------------------------|-----------------|---------------|-------------------|------------------|
|                         |                        |                                    |                                        | Diameter<br>(D) | Length<br>(L) | Lead Space<br>(S) | Lead Dia.<br>(d) |
| 25 Vdc (32 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 220                     | SK221M025ST            | 0.84                               | 320                                    | .315 (8.0)      | .453 (11.5)   | .138 (3.5)        | .0236 (0.6)      |
| 330                     | SK331M025ST            | 0.56                               | 420                                    | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 470                     | SK471M025ST            | 0.39                               | 540                                    | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 1,000                   | SK102M025ST            | 0.18                               | 950                                    | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 2,200                   | SK222M025ST            | 0.14                               | 1550                                   | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 3,300                   | SK332M025ST            | 0.10                               | 1950                                   | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 4,700                   | SK472M025ST            | 0.08                               | 2360                                   | .709 (18.0)     | 1.38 (35.0)   | .295 (7.5)        | .0315 (0.8)      |
| 6,800                   | SK682M025ST            | 0.06                               | 2550                                   | .709 (18.0)     | 1.65 (42.0)   | .295 (7.5)        | .0315 (0.8)      |
| 35 Vdc (44 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 10                      | SK100M035ST            | 15.92                              | 60                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 22                      | SK220M035ST            | 7.23                               | 95                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 33                      | SK330M035ST            | 4.82                               | 115                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 47                      | SK470M035ST            | 3.38                               | 140                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 100                     | SK101M035ST            | 1.59                               | 230                                    | .315 (8.0)      | .453 (11.5)   | .138 (3.5)        | .0236 (0.6)      |
| 220                     | SK221M035ST            | 0.72                               | 370                                    | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 330                     | SK331M035ST            | 0.48                               | 490                                    | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 470                     | SK471M035ST            | 0.33                               | 640                                    | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 1,000                   | SK102M035ST            | 0.15                               | 1100                                   | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 2,200                   | SK222M035ST            | 0.14                               | 1800                                   | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 3,300                   | SK332M035ST            | 0.10                               | 2220                                   | .709 (18.0)     | 1.38 (35.0)   | .295 (7.5)        | .0315 (0.8)      |
| 4,700                   | SK472M035ST            | 0.08                               | 2400                                   | .709 (18.0)     | 1.65 (42.0)   | .295 (7.5)        | .0315 (0.8)      |
| 50 Vdc (63 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 0.47                    | SKR47M050ST            | 282.33                             | 5                                      | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 1.0                     | SK010M050ST            | 132.70                             | 10                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 2.2                     | SK2R2M050ST            | 60.32                              | 23                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 3.3                     | SK3R3M050ST            | 40.21                              | 35                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 4.7                     | SK4R7M050ST            | 28.23                              | 40                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 10                      | SK100M050ST            | 13.27                              | 65                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 22                      | SK220M050ST            | 6.03                               | 100                                    | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 33                      | SK330M050ST            | 4.02                               | 125                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 47                      | SK470M050ST            | 2.82                               | 150                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 100                     | SK101M050ST            | 1.33                               | 250                                    | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 220                     | SK221M050ST            | 0.60                               | 440                                    | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 330                     | SK331M050ST            | 0.40                               | 580                                    | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 470                     | SK471M050ST            | 0.28                               | 760                                    | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 1,000                   | SK102M050ST            | 0.13                               | 1350                                   | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 2,200                   | SK222M050ST            | 0.14                               | 2090                                   | .709 (18.0)     | 1.38 (35.0)   | .295 (7.5)        | .0315 (0.8)      |
| 3,300                   | SK332M050ST            | 0.10                               | 2320                                   | .709 (18.0)     | 1.65 (42.0)   | .295 (7.5)        | .0315 (0.8)      |
| 63 Vdc (79 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 0.47                    | SKR47M063ST            | 254.10                             | 5                                      | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 1.0                     | SK010M063ST            | 119.43                             | 10                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 2.2                     | SK2R2M063ST            | 54.28                              | 29                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 3.3                     | SK3R3M063ST            | 36.19                              | 40                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 4.7                     | SK4R7M063ST            | 25.41                              | 45                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 10.0                    | SK100M063ST            | 11.94                              | 70                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |

\* Note max leakage current ≥100 Vdc is measured at 3 minutes

Parts highlighted in yellow are obsolete.

# Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

| Cap<br>(µF)               | Catalog<br>Part Number | Max ESR<br>120 Hz<br>+25 °C<br>(Ω) | Max Ripple<br>120 Hz<br>+85 °C<br>(mA) | Size in. (mm)   |               |                   |                  |
|---------------------------|------------------------|------------------------------------|----------------------------------------|-----------------|---------------|-------------------|------------------|
|                           |                        |                                    |                                        | Diameter<br>(D) | Length<br>(L) | Lead Space<br>(S) | Lead Dia.<br>(d) |
| 63 Vdc (79 Volts Surge)   |                        |                                    |                                        |                 |               |                   |                  |
| 22                        | SK220M063ST            | 5.43                               | 115                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 33                        | SK330M063ST            | 3.62                               | 140                                    | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 47                        | SK470M063ST            | 2.54                               | 190                                    | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 100                       | SK101M063ST            | 1.19                               | 300                                    | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 220                       | SK221M063ST            | 0.54                               | 490                                    | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 330                       | SK331M063ST            | 0.36                               | 680                                    | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 470                       | SK471M063ST            | 0.25                               | 880                                    | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 1,000                     | SK102M063ST            | 0.12                               | 1550                                   | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 100 Vdc (125 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 0.47                      | SKR47M100ST            | 225.87                             | 10                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 1                         | SK010M100ST            | 106.16                             | 21                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 2.2                       | SK2R2M100ST            | 48.25                              | 30                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 3.3                       | SK3R3M100ST            | 32.17                              | 40                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 4.7                       | SK4R7M100ST            | 22.59                              | 50                                     | .197 (5.0)      | .433 (11.0)   | .079 (2.0)        | .0197 (0.5)      |
| 10                        | SK100M100ST            | 10.62                              | 75                                     | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 22                        | SK220M100ST            | 4.83                               | 130                                    | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 33                        | SK330M100ST            | 3.22                               | 170                                    | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 47                        | SK470M100ST            | 2.26                               | 230                                    | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 100                       | SK101M100ST            | 1.06                               | 400                                    | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 220                       | SK221M100ST            | 0.48                               | 710                                    | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 330                       | SK331M100ST            | 0.32                               | 860                                    | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 470                       | SK471M100ST            | 0.23                               | 1100                                   | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 160 Vdc (200 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 0.47                      | SKR47M160ST            | 423.50                             | 12.0                                   | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 1.0                       | SK010M160ST            | 199.04                             | 17.0                                   | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 2.2                       | SK2R2M160ST            | 90.47                              | 26.0                                   | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 3.3                       | SK3R3M160ST            | 60.32                              | 35.0                                   | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 4.7                       | SK4R7M160ST            | 42.35                              | 40.0                                   | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 10                        | SK100M160ST            | 19.90                              | 65.0                                   | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 22                        | SK220M160ST            | 9.05                               | 110.0                                  | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 33                        | SK330M160ST            | 6.03                               | 150.0                                  | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 47                        | SK470M160ST            | 4.23                               | 180.0                                  | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 100                       | SK101M160ST            | 1.99                               | 300.0                                  | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 220                       | SK221M160ST            | 0.90                               | 510.0                                  | .630 (16.0)     | 1.42 (36.0)   | .295 (7.5)        | .0315 (0.8)      |
| 330                       | SK331M160ST            | 0.60                               | 600.0                                  | .709 (18.0)     | 1.65 (42.0)   | .295 (7.5)        | .0315 (0.8)      |
| 200 Vdc (250 Volts Surge) |                        |                                    |                                        |                 |               |                   |                  |
| 0.47                      | SKR47M200ST            | 423.50                             | 12                                     | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 1.0                       | SK010M200ST            | 199.04                             | 17                                     | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 2.2                       | SK2R2M200ST            | 90.47                              | 26                                     | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 3.3                       | SK3R3M200ST            | 60.32                              | 35                                     | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 4.7                       | SK4R7M200ST            | 42.35                              | 45                                     | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 10                        | SK100M200ST            | 19.90                              | 70                                     | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 22                        | SK220M200ST            | 9.05                               | 110                                    | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 33                        | SK330M200ST            | 6.03                               | 160                                    | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 47                        | SK470M200ST            | 4.23                               | 180                                    | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |

\* Note max leakage current ≥100 Vdc is measured at 3 minutes

Parts highlighted in yellow are obsolete.

# Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

| Cap<br>(μF)               | Catalog<br>Part Number | Max ESR                 | Max Ripple               | Size in. (mm)   |               |                   |                  |
|---------------------------|------------------------|-------------------------|--------------------------|-----------------|---------------|-------------------|------------------|
|                           |                        | 120 Hz<br>+25 °C<br>(Ω) | 120 Hz<br>+85 °C<br>(mA) | Diameter<br>(D) | Length<br>(L) | Lead Space<br>(S) | Lead Dia.<br>(d) |
| 200 Vdc (250 Volts Surge) |                        |                         |                          |                 |               |                   |                  |
| 100                       | SK101M200ST            | 1.99                    | 330                      | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 220                       | SK221M200ST            | 0.90                    | 520                      | .709 (18.0)     | 1.65 (42.0)   | .295 (7.5)        | .0315 (0.8)      |
| 250 Vdc (300 Volts Surge) |                        |                         |                          |                 |               |                   |                  |
| 0.47                      | SKR47M250ST            | 423.50                  | 12                       | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 1.0                       | SK010M250ST            | 199.04                  | 17                       | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 2.2                       | SK2R2M250ST            | 90.47                   | 30                       | .248 (6.3)      | .433 (11.0)   | .098 (2.5)        | .0197 (0.5)      |
| 3.3                       | SK3R3M250ST            | 60.32                   | 35                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 4.7                       | SK4R7M250ST            | 42.35                   | 45                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 10                        | SK100M250ST            | 19.90                   | 70                       | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 22                        | SK220M250ST            | 9.05                    | 130                      | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 33                        | SK330M250ST            | 6.03                    | 160                      | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 47                        | SK470M250ST            | 4.23                    | 210                      | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 100                       | SK101M250ST            | 1.99                    | 310                      | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 350 Vdc (400 Volts Surge) |                        |                         |                          |                 |               |                   |                  |
| 0.47                      | SKR47M350ST            | 564.67                  | 14                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 1.0                       | SK010M350ST            | 265.39                  | 18                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 2.2                       | SK2R2M350ST            | 120.63                  | 28                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 3.3                       | SK3R3M350ST            | 80.42                   | 35                       | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 4.7                       | SK4R7M350ST            | 56.47                   | 40                       | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 10                        | SK100M350ST            | 26.54                   | 70                       | .394 (10.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 22                        | SK220M350ST            | 12.06                   | 110                      | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 33                        | SK330M350ST            | 8.04                    | 140                      | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 47                        | SK470M350ST            | 5.65                    | 220                      | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 100                       | SK101M350ST            | 2.65                    | 360                      | .709 (18.0)     | 1.42 (36.0)   | .295 (7.5)        | .0315 (0.8)      |
| 400 Vdc (450 Volts Surge) |                        |                         |                          |                 |               |                   |                  |
| 0.47                      | SKR47M400ST            | 564.67                  | 14                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 1.0                       | SK010M400ST            | 265.39                  | 18                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 2.2                       | SK2R2M400ST            | 120.63                  | 28                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 3.3                       | SK3R3M400ST            | 80.42                   | 32                       | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 4.7                       | SK4R7M400ST            | 56.47                   | 41                       | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 10                        | SK100M400ST            | 26.54                   | 70                       | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 22                        | SK220M400ST            | 12.06                   | 120                      | .512 (13.0)     | .984 (26.0)   | .197 (5.0)        | .0236 (0.6)      |
| 33                        | SK330M400ST            | 8.04                    | 140                      | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 47                        | SK470M400ST            | 5.65                    | 160                      | .630 (16.0)     | 1.26 (32.0)   | .295 (7.5)        | .0315 (0.8)      |
| 450 Vdc (500 Volts Surge) |                        |                         |                          |                 |               |                   |                  |
| 0.47                      | SKR47M450ST            | 564.67                  | 14                       | .315 (8.0)      | .433 (11.0)   | .138 (3.5)        | .0236 (0.6)      |
| 1.0                       | SK010M450ST            | 265.39                  | 19                       | .315 (8.0)      | .453 (11.5)   | .138 (3.5)        | .0236 (0.6)      |
| 2.2                       | SK2R2M450ST            | 120.63                  | 29                       | .394 (10.0)     | .512 (13.0)   | .197 (5.0)        | .0236 (0.6)      |
| 3.3                       | SK3R3M450ST            | 80.42                   | 35                       | .394 (10.0)     | .630 (16.0)   | .197 (5.0)        | .0236 (0.6)      |
| 4.7                       | SK4R7M450ST            | 56.47                   | 50                       | .394 (10.0)     | .709 (18.0)   | .197 (5.0)        | .0236 (0.6)      |
| 10                        | SK100M450ST            | 26.54                   | 75                       | .512 (13.0)     | .827 (21.0)   | .197 (5.0)        | .0236 (0.6)      |
| 22                        | SK220M450ST            | 12.06                   | 110                      | .630 (16.0)     | .984 (25.0)   | .295 (7.5)        | .0315 (0.8)      |
| 33                        | SK330M450ST            | 8.04                    | 150                      | .630 (16.0)     | 1.42 (36.0)   | .295 (7.5)        | .0315 (0.8)      |
| 47                        | SK470M450ST            | 5.65                    | 230                      | .630 (16.0)     | 1.57 (40.0)   | .295 (7.5)        | .0315 (0.8)      |

Parts highlighted in yellow are obsolete.

# Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

## Taping & Packaging

Fig. 1 - Formed Taping




Fig. 2 - Straight Taping (5φ, 6.3φ, 8φ)




Fig. 3- Straight Taping (Under 10φ, 12φ, 13φ)






Fig. 4- Straight Taping (16φ, 18φ)



Standard Lead Spacing of Taped Components is 5mm  
Other Lead Spacing is Available by Special Order

| Code      | D       | A    | d     | P    | P <sub>0</sub> | P <sub>1</sub> | P <sub>2</sub> | F            | W    | W <sub>0</sub> | H     | H <sub>0</sub> | D <sub>0</sub> | t    | ih   | Fig. |
|-----------|---------|------|-------|------|----------------|----------------|----------------|--------------|------|----------------|-------|----------------|----------------|------|------|------|
| Tolerance | 0.5     | 1.0  | ±0.05 | ±1.0 | ±0.2           | ±0.7           | ±1.3           | +0.8<br>-0.2 | ±0.5 | Min.           | ±0.75 | ±0.5           | ±0.2           | ±0.2 | Max. |      |
| Item      | 4 ~ 6.3 | 7.0  | 0.45  | 12.7 | 12.7           | 3.85           | 6.35           | 5.0          | 18.0 | 12.5           | 18.5  | 16.0           | 4.0            | 0.7  | 2.0  | 1    |
|           | 5 ~ 8   | 12.5 | 0.5   | 12.7 | 12.7           | 3.85           | 6.35           | 5.0          | 18.0 | 12.5           | 18.5  | 16.0           | 4.0            | 0.7  | 2.0  |      |
|           | 5, 6.3  | 12.5 | 0.5   | 12.7 | 12.7           | 5.1            | 6.35           | 2.5          | 18.0 | 12.5           | 18.5  | —              | 4.0            | 0.7  | 2.0  | 2    |
|           | 8       | 12.5 | 0.5   | 12.7 | 12.7           | 4.6            | 6.35           | 3.5          | 18.0 | 12.5           | 18.5  | —              | 4.0            | 0.7  | 2.0  |      |
|           | 10      | 21.0 | 0.6   | 12.7 | 12.7           | 3.85           | 6.35           | 5.0          | 18.0 | 12.5           | 18.5  | —              | 4.0            | 0.7  | 2.0  | 3    |
|           | 12, 13  | 26.0 | 0.6   | 15.0 | 15.0           | 5.0            | 7.5            | 5.0          | 18.0 | 12.5           | 18.5  | —              | 4.0            | 0.7  | 2.0  |      |
|           | 16, 18  | 26.0 | 0.8   | 30.0 | 15.0           | 3.75           | 7.5            | 7.5          | 18.0 | 12.5           | 18.0  | —              | 4.0            | 0.7  | 2.0  | 4    |

| Capacitor Diameter D (mm) | Ammo Pack Box Dimensions (mm) |       |     | Quantity Per Ammo Pack Box |
|---------------------------|-------------------------------|-------|-----|----------------------------|
|                           | A±5                           | B Max | C±3 |                            |
| 4                         | 250                           | 340   | 54  | 3000                       |
| 5                         | 250                           | 340   | 54  | 2,000                      |
| 6.3                       | 290                           | 340   | 54  | 2,000                      |
| 8                         | 250                           | 340   | 54  | 1,000                      |
| 10 (12L)                  | 290                           | 340   | 54  | 600                        |
| 10 (16L)                  | 350                           | 340   | 59  | 600                        |
| 10 (20L)                  | 340                           | 340   | 71  | 600                        |
| 12, 13                    | 340                           | 340   | 71  | 400                        |
| 16                        | 340                           | 340   | 71  | 300                        |



| Tape And Reel Quantities |            |                  |
|--------------------------|------------|------------------|
| Case Diameter D (mm)     | Reel Width | Reel Qty. (Pcs.) |
| 4                        | 44         | 1500             |
| 5                        | 44         | 1200             |
| 6                        | 44         | 1000             |
| 8                        | 44         | 800              |
| 10 (12L)                 | 44         | 600              |
| 10 (16L)                 | 50         | 600              |
| 12, 13                   | -          | -                |
| 16                       | -          | -                |

## Type SK 85 °C Radial Leaded Aluminum Electrolytic Capacitors

---

**Notice and Disclaimer:** All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.