




10 | 9 | 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1



NOTES:

1. TERMINAL TO BE USED IN HOUSING 70066-**** AND 70450-****.
2. REFER TO PRODUCT SPECIFICATION PS-70058.
3. REFER TO MOLEX OPERATIONS AND SERVICE MANUAL FOR CRIMP DETAILS.
4. TERMINAL TO BE USED WITH (0.64)/.025 SQUARE PINS.
5. TERMINAL TO BE USED WITH 24-30 AWG STRANDED WIRE WITH (1.52)/.060 MAXIMUM DIAMETER INSULATION.
6. TERMINALS SUPPLIED IN REEL FORM.
7. CRIMP SIZE INDICATOR A=24-30 AWG

PLATING:

.000150 MINIMUM TIN PLATE IN SELECT AREA,
OVER NICKEL PLATE OVERALL.

REEL UNWIND DIR		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 10:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
EC NO: UCP2013-5345	REV: H	4 PLACES	± ---	± ---	DRAWN BY RWHIPPLE DATE 2013/06/11			
DRWNR:RWHIPPLE	CHKD:DMORGAN	3 PLACES	± ---	± .005	CHECKED BY JAS DATE 1988/02/03			
2013/06/11	2013/06/11	2 PLACES	± 0.13	± .01				
APP:SMILLER	2013/07/09	1 PLACE	± 0.25	± ---	APPROVED BY SMILLER DATE 2013/07/09			
		0 PLACE	± ---	± ---				
ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. 16-02-0069		DOCUMENT NO. SD-70058-0004		SHEET NO. 1 OF 1		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION