

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2011

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

A1

-

B1

DIM "B" ADDED

05DEC2014

PS

JK

NOTES:

1. MATERIALS:

HOUSING-PA66, UL94 VO, COLOR-GREEN

SCREW- M5, STEEL, NICKEL PLATED

CLAMP- STEEL, NICKEL PLATED

CONTACT PIN- BRASS, TIN PLATED

2. MECHANICAL:

PCB THICKNESS-2.40 MAX

PCB HOLE DIAMETER-1.60 MIN

STRIP LENGTH-18 mm

OPERATING TEMPERATURE:-40°C TO +110°C

RECOMMENDED/HIGHEST TIGHTENING TORQUE-2.1/2.5 Nm.


3. ELECTRICAL:

WIRE RANGE- 20 TO 1 AWG

VOLTAGE RATING- 600 VOLTS


CURRENT RATING-130 A FIELD WIRING;135A FACTORY WIRING

CONTACT RESISTANCE-15 mOHM MAX

INSULATION RESISTANCE- 10^9 OHMS MIN (500V DC)SCALE 1:1
-3 AS SHOWN

199.00	180.00	12	1-1986715-2
184.00	165.00	11	1-1986715-1
169.00	150.00	10	1-1986715-0
154.00	135.00	9	1986715-9
139.00	120.00	8	1986715-8
124.00	105.00	7	1986715-7
109.00	90.00	6	1986715-6
94.00	75.00	5	1986715-5
79.00	60.00	4	1986715-4
64.00	45.00	3	1986715-3
49.00	30.00	2	1986715-2
DIM "B"	DIM "A"	POLE	PART NUMBER

RECOMMENDED PCB LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 13SEP2011

RAGHAVENDRA

CHK 13SEP2011

SARVER MICHAEL

APVD 13SEP2011

SARVER MICHAEL

PRODUCT SPEC

-

APPLICATION SPEC

-


WEIGHT

-

Customer Drawing

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±

0.25

1 PLC

±

0.20

2 PLC

±

0.20

3 PLC

±

0.20

4 PLC

±

0.20

ANGLES

±

1°

MATERIAL

-

FINISH

-

NAME

POWER TERMINAL BLOCK, DOUBLE PIN
MOUNTING FLANGES; PITCH 15.00 mm

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=

1986715

SCALE

1:1

SHEET

1

OF

1

REV

B1