

TELECOMMUNICATION MODEM COUPLING TRANSFORMER


A. Electrical Specifications (@ 25° C)

1. Primary Impedance; 600Ω
2. Secondary Impedance; 600Ω
3. Insertion Loss: 1.20dB MAX @ 1KHz, 1Vrms
4. Frequency Response; ±0.16dB @ 300Hz to 3.5KHz, 1Vrms
5. Inductance; 1.5H MIN (Lp) @ 1KHz, 1.0Vrms measured (1-3)
6. Leakage Inductance; 2.0mH (Ls) MAX @ 10KHz, 0.1Vrms measured (1-3) with 6 & 4 shorted
7. DC Resistance;
 - (1-3) : 58Ω ±15%
 - (6-5) : 14Ω ±15%
 - (5-4) : 62Ω ±15%
8. Turns Ratio; (6-4):(1-3)=1:1±2%
(1-3):(5-4)=1:0.8±2%
9. Dielectric Strength; 1850V 1 second, Pri-Sec

B. Marking; TTC-294, TAMURA, date code and country of origin

C. Safety; UL1950 3rd Edition

D. Schematic;




White dot
indicates
pin 1

Country
of Origin


Safety Logo



UL# E208555



E. Mechanical Specifications;



PREPARED BY:

K. BRENNAN

ENGINEER:

M. PITCHAI

QUALITY CONTROL:

T. CLEM

APPROVED:

Y. SEKIGUCHI

DWG CONTROL NO.
P-A1-12413
ACAD\TTC\A1124131.DWG

REV
B

TELECOMMUNICATION MODEM
COUPLING TRANSFORMER

CONTENTS OF THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(951) 699-1270 FAX 9516769482

TTC-294

MODEL SPECIFICATION

DIM: mm(In) SCL: 2/1 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.

**RoHS
COMPLIANT**

MODEL NUMBER

TTC-294