





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		E1	REVISED PER ECO-11-004820	11MAR11	RK	HMR


- 10.00203 [.000080] MIN BRIGHT TIN-LEAD OVER
0.00127 [.000050] MIN NICKEL.
- 20.00330 [.000130] MAX PRE-TIN.
3. WIRE RANGE: 0.2-0.9mm² (24-18 AWG).
INSULATION RANGE: 2.79 [.110] DIA MAX.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 50.00203 [.000080] MIN BRIGHT TIN OVER
0.00127 [.000050] MIN NICKEL.




SECTION D-D
SCALE 10:1



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1

5	3-640706-1
2	640706-2
1	640706-1
FINISH	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 21AUG2003	TE Connectivity			
DIMENSIONS: INCHES		CHK J. ELLIS 21AUG2003				
		APVD J. ELLIS 21AUG2003	NAME RECEPTACLE, SL-156, LOOSE PIECE			
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C-640706	RESTRICTED TO -
MATERIAL 0.33 [.013] BRASS		WEIGHT SEE TABLE	CUSTOMER DRAWING			
		FINISH SEE TABLE	SCALE 5:1	SHEET 1 of 1	REV E1	