

# T6218 Line Printer

The ultimate heavy duty workhorse with class leading speed



- 1800 lines per minute / 512,000 pages per month
- Wide variety of connectivity options including IPDS capability
- QMS and Code V giving high speed and quality graphics
- Fully supported for all versions of Windows and SAP R-3
- Parallel and serial interfaces
- Straight paper path; up to 6 part forms
- Fourplex version (Parallel, Serial, Twinax, Coax)
- LANPlex version (Parallel, Serial, Ethernet, IG and GPO)
- Quick change, clean hands, long life ribbon cartridges

With line printers it's about speed, workload, ergonomics and running costs. The 'Enterprise' T6218 satisfies all of these. At 1800 lines per minute with fast slew the printer meets the demands of large jobs and 'just-in-time' print tasks.

The patented 'Stay Black' easy to load, clean hands cartridge ribbon, has a capacity up to 250 million characters. Hence, the most arduous print tasks can be left to print unattended in complete confidence, at very low cost.

A simple stacking system stacks paper to perfection. High workload print tasks cost far less than any alternative digital print technology. Whether it's the back office, warehouse, factory or computer room, this is the best.

---

## Available Configuration:

- T6218** Enclosed Pedestal (Cabinet) Parallel & Serial Interface
- T6218N** Enclosed Pedestal (Cabinet) Parallel, Serial and Ethernet Interface
- T6218** Enclosed Pedestal Parallel, Serial ,Co-Ax and Twin-Ax Interface
- T6218LJ** Enclosed Pedestal With Laserjet Emulation
- LGi18** Enclosed Pedestal with DEC/Compaq Emulation

<b>Print Speed</b>	1800 lines per minute (upper case draft)
<b>Graphic Speed</b>	Up to 225 inches per minute
<b>Resolution</b>	Up to 240 x 288 dpi
<b>Character Density</b>	5, 6, 6.7, 7.5, 8.3, 8.6, 10, 12, 13.3, 15, 16.7, 17.1, 20 cpi (Enhanced Density) 12, 13.3, 15, 17.1 (Constant Density)
<b>Line Density</b>	1.5, 2, 3, 4, 5, 6, 8, 9, 10, 12 (plus variable line spacing)
<b>Memory</b>	16Mb
<b>Standard Connectivity</b>	IEEE 1284 compliant parallel, serial with 38.4K baud transfer
<b>Optional Connectivity</b>	Twinax and Coax (+IPDS), LANPlex, Ethernet (+IPDS)
<b>Standard Emulation</b>	MT660/MT690, Epson FX+, IBM ProPrinter XL, Genicom ANSI, HP2564C, Printronix P600/P6000, DEC LG01, Tally industrial graphics, QMS Code V, Printronix Graphics Language, MPTL, contextual Arabic
<b>Fonts</b>	Draft, Data Processing, Courier, Gothic, OCR-A, OCR-B. Range of Arabic
<b>Consumables</b>	Ribbon: 40, 60 and 250 million characters
<b>STD Paper Handling</b>	4 tractors. 36 inch per second slew rate (max.). Paper motion detection, paper out detection
<b>Number of Copies</b>	Up to 6 part forms
<b>Paper Type</b>	Continuous
<b>Paper Weight</b>	65 to 365 gsm
<b>Paper Size</b>	Width: 2.5 to 18.9 inches. Length: 1 to 255 lines
<b>Physical Weight</b>	85Kg
<b>PhysicalSize</b>	1016(h) x 732(w) x 719(d) mm
<b>Power Voltage</b>	Auto ranging: 90-130V and 180-264V
<b>Power Frequency</b>	57-63Hz and 47-53Hz
<b>Power Consumption</b>	215W average
<b>Workload</b>	512,000 pages per month
<b>Drivers</b>	
<b>Temperature</b>	
<b>Humidity</b>	
<b>Acoustic</b>	55dB(A)
<b>Warranty</b>	1 year on-site, 1 business day response. Installation Free of charge, mainland UK & Eire