

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A

A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

**ASSEMBLY-
PUSHBUTTON SWITCH**

CATALOG LISTING

IPB575-T

FAA-PMA

IPB575-T

PAGE 1 OF 1

MDRAWING
NUMBER**X**

ISSUE

8

REPLACES

PR-9121-T

CHECK

CHECK

REVISIONS

A	PR-9121	WJM	24 JUL 80	
B	C O	48535	JMJ	13 OCT 80
C	C048860	CEB	22 DEC 80	
D	C049278	JAP	MAR 81	
E	C077562	JAL	MAR 94	
F	CO-93156	GJW	20 JUL 98	
G	C093880	GJW	6 JAN 99	

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK


CHECK

**NOTE -**

- 1 - UNIT INCLUDES CAT. LIST. "23SM" BASIC SWITCH
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - RECOMMENDED FOR MANUAL OPERATION ONLY
- 4 - MOUNTING HARDWARE AND WHITE PLASTIC BUTTON FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**OPERATING FORCE --- 1 LB APPROX
TOTAL TRAVEL ----- .030 APPROX**ELECTRICAL DATA**CONTACT ARRANGEMENT
S P D T**30 VOLT DC RATING**INDUCTIVE ----- SEA LEVEL ----- .5 AMP
50,000 FT ----- .5 AMP
RESISTIVE ----- SEA LEVEL ----- 1.0 AMP
50,000 FT ----- 1.0 AMP
MAXIMUM INRUSH ----- .2 AMP**SCALE FULL**

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM.	TOL.	DIM.	TOL.
	mm	mm/in	in	mm/in
NO PLACES	X	1/.04		
ONE PLACE	X,X	0.4/.016	X,X	0.8/.03
TWO PLACES	X,XX	0.19/.008	X,XX	0.38/.015
THREE PLACES			X,XXX	0.13/.005
ANGLES				

DESIGN UNITS ☐ SI METRICUS CUSTOMARY ☒

WEIGHT

FORMTEK

FO-52848-A

DRAWN

WJM 24 JUL 80

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1PB575-T](#)